

DC axial fan

Series 600 J 60 x 60 x 32



- **General description:** DC fan with electronically commutated external rotor motor. Commutation electronics completely integrated. Innovative impeller design with winglets. Compact design with high power density. Rigid compression curve at low noise.


- **Impeller material:** Fiberglass-reinforced PA plastic

- **Housing material:** Fiberglass-reinforced PBT plastic

Nominal data		Voltage	Voltage range VDC	Air flow	Speed	Power consumption	Sound level	Sound pressure level	Ambient temperature	L10 service life at 40 °C	L10 service life at max. temp.	Weight
Type	Motor	VDC	VDC	m³/h	1/min	W	Bel	dB(A)	°C	h	h	kg
614 JH	--	24	14 - 26.4	70	11700	7.7	6.4	53	-20 .. 70	57500	27500	0.100

Subject to modification


Characteristic: Pressure over air flow



DC axial fan

Series 600 J 60 x 60 x 32

Specific drawing



Technical description

- **General description:** DC fan with electronically commutated external rotor motor. Commutation electronics completely integrated. Innovative impeller design with winglets. Compact design with high power density. Rigid compression curve at low noise.
- **Housing material:** Fiberglass-reinforced PBT plastic
- **Direction of rotation:** Right, looking at rotor
- **Electrical connection:** 2 single strands AWG 24, TR 64
- **Locked-rotor protection:** With electronic locked-rotor and overload protection
- **Option:** Speed signal
- **Impeller material:** Fiberglass-reinforced PA plastic
- **Bearings:** Ball bearings
- **Direction of air flow:** Air exhaust over bars
- **Motor protection:** With electronic reverse polarity protection. The fan runs only if the polarity is correct.
- **Approvals:** CE

Contact

ebm-papst St. Georgen GmbH & Co. KG
Hermann-Papst-Straße 1
D-78112 St. Georgen
Phone +49 (0) 7724 / 81-0
Fax +49 (0) 7724 / 81-1309
info2@de.ebmpapst.com
www.ebmpapst.com