PREPARED BY:	DATE:			SPEC. No.	ED-99075
	7 1029	SHA	RP	ISSUE	April 7, 1999
J. Tabacka 4	ord. 6./911			PAGE	8 Pages
APPROVED BY:	DATE:	ELECTRONIC COM GROUP SHARP CO		REPRESENT	TATIVE DIVISION
T. M. 800 24	8 1000	SPECIFICA			TRONIC DEVICES DIV.
		E SPECIFICATION FOR			
	MODE	DISTANCE MEASURI L No.	NG SENSOR		
		GP2Y0D02	YK		
	-				
These specific     Please do not	cation sheets in reproduce or c	clude materials protected un ause anyone to reproduce th	der copyright of S em without Sharp	harp Corporation's consent.	on ("Sharp").
in these spec for any dama	ification sheets ge resulting fro	ease observe the absolute ma , as well as the precautions in m use of the product which d in these specification shee	nentioned below. does not comply w	Sharp assumes rith the absolute	no responsibility maximum ratings
(Precaution	ıs)				
(1) This	s product is des	igned for use in the followin	g application areas	s; <b>–</b>	
	OA equipment	<ul> <li>Audio visual equipment tion equipment (Terminal)</li> </ul>	· Home appliance	es	
•		roduct in the above applicati			
(2)	or (3), please b	e sure to observe the precau	tions given in thos	se respective pa	ragraphs.
the and	safety design of safety when th	res, such as fail-safe design the overall system and equi is product is used for equipn nd precision, such as;	pment, should be	taken to ensure	reliability
		control and safety equipmen			
I I	Fraffic signals Other safety eqi	· Gas leakage sensor break tipment	ers · Rescue and	l security equip	ment
(3) Plea	se do not use safety in functi	this product for equipment wo on and precision, such as ;	hich require extre	mely high relial	pility
$\lceil \cdot \rfloor$	Space equipmer	it · Telecommunication equipment · Medica	uipment (for trunk l equipment	lines)	
(4) Plea	se contact and	consult with a Sharp sales ration of the above three para	epresentative if th	ere are any que	stions
:		ith a Sharp sales representa	_	ions about this	product
		1			product.
CUSTOME	R'S APPROVA	L	DATE PRESENTEI BY	Dawo	
DATE				7	
BY			Opto-E	lectronic Devid M Group	ces Div.

ED-99075	April 7,	1999
MODEL No.		PAGE
GP2Y0	D02YK	1/8

### 1. Application

This specification applies to the outline and characteristics of 1 bit output type distance measuring sensor, Model No. GP2Y0D02YK.

### 2. Outline

Refer to the attached drawing No. SOD03673A.

## 3. Ratings and characteristics

- 3-1 Constitution diagram: Refer to the attached sheet, page 4.
- 3-2 Absolute maximum ratings: Refer to the attached sheet, page 4.
- 3-3 Electro-optical Characteristics: Refer to the attached sheet, page 5.
- 3-4 Timing chart: Refer to the attached sheet, page 5.

### 4. Reliability

Refer to the attached sheet, page 6.

### 5. Incoming inspection

Refer to the attached sheet, page 7.

### 6. Supplement

6-1 GP2Y0D02YK Example of Output distance characteristics

Refer to the attached sheet, page 8.

## 6-2 ODS materials

This product shall not contain the following materials. Also, the following materials shall not be used in the production process for this product.

Materials for ODS  $\,:\,$  CFC  $_{\rm S},$  Halon, Carbon tetrachloride,


 $1.1.\tilde{1}$ -Trichloroethane (Methylchloroform)

6-3 Product mass: Approx. 4.8g


- 1			
	ED-99075	April 7,	1999
	MODEL No.		PAGE
	GP2Y01	D02YK	2/8

#### 7. Notes

- 7-1 Lens of this device shall be kept cleanly. There are cases that dust, water or oil and so on deteriorate the characteristics of this device. Please consider in actual application.
- 7-2 In case that protection cover is set in front of the emitter and detector portion, the protection cover which has the most efficient transmittance at the emitting wavelength range of LED for the GP2Y0D02YK (  $\lambda$  =850nm $\pm$ 70nm), shall be recommended to use. The face and back of protection cover should be mirror polishing. Also, as there are cases that the characteristics may not be satisfied with according to the distance between the protection cover and the GP2Y0D02YK or the thickness of the protection cover, please use the GP2Y0D02YK after confirming the operation sufficiently in actual application.
- 7-3 In case that there is an object near to light exits of the sensor between the sensor and the detected object, please use this device after confirming sufficiently what the characteristics of this sensor do not change by the object.
- 7-4 When the detector surface receive direct light from the sun, Tungsten lamp and so on, there are cases that it can not measure the distance exactly. Please consider the design that the detector does not receive direct light from such light source.
- 7-5 Distance between sensor and mirror reflector can not sometimes measure exactly. In case of changing the mounting angle of the GP2Y0D02YK, it may measure the distance exactly.
- 7-6 In case that reflective object has boundary line clearly, there is cases that distance can not measure exactly. At that time, if direction of boundary line and the line between emitter center and detector center parallels, it is possible to decrease deviation of measuring distance.



7-7 In order to decrease measuring error by moving direction of object, we recommend to mount the sensor like below drawing.



- 7-8 In order to stabilize power supply line, we recommend to connect a by-pass capacitor of 10  $\mu$ F or more between Vcc and GND near the GP2Y0D02YK.
- 7-9 Please don't do washing. Washing may deteriorate the characteristics of optical system and so on.
- 7-10 There are some possibilities that the sensor inside the case package with lens may be exposed to the excessive mechanical stress. Please be careful not to cause any excessive pressure on the case package with lens and also on the PCB at the assembly and inserting of the set.

ED-99075 April 7, 1999


MODEL No. PAGE
GP2Y0D02YK 3/8

#### 2. Outline


. . .

Note 1) \* dimension shall be reference lens center.

Note 2) Unspecified tolerance shall be  $\pm 0.3 mm$ .




Stamp (Example)




Connector signal

	Signal name
1	Vo
2	GND
3	Vcc

Connector: J.S.T. TRADING COMPANY, LTD. S3B-PH





Material

Lens: Acrylic acid resin

(Visible light cut-off resin)

Case: Carbonic ABS

(Electro-conductive resin)

PCB: Paper phenol


(Scale : 2/1) (Unit : mm)

Name	GP2Y0D02YK Outline Dimensions
Drawing No.	SOD03673A

ED-99075	April 7, 1999
MODEL No.	PAGE
GP2Y0	D02YK 4/8

# 3. Ratings and characteristics

## 3-1 Constitution diagram



# 3-2 Absolute maximum ratings

(Ta=25°C, Vcc=5V)

Parameter	Symbol	Rating	Unit	Remark
Supply voltage	Vcc	-0.3 to +7	V	-
Output terminal voltage	Vo	-0.3 to Vcc+0.3	V	Open collector output
Operating temperature	Topr	-10 to +60	C	-
Storage temperature	Tstg	-40 to +70	Ĉ	-

# · Operating Supply Voltage

Parameter	Symbol	Rating	Unit	Remark
Operating Supply Voltage	Vec	4.5 to 5.5	V	-

ED-99075	April 7, 1999			
 MODEL No.		PAGE		
GP2Y0	D02YK	5/8		


## 3-3 Electro-optical Characteristics

(Ta=25°C, Vcc=5V)

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Unit
Measuring distance range	ΔL	(*1) (*3)	200	-	1500	mm
Output terminal voltage	$V_{\mathrm{OH}}$	Output voltage at high level (*1)	Vcc -0.3	-	-	
	V <sub>OL</sub>	Output voltage at low level (*1)	-	-	0.6	V
Output distance characteristics	Vo	(*1) (*2) (*4)	700	800	900	mm
Average supply current	Icc		-	33	50	mA

- L: Distance to reflective object
- (\*1) Using reflective object : White paper (Made by Kodak Co. Ltd. gray cards R-27 white face, reflective ratio; 90%)
- (\*2) We ship the device after the following adjustment: Output switching distance L=800mm  $\pm 100$ mm must be measured by the sensor
- (\*3) Possible distance measuring range (of the sensor optics)
- (\*4) Output switching has a hysteresis width. The distance specified by Vo should be the one with which the output L switches to the output H.

### 3-4 Timing chart



ED-99075	April 7,	1999
MODEL No. GP2Y0	D02YK	PAGE 6/8

### 4. Reliability

The reliability of products shall satisfy items listed below.

Confidence level : 90% LTPD : 20%/40%

No.	Total		T	T
No.	Test Items	Test Conditions	Failure Judgement Criteria	Samples (n) Defective(C)
1	Temperature cycling	1 cycle -40°←→+70°C (30min) (30min) 25 cycles test		n=11, C=0
2	High temp. and high humidity storage	+40℃,90%RH, 500h		n=11, C=0
3	High temp. storage	+70℃, 500h	Initial $ imes$ 0.8 $>$ Vo	n=11, C=0
4	Low temp. storage	-40℃, 500h	Vo > Initial × 1.2	n=11, C=0
5	Operation life (High temp.)	+60℃, Vec=5V, 500h	(*1)	n=11, C=0
6	Mechanical shock	$100\text{m/s}^2$ , 6.0ms $3\text{times}/\pm X$ , $\pm Y$ , $\pm Z$ direction		n= 6 , C=0
7	Variable frequency vibration	10 to 55 to 10Hz/1min Overall amplitude : 1.5mm 2h/X, Y, Z direction		n= 6 , C=0

<sup>\*1</sup> Test conditions are according to 3-3 Electro-optical characteristics. Vo : L=800mm  $\pm 100$ mm at initial

<sup>\*2</sup> After test, measurement shall be measured after leaving under the normal temperature and the normal humidity for two hours. But, no dew point.

ED-99075	April 7, 1999	
MODEL No.  GP2Y0D02YK		PAGE
GI 210L	/UZ1K	1/0

## 5. Incoming inspection

(1) Inspection lot

Inspection shall be carried out per each delivery lot.

(2) Inspection method

A single sampling plan, normal inspection level  $\, \mathbb{I} \,$  based on ISO 2859 shall be adopted.

Defect	Inspection items and test method	
Major defect	Electro-optical characteristics defect (In para. 3-3)	0.4
Minor defect	Defect on appearance and dimension	1.0


Split Chip

One which affects the characteristics Scratch of para. 3-3 shall be defect.

Stain

ED-99075	April 7, 1999	_
MODEL No.  GP2Y0I	PAGE 8/8	

# 6-1 GP2Y0D02YK Example of Output distance characteristics



Distance to reflective object L (mm)