

.08  
(2.0) VP. ▸ ▸

.467  
(.86) ▸ ▸  
2 C PCU

.467  
(.86) ▸ ▸  
4 C PCU

.633  
(6.08) ▸ ▸  
6 C PCU

.055  
(.40) ▸ ▸

.055  
(.40) ▸ ▸

.08  
(2.0) VP. ▸ ▸

. MATERIAL: UNF LLED POLYES EP, U.L. 94V 0.

2. FINISH COLOR:  
A MOLDED BLAC

P. ANGLE ENDEPS 30070 & 44483.

5. PRODUCT SPECIFICATION: PS 5556 003.


6.

.30 ▸ ▸


.28  
(2.8) ▸ ▸

.08  
(2.0) VP. ▸ ▸


CKT. SIZE	ENG. NO.	EDP. NO.	DIM. "A"	DIM. "B"
02	30067-02A2	15-97-5021	—	.467 (11.86)
04	30067-04A2	15-97-5041	.165 (4.20)	.467 (11.86)
06	30067-06A2	15-97-5061	.331 (8.40)	.633 (16.08)
08	30067-08A2	15-97-5081	.496 (12.60)	.798 (20.27)
10	30067-10A2	15-97-5101	.661 (16.80)	.963 (24.46)
12	30067-12A2	15-97-5121	.827 (21.00)	1.129 (28.68)
14	30067-14A2	NOT TOOLED	.992 (25.20)	1.294 (32.87)
16	30067-16A2	15-97-5161	1.157 (29.40)	1.459 (37.06)
18	30067-18A2	NOT TOOLED	1.520 (38.60)	1.822 (46.28)
20	30067-20A2	NOT TOOLED	1.685 (42.80)	1.987 (50.46)
22	30067-22A2	NOT TOOLED	1.850 (47.00)	2.152 (54.66)
24	30067-24A2	NOT TOOLED	2.016 (51.20)	2.318 (58.88)




24 CIRCUIT



22 CIRCUIT



20 CIRCUIT



18 CIRCUIT

LEGEND:

30067 - \*\* \* 2  
 CIRCUIT SIZE (02-24)  
 HOUSING COLOR  
 A = MOLDED BLACK

SEE SHEET ONE EC NO: UCP2005-1142 G DRWALS:EMWART 2004/12/16 CHKD:GPOLGAR 2004/12/16 APPR:YMARGULLI 2004/12/20 REV DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE IN/MM	SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION																														
	 	<table border="1"> <thead> <tr> <th></th> <th>mm</th> <th>INCH</th> </tr> </thead> <tbody> <tr> <td>4 PLACES</td> <td>± .010</td> <td>± .0004</td> </tr> <tr> <td>3 PLACES</td> <td>± .012</td> <td>± .0005</td> </tr> <tr> <td>2 PLACES</td> <td>± 0.25</td> <td>± .010</td> </tr> <tr> <td>1 PLACE</td> <td>± 0.36</td> <td>± .014</td> </tr> <tr> <td colspan="3">ANGULAR ±1/2°</td> </tr> </tbody> </table>		mm	INCH	4 PLACES	± .010	± .0004	3 PLACES	± .012	± .0005	2 PLACES	± 0.25	± .010	1 PLACE	± 0.36	± .014	ANGULAR ±1/2°			<table border="1"> <tr> <td>DRAWN BY</td> <td>DATE</td> </tr> <tr> <td>RJF</td> <td>09/23/09</td> </tr> <tr> <td>CHECKED BY</td> <td>DATE</td> </tr> <tr> <td>GEP</td> <td>09/23/09</td> </tr> <tr> <td>APPROVED BY</td> <td>DATE</td> </tr> <tr> <td>RAS</td> <td>09/23-04</td> </tr> </table>	DRAWN BY	DATE	RJF	09/23/09	CHECKED BY	DATE	GEP	09/23/09	APPROVED BY	DATE	RAS	09/23-04	TITLE	MINI-FIT T.P.A. RECEPTACLE HOUSING	
		mm	INCH																																	
	4 PLACES	± .010	± .0004																																	
3 PLACES	± .012	± .0005																																		
2 PLACES	± 0.25	± .010																																		
1 PLACE	± 0.36	± .014																																		
ANGULAR ±1/2°																																				
DRAWN BY	DATE																																			
RJF	09/23/09																																			
CHECKED BY	DATE																																			
GEP	09/23/09																																			
APPROVED BY	DATE																																			
RAS	09/23-04																																			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO. SEE CHART	DOCUMENT NO. SD-30067-*	SHEET NO. 2 OF 2																															
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																				