IN

- No Frequency Compensation Required
- Low Power Consumption
- Short-Circuit Protection
- Offset-Voltage Null Capability
- Wide Common-Mode and Differential Voltage Ranges
- No Latch-Up
- Designed to Be Interchangeable With Fairchild μA747C and μA747M


#### description

The uA747 is a dual general-purpose operational amplifier featuring offset-voltage null capability. Each half is electrically similar to uA741.

The high common-mode input voltage range and the absence of latch-up make this amplifier ideal for voltage-follower applications. The device is short-circuit protected and the internal frequency compensation ensures stability without external components. A low-value potentiometer may be connected between the offset null inputs to null out the offset voltage as shown in Figure 2.

The uA747C is characterized for operation from  $0^{\circ}$ C to  $70^{\circ}$ C; the uA747M is characterized for operation over the full military temperature range of  $-55^{\circ}$ C to  $125^{\circ}$ C.


#### symbol (each amplifier)



#### (TOP VIEW) 14 OFFSET 1N1 IN + [ ] 1 V<sub>CC +</sub>† 2 13 OFFSET 1N2 □ Тυο Π 12 J NC Vcc\_[ 11 10 OUT $IN + \Gamma$ 9 2 V<sub>CC+</sub>†

**OFFSET 2N1** 

D, J, N, OR W PACKAGE



NC - No internal connection


#### **AVAILABLE OPTIONS**

		PACKAGE							
1	V May				20-PIN				
TA	V <sub>IO</sub> Max AT 25°C	SMALL OUTLINE (D)	CERAMIC DIP (J)	PLASTIC DIP (N)	FLAT PACK (W)	CHIP CARRIER (FK)			
0°C to									
to 70°C	6 mV	uA747CD	_	uA747CN	_	_			
–55°C									
to 125°C	5 mV	_	uA747MJ	_	uA747MW	uA747MFK			

The D package is available taped and reeled. Add the suffix R to the device type, (i.e., uA747CDR).

<sup>&</sup>lt;sup>†</sup> The two positive supply terminals (1 V<sub>CC +</sub> and 2 V<sub>CC +</sub>) are connected together internally.

#### schematic (each amplifier)



#### absolute maximum ratings over operating free-air temperature range (unless otherwise noted)

		uA747C	uA747M	UNIT
Supply voltage, V <sub>CC+</sub> (see Note 1)	18	22	V	
Supply voltage, V <sub>CC</sub> (see Note 1)		-18	-22	V
Differential input voltage (see Note 2)		±30	±30	V
Input voltage any input (see Notes 1 and 3)		±15	±15	V
Voltage between any offset null terminal (N1/N2) and V <sub>CC</sub> -	±0.5	±0.5	V	
Duration of output short circuit (see Note 4)	unlimited	unlimited		
Continuous total dissipation	See Diss	ipation Rating Ta	ble	
Operating free-air temperature range		0 to 70	-55 to 125	°C
Storage temperature range		-65 to 150	-65 to 150	°C
Case temperature for 60 seconds	FK package		260	°C
Lead temperature 1,6 mm (1/16 inch) from case for 60 seconds	J or W package		300	°C
Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds	D or N package	260		°C

- NOTES: 1. All voltage values, unless otherwise noted, are with respect to the midpoint between  $V_{CC}$  + and  $V_{CC}$  -.
  - 2. Differential voltages are at the noninverting input terminal with respect to the inverting input terminal.
  - 3. The magnitude of the input voltage must never exceed the magnitude of the supply voltage or 15 V, whichever is less.
  - 4. The output may be shorted to ground or either power supply. For the uA747M only, the unlimited duration of the short circuit applies at (or below) 125°C case temperature or 75°C free-air temperature.

#### **DISSIPATION RATING TABLE**

PACKAGE	$T_{\mbox{A}} \le 25^{\circ}\mbox{C}$ POWER RATING	DERATING FACTOR	DERATE ABOVE T <sub>A</sub>	T <sub>A</sub> = 70°C POWER RATING	T <sub>A</sub> = 125°C POWER RATING
D	800 mW	7.6 mW/°C	45°C	608 mW	_
FK	800 mW	11.0 mW/°C	77°C	800 mW	275 mW
J	800 mW	11.0 mW/°C	77°C	800 mW	275 mW
N	800 mW	9.2 mW/°C	63°C	736 mW	_
W	800 mW	8.0 mW/°C	50°C	640 mW	200 mW



SLOS009A - D971, FEBRUARY 1971 - REVISED OCTOBER 1990

# electrical characteristics at specified free-air temperature, $V_{\mbox{CC}\pm}$ = $\pm 15~\mbox{V}$

PARAMETER		TEST CONDITIONS†	TA∓	ι	uA747C			uA747M		
			'A*	MIN	TYP	MAX	MIN	TYP	MAX	UNIT
\/.0	Input offset voltage	Va - 0	25°C		1	6		1	5	mV
VIO	Input offset voltage	VO = 0	Full range			7.5			6	IIIV
$\Delta V$ IO(adj)	Offset voltage adjust range		25°C		±15			±15		mV
L =	land offers and accomment		25°C		20	200		20	200	A
liO	Input offset current		Full range			300			500	nA
L-	Innut hine aument		25°C		80	500		80	500	A
IIB	Input bias current		Full range			800			1500	nA
\/	Common-mode		25°C	±12	±13		±12	±13		V
VICR	input voltage range		Full range	±12			±12			V
	Maximum peak-to-peak	R <sub>L</sub> = 10 kΩ	25°C	24	28		24	28		
		R <sub>L</sub> ≥ 10 kΩ	Full range	24			24			٧
VO(PP)	output voltage swing	R <sub>L</sub> = 2 kΩ	25°C	20	26		20	26		
		$R_L \ge 2 k\Omega$	Full range	20			20			
AVD	Large-signal differential	$R_L \ge 2 k\Omega$ ,	25°C	25	200		50	200		V/mV
	voltage amplification	$V_0 = \pm 10 \text{ V}$	Full range	15			25			
rį	Input resistance		25°C	0.3	2		0.3*	2		МΩ
r <sub>O</sub>	Output resistance	See Note 5	25°C		75			75		Ω
Ci	Input capacitance		25°C		1.4			1.4		pF
CMDD	Common-mode rejection ratio	V V	25°C	70	90		70	90		dB
CMRR		V <sub>IC</sub> = V <sub>ICR</sub>	Full range	70			70			aB
ksvs	Supply-voltage sensitivity	V <sub>CC</sub> = ± 9 V to ± 15 V	25°C		30	150		30	150	μV/V
	(ΔV <sub>IO</sub> / ΔV <sub>CC</sub> )	VCC = ±0 V to ± 10 V	Full range			150			150	μν/ν
los	Short-circuit output current		25°C		±25	±40		±25	±40	mA
	Supply current	Notes	25°C		1.7	2.8		1.7	2.8	mA
ICC	(each amplifier)	No load	Full range			3.3			3.3	IIIA
PD	Power dissipation	No load, $V_0 = 0$	25°C		50	85		50	85	mW
טי	(each amplifier)	No load, $V_0 = 0$	Full range			100			100	11100
$V_{01}/V_{02}$	Channel separation		25°C		120			120	0	dB

<sup>†</sup> All characteristics are measured under open-loop conditions with zero common-mode input voltage unless otherwise specified.

# operating characteristics, V<sub>CC</sub> $_{\pm}$ = $\pm$ 15 V, T<sub>A</sub> = 25°C

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
t <sub>r</sub>	Rise time	$V_{\parallel}$ = 20 mV, R <sub>L</sub> = 2 k $\Omega$ , C <sub>L</sub> = 100 pF, See Figure 1		0.3		μs
	Overshoot factor			5%		
SR	Slew rate at unity gain	$V_I = 10 \text{ mV}, R_L = 2 \text{ k}\Omega, C_L = 100 \text{ pF}, \text{ See Figure 1}$		0.5		V/μs

<sup>‡</sup> Full range for uA747C is 0°C to 70°C and for uA747M is -55°C to 125°C.

<sup>\*</sup>On products compliant to MIL-STD-883, Class B, this parameter is not production tested.

NOTE 5: This typical value applies only at frequencies above a few hundred hertz because of the effects of drift and thermal feedback.

#### PARAMETER MEASUREMENT INFORMATION




Figure 1. Rise Time, Overshoot, and Slew Rate

#### **APPLICATION INFORMATION**




Figure 2. Input Offset Voltage Null Circuit

#### TYPICAL CHARACTERISTICS<sup>†</sup>

# INPUT OFFSET CURRENT vs




Figure 3

#### **INPUT BIAS CURRENT**

#### vs FREE-AIR TEMPERATURE




Figure 4

<sup>†</sup> Data at high and low temperatures are applicable only within the rated operating free-air temperature range of the particular devices.



#### TYPICAL CHARACTERISTICS




Figure 5

**OPEN-LOOP LARGE-SIGNAL** 




Figure 7

10 12

 $|V_{CC\pm}|$  – Supply Voltage – V

14 16

8




Figure 6

#### **OPEN-LOOP LARGE-SIGNAL DIFFERENTIAL VOLTAGE AMPLIFICATION**




Figure 8




20

20


10

0 2

#### TYPICAL CHARACTERISTICS



#### rigule 5







ti.com 23-Apr-2005

#### PACKAGING INFORMATION

Orderable Device	Status <sup>(1)</sup>	Package Type	Package Drawing	Pins Packa Qty	age Eco Plan <sup>(2)</sup> /	Lead/Ball Finish	MSL Peak Temp <sup>(3)</sup>
UA747-1MJ	OBSOLETE	CDIP	J	14	TBD	Call TI	Call TI
UA747CD	OBSOLETE	SOIC	D	14	TBD	Call TI	Call TI
UA747CD	OBSOLETE	SOIC	D	14	TBD	Call TI	Call TI
UA747CDR	OBSOLETE	SOIC	D	14	TBD	Call TI	Call TI
UA747CDR	OBSOLETE	SOIC	D	14	TBD	Call TI	Call TI
UA747CN	ACTIVE	PDIP	N	14 25	Pb-Free (RoHS)	CU NIPDAU	Level-NC-NC-NC
UA747CN	ACTIVE	PDIP	N	14 25	Pb-Free (RoHS)	CU NIPDAU	Level-NC-NC-NC

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS) or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

**Pb-Free** (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

(3) MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

### 14 LEADS SHOWN



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package is hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
- E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

## N (R-PDIP-T\*\*)

## PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- The 20 pin end lead shoulder width is a vendor option, either half or full width.



# D (R-PDSO-G14)

## PLASTIC SMALL-OUTLINE PACKAGE



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15).
- D. Falls within JEDEC MS-012 variation AB.



#### **IMPORTANT NOTICE**

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DSP	dsp.ti.com	Broadband	www.ti.com/broadband
Interface	interface.ti.com	Digital Control	www.ti.com/digitalcontrol
Logic	logic.ti.com	Military	www.ti.com/military
Power Mgmt	power.ti.com	Optical Networking	www.ti.com/opticalnetwork
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
		Telephony	www.ti.com/telephony
		Video & Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments

Post Office Box 655303 Dallas, Texas 75265

Copyright © 2005, Texas Instruments Incorporated