


2.54mm (.100") Pitch

SL™

Interim Clip

70013

Dual Row



Not For Use With Molex C-Grid III™ Components

Circuits	Order No.	
	Version A Without Ribs	Version B With Ribs
6	15-04-5061	15-04-5064
8	15-04-5081	15-04-5084
10	15-04-5101	15-04-5104
12	15-04-5121	15-04-5124
14	15-04-5141	15-04-5144
16	15-04-5161	15-04-5164
18	15-04-5181	15-04-5184
20	15-04-5201	15-04-5204

Features and Benefits

- Sizes 6 to 50 circuits
- Positive latch retains clip to dual row panel mount or headers
- Optional front polarization rib available (version B)
- Stacks single row 70066/70400D assemblies side-to-side and end-to-end to form a larger dual row connector, accepts 70450C dual row connector to provide positive latch feature

Reference Information

Packaging: Bag
 UL File No.: E29179
 CSA File No.: LR19980
 Mates With: 70013, Version A—8724B and 70567B
 70013, Version B—70022, 70567C, 70568,
 71349 and 70229

Use With: 70066D housing and 70021 terminals, 70450C housing and 70021 terminals, 70430D and 70400D connector assemblies

Designed In: Inches

Physical

Housing: Black polyester, UL 94V-0
 Operating Temperature: -40 to +105°C

Circuits	Order No.	
	Version A Without Ribs	Version B With Ribs
22	15-04-5221	15-04-5224
24	15-04-5241	15-04-5244
26	15-04-5261	15-04-5264
28	15-04-5281	15-04-5284
30	15-04-5301	15-04-5304
32	15-04-5321	15-04-5324
34	15-04-5341	15-04-5344
36	15-04-5361	15-04-5364

Circuits	Order No.	
	Version A Without Ribs	Version B With Ribs
38	15-04-5381	15-04-5384
40	15-04-5401	15-04-5404
42	15-04-5421	15-04-5424
44	15-04-5441	15-04-5444
46	15-04-5461	15-04-5464
48	15-04-5481	15-04-5484
50	15-04-5501	15-04-5504


2.54mm (.100") Pitch

SL™

Wire-to-Board Shrouded Header

70543

Single Row, .120" Pocket Vertical



Not For Use With C-Grid III™ Components

Circuits	Order No.			Lead-free
	150µm Tin	15µm Gold	30µm Gold	
2	70543-0036	70543-0001	70543-0106	Yes
3	70543-0037	70543-0002	70543-0107	
4	70543-0038	70543-0003	70543-0108	
5	70543-0039	70543-0004	70543-0109	
6	70543-0040	70543-0005	70543-0110	
7	70543-0041	70543-0006	70543-0111	
8	70543-0042	70543-0007	70543-0112	
9	70543-0043	70543-0008	70543-0113	
10	70543-0044	70543-0009	70543-0114	
11	70543-0045	70543-0010	70543-0115	
12	70543-0046	70543-0011	70543-0116	
13	70543-0047	70543-0012	70543-0117	

Features and Benefits

- Sizes 2 to 25 circuits
- Locking crown secures positive latch to header
- Polarization slots guide front ribs of mating connector to prevent pin damage
- Standoffs minimize flux retention

Reference Information

Product Specification: PS-70541
 Packaging: Tube
 UL File No.: E29179
 CSA File No.: LR19980
 Mates With: 70066G, 70066N, 70400G and 70430G
 Designed In: Inches

Electrical

Voltage: 250V
 Current: 3.0A
 Contact Resistance: 15 milliohms max.
 Dielectric Withstanding Voltage: 1500V
 Insulation Resistance: 10,000 Megohms min.

Mechanical

Durability: Tin—25 cycles; Gold—50 cycles

Physical

Housing: Black polyester, UL 94V-0
 Contact: Copper Alloy
 Plating: See Table
 Operating Temperature: -40 to +105°C

Circuits	Order No.			Lead-free
	150µm Tin	15µm Gold	30µm Gold	
14	70543-0048	70543-0013	70543-0118	Yes
15	70543-0049	70543-0014	70543-0119	
16	70543-0050	70543-0015	70543-0120	
17	70543-0051	70543-0016	70543-0121	
18	70543-0052	70543-0017	70543-0122	
19	70543-0053	70543-0018	70543-0123	
20	70543-0054	70543-0019	70543-0124	
21	70543-0055	70543-0020	70543-0125	
22	70543-0056	70543-0021	70543-0126	
23	70543-0057	70543-0022	70543-0127	
24	70543-0058	70543-0023	70543-0128	
25	70543-0059	70543-0024	70543-0129	