




HC-49/U Standard Height Crystal



HC-49/U

FEATURES

- Wide Frequency Range
- Additional EMI Protection
- Custom Manufacturing Capability
- Fast Turnaround Options

APPLICATIONS

- Microprocessor Systems
- Datacommunications
- Consumer Electronics
- Automotive Electronics

STANDARD SPECIFICATION


Frequency Range: 300 kHz to 225 MHz
 Adjustment Tolerance at 25°C: ±30PPM Max.
 Frequency Stability: ±50PPM Max.
 Operating Temperature Range: -10°C to +60°C
 Load Capacity: 30pF
 E.S.R: See Table
 Drive level: 500 MicroWatt
 Ageing: ±5PPM 1st Year Max.

| Frequency Range | E.S.R |
|-------------------|--------|
| 300kHz ~ 800 kHz | 3000 Ω |
| 800kHz ~ 1.3 MHz | 5000 Ω |
| 1.8 MHz ~ 2.0 MHz | 800 Ω |
| 2.0MHz ~ 2.4 MHz | 300 Ω |
| 2.4MHz ~ 3.0 MHz | 250 Ω |
| 3.0MHz ~ 3.2 MHz | 120 Ω |
| 3.2MHz ~ 4.0 MHz | 90 Ω |
| 4.0MHz ~ 4.2 MHz | 100 Ω |
| 4.2MHz ~ 6.0 MHz | 50 Ω |
| 6.0MHz ~ 8.0 MHz | 40 Ω |
| 8.0MHz ~ 36 MHz | 25 Ω |
| 36MHz ~ 64 MHz | 40 Ω |
| 64MHz ~ 125 MHz | 80 Ω |
| 125MHz ~ 200 MHz | 140 Ω |

AVAILABLE OPTIONS

Frequency Range: 300 kHz ~ 225 MHz
 Adjustment Tolerance: ±5PPM ~ ±100PPM
 Load Capacity: Series or 9pF ~ 50pF
 Shunt Capacity (C0): 4.5pF ~ 7pF (Typ.)
 Dynamic Capacity (C1): 18fF ~ 20fF (Typ.)

Frequency Stability vs Operating Temperature Range



Value Added Services

In addition, AEL Crystals Ltd are able to offer our customers the following value added services:-

- Fitted Insulators
- Radial Taping
- Lead Pre-Forming
- Lead Cropping
- Earth Lead
- Bar-Coding



www.aelcrystals.co.uk

quartz based frequency control components

Order Hotline +44 1293 524245

www.aelcrystals.co.uk
sales@aelcrystals.co.uk