

	PART NO.		REVISIONS									
		ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE		
		-	А	RELEASED	Veena	02/8/08	Suresh	02/8/08	G. C	17/8/08		





Specifications:

Current rating Voltage rating Maximum contact resistance Minimum insulation resistance Withstanding voltage Operating temperature rating Material and Finish: Insulator Insulator colour Contact Finish

- : 3.0A ac/dc.
- : 250V ac/dc.


: 20mΩ.

- : 1000MΩ.
- : 600V ac for one minute.
- : -40°C to +105°C.
- : High temperature plastic.
- : Black.
- : Phosphor bronze.
- : Gold plated.

Specification Table

Number of Positions	Α	В	Part Number		
2	2.54	5.08	2226A-02		
Dimensions : Millimetres					

Part Number Explanation:



Number of Positions : 02 = 2 Positions.

completeness, any error in or omission irom it or or any use mate auto it. Users of this data sheet should check for themselves the information and the suitations of the prod- ucts fort. Listing the product of the should be also also also also also also also also	TOLERANCES:	DRAWN BY:	DATE:	DRAWING TITLE:				
	UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	Veena	02/08/08	Single Row Housing & Terminal - 2 Way				
		CHECKED BY:	DATE:	SIZE DWG NO.		ELECTRONIC FILE 2226A-XX-F4(PC0006)_1_DWG		REV
		Suresh	02/08/08	Δ	M10001361			Α
		APPROVED BY:	DATE:					OF 1
		G.Cook	17/08/08	SCALE: NTS	U.O.M.: mm	9	SHEET: 1 O	

http://www.farnell.com

http://www.newark.com

http://www.cpc.co.uk