
- Rugged Triple-Diffused Planar Construction
- 2.5 A Continuous Collector Current
- Operating Characteristics Fully Guaranteed at 100°C
- 850 Volt Blocking Capability
- 50 W at 25°C Case Temperature

TO-220 PACKAGE (TOP VIEW)



Pin 2 is in electrical contact with the mounting base.

MDTRACA

absolute maximum ratings at 25°C case temperature (unless otherwise noted)

RATING	SYMBOL	VALUE	UNIT	
Collector-base voltage (I _E = 0)	V _{CBO}	850	V	
Collector-emitter voltage (V _{BE} = 0)	V _{CES}	850	V	
Collector-emitter voltage (I _B = 0)	V _{CEO}	400	V	
Emitter-base voltage	V _{EBO}	10	V	
Continuous collector current	I _C	2.5	Α	
Peak collector current (see Note 1)	I _{CM}	8	Α	
Continuous device dissipation at (or below) 25°C case temperature	P _{tot}	50	W	
Operating junction temperature range	T _j	-65 to +150	°C	
Storage temperature range	T _{stg}	-65 to +150	°C	

NOTE 1: This value applies for $t_p \le 10$ ms, duty cycle $\le 2\%$.



TIPL770 NPN SILICON POWER TRANSISTOR

MARCH 1984 - REVISED MARCH 1997

electrical characteristics at 25°C case temperature (unless otherwise noted)

PARAMETER		TEST CONDITIONS				MIN	TYP	MAX	UNIT
V _{CEO(sus)}	Collector-emitter sustaining voltage	I _C = 1	100 mA	L = 25 mH	(see Note 2)	400			V
I _{CES}	Collector-emitter cut-off current	V _{CE} = V _{CE} =		$V_{BE} = 0$ $V_{BE} = 0$	T _C = 100°C			5 200	μΑ
I _{CEO}	Collector cut-off current	V _{CE} =	400 V	I _B = 0				5	μΑ
I _{EBO}	Emitter cut-off current	V _{EB} =	10 V	I _C = 0				1	mA
h _{FE}	Forward current transfer ratio	V _{CE} =	5 V	$I_C = 0.5 A$	(see Notes 3 and 4)	20		60	
V _{CE(sat)}	Collector-emitter saturation voltage	I _B = I _B = I _B =	0.2 A 0.5 A 0.5 A	$I_{C} = 1 A$ $I_{C} = 2.5 A$ $I_{C} = 2.5 A$	(see Notes 3 and 4) $T_C = 100^{\circ}C$			1.0 2.5 5.0	V
V _{BE(sat)}	Base-emitter saturation voltage	I _B = I _B = I _B =	0.2 A 0.5 A 0.5 A	$I_{C} = 1 A$ $I_{C} = 2.5 A$ $I_{C} = 2.5 A$	(see Notes 3 and 4) $T_C = 100^{\circ}C$			1.0 1.2 1.3	V
f _t	Current gain bandwidth product	V _{CE} =	10 V	I _C = 0.5 A	f = 1 MHz		12		MHz
C _{ob}	Output capacitance	V _{CB} =	20 V	I _E = 0	f = 0.1 MHz		55		pF

NOTES: 2. Inductive loop switching measurement.

- 3. These parameters must be measured using pulse techniques, t_p = 300 μ s, duty cycle \leq 2%.
- 4. These parameters must be measured using voltage-sensing contacts, separate from the current carrying contacts.

thermal characteristics

PARAMETER			MAX	UNIT
R _{0JC} Junction to case thermal resistance			2.5	°C/W

inductive-load-switching characteristics at 25°C case temperature (unless otherwise noted)

	PARAMETER		TEST CONDITION	is †	MIN	TYP	MAX	UNIT	
t _{sv}	Voltage storage time	I _C = 2.5 A V _{BE(off)} = -5 V					2	μs	
t _{rv}	Voltage rise time						200	ns	
t _{fi}	Current fall time		$I_{B(on)} = 0.5 A$	(see Figures 1 and 2)			200	ns	
t _{ti}	Current tail time						50	ns	
t _{xo}	Cross over time						300	ns	
t _{sv}	Voltage storage time	I _C = 2.5 A V _{BE(off)} = -5 V					2.5	μs	
t _{rv}	Voltage rise time		Ι – 0.5 Δ				400	ns	
t _{fi}	Current fall time		1 _C = 2.5 A	$I_{B(on)} = 0.5 A$ $T_{C} = 100^{\circ}C$	(see Figures 1 and 2)			250	ns
t _{ti}	Current tail time		1C = 100 C				50	ns	
t _{xo}	Cross over time						500	ns	

[†] Voltage and current values shown are nominal; exact values vary slightly with transistor parameters.

PRODUCT INFORMATION

PARAMETER MEASUREMENT INFORMATION





Figure 1. Inductive-Load Switching Test Circuit



NOTES: A. Waveforms are monitored on an oscilloscope with the following characteristics: $t_r < 15$ ns, $R_{in} > 10 \Omega$, $C_{in} < 11.5$ pF. B. Resistors must be noninductive types.

Figure 2. Inductive-Load Switching Waveforms



TYPICAL CHARACTERISTICS

TYPICAL DC CURRENT GAIN VS COLLECTOR CURRENT TCP770AD TC = 125°C T_C = 25°C T_C = -65°C T_C = -65°C T_C = -65°C

COLLECTOR-EMITTER SATURATION VOLTAGE






Figure 3.



BASE-EMITTER SATURATION VOLTAGE



PRODUCT INFORMATION

MAXIMUM SAFE OPERATING REGIONS





Figure 7.

MECHANICAL DATA

TO-220

3-pin plastic flange-mount package

This single-in-line package consists of a circuit mounted on a lead frame and encapsulated within a plastic compound. The compound will withstand soldering temperature with no deformation, and circuit performance characteristics will remain stable when operated in high humidity conditions. Leads require no additional cleaning or processing when used in soldered assembly.



NOTES: A. The centre pin is in electrical contact with the mounting tab.

B. Mounting tab corner profile according to package version.

C. Typical fixing hole centre stand off height according to package version. Version 1, 18.0 mm. Version 2, 17.6 mm. **MDXXBE**

PRODUCT INFORMATION

MARCH 1984 - REVISED MARCH 1997

IMPORTANT NOTICE

Power Innovations Limited (PI) reserves the right to make changes to its products or to discontinue any semiconductor product or service without notice, and advises its customers to verify, before placing orders, that the information being relied on is current.

PI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with PI's standard warranty. Testing and other quality control techniques are utilized to the extent PI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except as mandated by government requirements.

PI accepts no liability for applications assistance, customer product design, software performance, or infringement of patents or services described herein. Nor is any license, either express or implied, granted under any patent right, copyright, design right, or other intellectual property right of PI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used.

PI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, INTENDED, AUTHORIZED, OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT APPLICATIONS, DEVICES OR SYSTEMS.

Copyright © 1997, Power Innovations Limited

