




WISHER is Special & High Quality.

Datasheet

(USA PATENT NO.:4,606,725 & D.299,253)

Breadboard Type: WB-601J



Material: high class POM plastic steel, Dimension: 115 x 70 x 8.2mm
Distribution strips: 2, Distribution holes: 600, Terminal strips: 1,
Terminal holes: +30(6 sections) or -35(All through), Aluminum plate thick: 0.4
With paper box or skin packing.

Features of WISHBOARD WBU-5XX series:

1. High-class acetal material allows insertion hole to withstand wear and tear without easily deforming, also ideal for high frequency and low static.
2. Horizontal assembly corresponds to the operation flow design of the PC boards for handy operation.
3. The power distribution strip provides 4 sections of positive voltage terminals handy for using different voltage at the same time, also 45 connected tie points for negative circuit..
4. Exquisitely printed coordinates for easy recognition and calculation.
5. Easy-on-the-eyes color for longer operation without eye fatigue.
6. Durable base stand aluminum nameplate means no static interference.
7. The dovetail protrusions and recesses designed to connect two adjacent boards tightly together (i.e.perfect size distance from one board to another) and forming a V-shaped cross-sectional groove which allows DIP IC pins inserting across two parts and to increase the rate of utilization.
8. Insertion Range: 20-29AWG(ϕ 0.3- ϕ 0.8mm) wire all dip size components acceptable.(special design over 10,000 insertion cycles.)

WISHER ENTER ENTERPRISE CO., LTD.

Office: 4F-2, 333, FU-HSING N, RD., TAIPEI, TAIWAN, R.O.C.

Tel: 886-2-27191369 Fax.: 886-2-2-7191366

WEB.: www.wishmaker.com.tw