




profiline

POLYSTYRENE CASES



Twist drill sets in polystyrene case



No. 258 214 RO



No. 258 214 FRO



No. 215 214 RO



No. 250 214 TRO

Description	Article no. HSS-G	Article no. HSS-G Co 5	Article no. HSS-G TiN	Article no. HSS-G TiAIN
19-piece set of twist drills DIN 338 TL 3000 ground, with split point Ø 1,0 mm up to 10,0 mm in increments of 0,5 mm	258 214 RO	229 214 RO	258 214 TRO	258 214 FRO
25-piece set of twist drills DIN 338 TL 3000 ground, with split point Ø 1,0 mm up to 13,0 mm in increments of 0,5 mm	258 215 RO	229 215 RO	258 215 TRO	258 215 FRO

Description	Article no. HSS-R	Article no. HSS-G	Article no. HSS-G Co 5	Article no. HSS-G TiN
19-piece set of twist drills DIN 338 type N Ø 1,0 mm up to 10,0 mm in increments of 0,5 mm	205 212 RO	214 214 RO	215 214 RO	250 214 TRO
25-piece set of twist drills DIN 338 type N Ø 1,0 mm up to 13,0 mm in increments of 0,5 mm	205 213 RO	214 215 RO	215 215 RO	250 215 TRO


Tube and sheet drill sets in polystyrene case

Description	Article no.
4-piece set of tube and sheet drills HSS sizes 1, 2, 3 and 1 cutting paste 30 g	101 020 RO
4-piece set of tube and sheet drills HSS Co 5 sizes 1, 2, 3 and 1 cutting paste 30 g	101 020 ERO
4-piece set of tube and sheet drills HSS-TiN sizes 1, 2, 3 and 1 cutting paste 30 g	101 020 TRO



Step drill sets in polystyrene case

Description	Article no.
3-piece set of step drills HSS spiral fluted, sizes 0/9, 1, 2	101 026 RO
3-piece set of step drills HSS Co 5 spiral fluted, sizes 0/9, 1, 2	101 026 ERO
3-piece set of step drills HSS-TiN spiral fluted, sizes 0/9, 1, 2	101 026 TRO
3-piece set of step drills HSS TiAIN spiral fluted, sizes 0/9, 1, 2	101 026 FRO



Taper and deburring countersinker sets in polystyrene case



No. 102 152 TRO



No. 102 152 HMRO



No. 102 312 TRO



No. 102 452 RO

Description	Article no. HSS	Article no. HSS Co 5	Article no. HSS-TiN	Article no. HSS-TiAIN	Article no. Carbide K 20
6-piece set of taper and deburring countersinkers DIN 335 type C 90° Ø 6,3 - 8,3 - 10,4 - 12,4 - 16,5 (shank-Ø 10,0 mm) - 20,5 mm	102 152 RO	102 152 ERO	102 152 TRO	102 152 FRO	102 152 HMRO
8-piece set of taper and deburring countersinkers bits Ø 6,3 - 8,3 - 10,4 - 12,4 - 16,5 - 20,5 mm + 1 universal handle + 1 cutting paste 30 g	102 319 RO	—	102 319 TRO	—	—
4-piece set of slotted taper and deburring countersinkers 90° nominal Ø mm: 2/5 - 5/10 - 10/15 - 15/20	102 312 RO	102 312 ERO	102 312 TRO	—	—
6-piece set of flat countersinkers for through holes, fine grade, for threads: M 3 - M 4 - M 5 - M 6 - M 8 - M 10	102 450 RO	—	102 450 TRO	—	—
6-piece set of flat countersinkers for through holes, medium grade, for threads: M 3 - M 4 - M 5 - M 6 - M 8 - M 10	102 451 RO	—	102 451 TRO	—	—
6-piece set of flat countersinkers for core holes, for threads: M 3 - M 4 - M 5 - M 6 - M 8 - M 10	102 452 RO	—	102 452 TRO	—	—

Tap sets in polystyrene case



No. 245 001 RO



No. 245 063 RO



No. 245 066 RO



No. 245 051 RO

Description	Article no. HSS	Article no. HSS Co 5	Article no. HSS TiN	Article no. HSS TiAIN
21-piece set of hand taps M DIN 352 one three-piece set each of M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12	245 001 RO	245 001 ERO	—	—
28-piece set of hand taps M DIN 352 one three-piece set each of M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12 + 7 twist drills DIN 338 Type N HSS, ground Ø 2,5 - 3,3 - 4,2 - 5,0 - 6,8 - 8,5 - 10,2 mm	245 003 RO	245 003 ERO	—	—
15-piece set of single-cut taps 7 single-cut taps M ≈ DIN 352 M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12 + 7 twist drills DIN 338 Type N HSS, ground Ø 2,5 - 3,3 - 4,2 - 5,0 - 6,8 - 8,5 - 10,2 mm + 1 tap wrench, size 1½ DIN 1814	245 004 RO	—	—	—

Machine tap sets in polystyrene case

Description	Article no. HSS	Article no. HSS Co 5	Article no. HSS TiN	Article no. HSS TiAIN
7-piece set of machine taps M DIN 371 / 376 type B with progressive tap M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12	245 057 RO	245 061 RO	245 063 RO	245 065 RO
7-piece set of machine taps M DIN 371 / 376 type C / 35° right-hand spiral flutes M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12	245 058 RO	245 062 RO	245 064 RO	245 066 RO
14-piece set of machine taps 7 machine taps M DIN 371 / 376 type B with progressive tap M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12 + 7 twist drills DIN 338 Typ N Ø 2,5 - 3,3 - 4,2 - 5,0 - 6,8 - 8,5 - 10,2 mm	245 050 RO	245 051 RO	—	—
14-piece set of machine taps 7 machine taps M DIN 371 / 376 type C / 35° right-hand spiral flutes M 3 - M 4 - M 5 - M 6 - M 8 - M 10 - M 12 + 7 twist drills DIN 338 Typ N Ø 2,5 - 3,3 - 4,2 - 5,0 - 6,8 - 8,5 - 10,2 mm	—	245 052 RO	—	—

Tungsten carbide rotary burr sets in polystyrene case

Description	Article no.
10-piece set of tungsten carbide rotary burrs TC 2 x shape A, cylinder (ZYA) without end tothing Ø D1 10,0 / 12,0 mm 2 x shape C, oval (WRC) Ø D1 10,0 / 12,0 mm 2 x shape G, tree (SPG) Ø D1 10,0 / 12,0 mm 2 x shape F, ball nose tree (RBF) Ø D1 10,0 / 12,0 mm 1 x shape M, cone (SKM) Ø D1 12,0 mm 1 x shape D, ball type (KUD) Ø D1 12,0 mm	116 003 RO
10-piece set of tungsten carbide rotary burrs TiCN 2 x shape A, cylinder (ZYA) without end tothing Ø D1 10,0 / 12,0 mm 2 x shape C, oval (WRC) Ø D1 10,0 / 12,0 mm 2 x shape G, tree (SPG) Ø D1 10,0 / 12,0 mm 2 x shape F, ball nose tree (RBF) Ø D1 10,0 / 12,0 mm 1 x shape M, cone (SKM) Ø D1 12,0 mm 1 x shape D, ball type (KUD) Ø D1 12,0 mm	116 003 TCRO
10-piece set of tungsten carbide rotary burrs ALU 2 x shape A, cylinder (ZYA) with end tothing Ø D1 6,0 / 12,0 mm 2 x shape C, oval (WRC) Ø D1 6,0 / 12,0 mm 2 x shape G, tree (SPG) Ø D1 6,0 / 12,0 mm 2 x shape F, ball nose tree (RBF) Ø D1 6,0 / 12,0 mm 2 x shape D, ball type (KUD) Ø D1 6,0 / 12,0 mm	116 103 RO



SDS-plus hammer drills set in polystyrene case

Description	Article no.
7-piece set of SDS-plus hammer drills Ø 5,0 - 6,0 - 8,0 x 110,0 mm and Ø 6,0 - 8,0 - 10,0 - 12,0 x 160,0 mm	205 246 RO




Concrete drill set with carbide cutting edge and straight shank ISO 5468 - DIN 8039 in polystyrene case

Description	Article no.
7-piece set of concrete drills with carbide cutting edge and straight shank Ø 4,0 x 75,0 mm - 5,0 x 85,0 mm - 6,0 x 100,0 mm - 6,0 x 100,0 mm - 8,0 x 120,0 mm - 10,0 x 120,0 mm - 12,0 x 150,0 mm	205 255 RO

No. 205 255 RO

Percussion drill set with carbide cutting edge and straight shank ISO 5468 - DIN 8039 in polystyrene case

Description	Article no.
7-piece set of percussion drills with carbide cutting edge and straight shank Ø 4,0 x 75,0 mm - 5,0 x 85,0 mm - 6,0 x 100,0 mm - 6,0 x 100,0 mm - 8,0 x 120,0 mm - 10,0 x 120,0 mm - 12,0 x 150,0 mm	205 256 RO



No. 205 256 RO

