



This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, without the prior written consent of Amphenol Corporation without its prior consent. All rights are reserved. It is to be used only for the information in this document.




REVISIONS			
SN	EDN	DESCRIPTION	DATE
B			24/01/07

D-SUB TECHNICAL DATA

SHELL : Steel 2.5um(100u") min tin over 1.25um(50u") min nickel
BODY : Glass filled thermoplastic.
Flame retardant to UL94 V-0 Color Black
CONTACTS : brass.
0.1um(4u") min gold over 1.25um(50u") min nickel
ELECTRICAL : Voltage rating : 300 V RMS at 50 Hz
Current rating 7.5A.
Insulation resistance >5000 M Ohms
Contact resistance 8.5 mOhms max.
CLIMATIC : Temperature range -55 °C up to 125°C
Damp heat 21 days(40 °C-95% HR)
MECHANICAL : mating force 0.34kg Max
unmating force 0.021kg min
MARKING : Amphenol-...(Series No.)
Commercial reference
Manufacturing date

PRODUCT CODE

L 717D B 25 P



UNLESS OTHERWISE SPECIFIED			
TOLERANCES		APPROVAL	DATE
U.S.	METRIC	DRAWN	Wen-Jeng/01/07
.X +/-	0.50	CHECKED	Wen-Jeng/01/07
.XX +/-	0.30		
.XXX +/-	0.20		
FRACTIONS +/-			
ANGLES +/-	2°		
FOR MATERIALS AND FINISHES			
REMOVE SHARP EDGES			
DIMENSIONS		ANGLE OF PROJECTION	
1st ANGLE	3RD ANGLE		
METRIC	MM		
DRAWING FILE :			
Screw-machined contacts connector, D series			
SIZE		REV.	
A4	C L717DB25P		B
SCALE		SHEET	
NONE		1 OF 1	

Amphenol