

# Phase-sequence Phase-loss Relay K8AB-PH

#### Ideal for phase sequence and phase loss monitoring for industrial facilities and equipment.

- Simultaneously monitor phase sequence and phase loss for three-phase 3-wire power supplies.
- One SPDT output relay, 6 A at 250 VAC (resistive load).
- Relay warning status easily monitoring using LED indicator.
- Easy wiring with ferrules 2 × 2.5 mm<sup>2</sup> solid or 2 × 1.5 mm<sup>2</sup> standard ferrules.
- CE mark compliance certified by third party. UL certification pending.



CE

## **Model Number Structure**

## **■** Model Number Legend

K8AB-□□

1 23

1. Basic Model

K8AB: Measuring and Monitoring Relays

2. Functions

PH: Phase-sequence Phase-loss Relay

3. Rated Input Voltage

1: 200 to 500 VAC

# **Ordering Information**

### **■** List of Models

Phase-sequence Phase-loss Relay	Rated input voltage (See note.)	Model
	200 to 500 VAC	K8AB-PH1

Note: The power supply is shared with the rated input voltage.

# **Ratings and Specifications**

# **■** Ratings

Rated input voltage	Non-isolated	200 to 500 VAC (15 VA)
Phase sequence, phase	se loss operating time	0.1 s max. (value when rated operating voltage changes quickly from 0% to 100%) (Relays are normally ON and turn OFF for phase sequence or loss phase errors.)
Resetting method		Automatic reset
Input frequency		45 to 65 Hz
Input impedance		100 k $\Omega$ min.
Indicators		Power (PWR): Green LED, Relay output (RY): Yellow LED
Output relays One SPDT relay (6 A at 250 VAC, resistive load)		One SPDT relay (6 A at 250 VAC, resistive load)


# **■** Specifications

Ambient operating ten	nperature	–20 to 60°C (with no condensation or icing)	
Storage temperature		-40 to 70°C (with no condensation or icing)	
Ambient operating humidity		25% to 85%	
Storage humidity		25% to 85%	
Altitude		2,000 m max.	
Voltage fluctuation range		85% to 110% of rated input voltage	
Input frequency		50/60 Hz ±5 Hz (AC power supply)	
Output relays	Resistive load	6 A at 250 VAC (cos φ = 1) 6 A at 30 VDC (L/R = 0 ms)	
	Inductive load	1 A at 250 VAC (cos φ = 0.4) 1 A at 30 VDC (L/R = 7 ms)	
	Minimum load	10 mA at 5 VDC	
	Maximum contact voltage	250 VAC	
	Maximum contact current	6 A AC	
	Maximum switching capacity	1,500 VA	
	Mechanical life	10,000,000 operations	
	Electrical life	Make: 50,000 times, Break: 30,000 times	
Terminal screw tighter	ning torque	1.2 N·m	
Crimp terminals		Two solid wires of $2.5\ mm^2$ , two crimp terminals of $1.5\ mm^2$ with insulation sleeves, can be tightened together	
Insulation resistance		20 M $\Omega$ (at 500 V) between charged terminals and exposed uncharged parts 20 M $\Omega$ (at 500 V) between any charged terminals (i.e., between input, output, and power supply terminals)	
Degree of protection		Terminal section: IP20, Rear case: IP40	
Case color		Munsell 5Y8/1 (ivory)	
Case material		ABS resin (self-extinguishing resin) UL94-V0	
Weight		200 g	
Mounting		Mounted to DIN Track or via M4 screws	
Dimensions		22.5 (W) x 90 (H) x 100 (D) mm	
Installation environme	ent	Overvoltage Category III, Pollution Degree 2	
Application standards	i	EN60255-5/-6	
Safety standards		EN60664-1	
ЕМС		EMI: EN61326 Industrial applications Electromagnetic interference wave     CISPR11 Group 1, Class A: CISPR16-1/-2 Terminal interference wave voltage     CISPR11 Group 1, Class A: CISPR16-1/-2 EMS: EN61326 Industrial applications Electrostatic discharge EN61000-4-2: 8 kV (in air) Radiating radio-frequency electromagnetic field EN61000-4-3:     10 V/m 1 kHz sine wave amplitude modulation (80 MHz to 1 GHz) Burst EN61000-4-4: 1 kV (I/O signal line), 2 kV (power line) Surge EN61000-4-5: 1 kV with line (power line),     2 kV with ground (power line) Conducted RF EN61000-4-6: 3 V (0.15 to 80 MHz) Power frequency magnetic field immunity EN61000-4-8: 30 A/m Voltage dip/short interruptions EN61000-4-11: 0.5 cycle, 0.180° each, polarity 100% (rated voltage)	


# **Connections**

# **■** Wiring Diagram

### **Phase Sequence and Phase Loss Operation Diagram**




- Note: 1. Motor load phase loss cannot be detected. To detect motor load phase loss, use the K8AB-PM or K8AB-PA.
  - 2. The K8AB-PH output relay is normally operative.



# **Nomenclature**

#### **■** Front



### **Indicators**


Item	Meaning
Power indicator (PWR: Green)	Lit when power is being supplied.
Relay status indicator (RY: Yellow)	Lit when relay is operating (normally lit).

# **Dimensions**

#### K8AB-PH







# **Safety Precautions**

#### ■ Precautions for Safe Use

Make sure to follow the instructions below to ensure safety.

- 1. Do not use or keep this product in the following environments.
  - Outdoors, or places subject to direct sunlight or wearing weather.
  - Places where dust, iron powder, or corrosive gases (in particular, sulfuric or ammonia gas) exist.
  - Places subject to static electricity or inductive noise.
  - Places where water or oil come in contact with the product.
- 2. Make sure to install this product in the correct direction.
- 3. There is a remote risk of electric shock. Do not touch terminals while electricity is being supplied.
- 4. Make sure to thoroughly understand all instructions in the Instructions Manual before handling this product.
- 5. Make sure to confirm terminal makings and polarity for correct
- 6. Tighten terminal screws firmly using the following torque. Recommended torque: 0.54 N·m
- 7. Operating ambient temperature and humidity for this product must be within the indicated rating when using this product.
- There is a remote risk of explosion. Do not use this product where flammable or explosive gas exists.
- 9. Make sure that no weight rests on the product after installation.
- 10. To enable an operator to turn off this product easily, install switches or circuit breakers that conform to relevant requirements of IEC60947-1 and IEC60947-3, and label them appropriately.

#### ■ Precautions for Correct Use

#### For Proper Use

- 1. Do not use the product in the following locations.
  - · Places subject to radiant heat from heat generating devices.
  - · Places subject to vibrations or physical shocks.
- 2. Make sure to use setting values appropriate for the controlled object. Failure to do so can cause unintended operation, and may result in accident or corruption of the product.
- 3. Do not use thinner or similar solvent for cleaning. Use commercial alcohol.
- 4. When discarding, properly dispose of the product as industrial
- 5. Only use this product within a board whose structure allows no possibility for fire to escape.

#### **About Installation**

- 1. When wiring, use only recommended crimp terminals.
- 2. Do not block areas around the product for proper dissipation of heat. (If you do not secure space for heat dissipation, life cycle of the product will be compromised.)
- 3. To avoid electrical shocks, make sure that power is not supplied to the product while wiring.
- 4. To avoid electrical shocks, make sure that power is not supplied to the product when performing DIP switch settings.

#### Noise Countermeasures

- 1. Do not install the product near devices generating strong high frequency waves or surges.
- 2. When using a noise filter, check the voltage and current and install it as close to the product as possible
- 3. In order to prevent inductive noise, wire the lines connected to the product separately from power lines carrying high voltages or currents. Do not wire in parallel with or on the same cable as power lines.
  - Other measures for reducing noise include running lines along separate ducts and using shield lines.

### To avoid faulty operations, malfunctions, or failure, observe the following operating instructions.

- 1. When turning on the power, make sure to realize rated voltage within 1 second from the time of first supply of electricity.
- 2. Make sure to use power supply for operations, inputs, and transformer with the appropriate capacity and rated burden.
- 3. Maintenance and handling of this product may only be performed by qualified personnel.
- 4. Distortion ratio of input wave forms must be 30% or less. Use of this product with circuits that have large distortion in wave forms may result in unwanted operations.
- 5. Using this product for thyristor controls or inverters will result in
- 6. When setting the volume, adjust the control from the minimum side to the maximum side



# Warranty and Application Considerations

#### Read and Understand this Catalog

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

#### **Warranty and Limitations of Liability**

#### WARRANTY

OMRON's exclusive warranty is that the products are free from defects in materials and workmanship for a period of one year (or other period if specified) from date of sale by OMRON.

OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, REGARDING NON-INFRINGEMENT, MERCHANTABILITY, OR FITNESS FOR PARTICULAR PURPOSE OF THE PRODUCTS. ANY BUYER OR USER ACKNOWLEDGES THAT THE BUYER OR USER ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE. OMRON DISCLAIMS ALL OTHER WARRANTIES, EXPRESS OR IMPLIED.

#### LIMITATIONS OF LIABILITY

OMRON SHALL NOT BE RESPONSIBLE FOR SPECIAL, INDIRECT, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS, OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED ON CONTRACT, WARRANTY, NEGLIGENCE, OR STRICT LIABILITY.

In no event shall the responsibility of OMRON for any act exceed the individual price of the product on which liability is asserted. IN NO EVENT SHALL OMRON BE RESPONSIBLE FOR WARRANTY, REPAIR, OR OTHER CLAIMS REGARDING THE PRODUCTS UNLESS OMRON'S ANALYSIS CONFIRMS THAT THE PRODUCTS WERE PROPERLY HANDLED, STORED, INSTALLED, AND MAINTAINED AND NOT SUBJECT TO CONTAMINATION, ABUSE, MISUSE, OR INAPPROPRIATE MODIFICATION OR REPAIR.

#### **Application Considerations**

#### **SUITABILITY FOR USE**

OMRON shall not be responsible for conformity with any standards, codes, or regulations that apply to the combination of products in the customer's application or use of the products.

Take all necessary steps to determine the suitability of the product for the systems, machines, and equipment with which it will be used. Know and observe all prohibitions of use applicable to this product.

NEVER USE THE PRODUCTS FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCTS ARE PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

#### **Disclaimers**

#### **PERFORMANCE DATA**

Performance data given in this catalog is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of OMRON's test conditions, and the users must correlate it to actual application requirements. Actual performance is subject to the OMRON *Warranty and Limitations of Liability.* 

#### **CHANGE IN SPECIFICATIONS**

Product specifications and accessories may be changed at any time based on improvements and other reasons. Consult with your OMRON representative at any time to confirm actual specifications of purchased product.

#### **DIMENSIONS AND WEIGHTS**

Dimensions and weights are nominal and are not to be used for manufacturing purposes, even when tolerances are shown.

#### ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

Cat. No. N145-E1-01 In the interest of product improvement, specifications are subject to change without notice.

#### **OMRON Corporation**

**Industrial Automation Company** 

Industrial Devices and Components Division H.Q. Industrial Control Components Department

Shiokoji Horikawa, Shimogyo-ku, Kyoto, 600-8530 Japan

Tel: (81)75-344-7119/Fax: (81)75-344-7149