


PCB Relay

G₂E

Miniature, Low-cost, Single-pole PCB Relay

- Miniature: 15.5 x 10.5 x 11.5 mm (L x W x H).
- Low power consumption: 200 mW.
- Bifurcated crossbar contacts.
- Gold-clad contacts.
- Fully sealed type available.
- Ideal for telecommunications equipment and security systems.





Ordering Information

Contact		General-purpose	High-sensitivity	
		Fully sealed	Fully sealed	
SPDT	Single crossbar	G2E-184P-M-US	G2E-184P-H-M-US	
	Bifurcated crossbar	G2E-134P-M-US	G2E-134P-H-M-US	

Note: When ordering, add the rated coil voltage to the model number. Example: G2E-184P-M-US 12 VDC

-- Rated coil voltage

Model Number Legend

VDC 8 5 6

- 1. Contact Form
 - 1: SPDT
- 2. Contact Type
 - 3: Bifurcated crossbar
 - 8: Single crossbar
- 3. Enclosure Ratings
 - 4: Fully sealed
- 4. Terminals
 - Straight PCB
- 5. Power Consumption

None: General-purpose (450 mW) High-sensitivity (200 mW)

- 6. Classification
 - M: General-purpose
- 7. Approved Standards US: UL, CSA certified
- 8. Rated Coil Voltage 1.5, 3, 5, 6, 9, 12, 24 VDC

Specifications

■ Coil Ratings

General-purpose Relays

Rated voltage		1.5 VDC	3 VDC	5 VDC	6 VDC	9 VDC	12 VDC	24 VDC	
Rated current		300 mA	150 mA	89.3 mA	75 mA	50 mA	37.5 mA	18.8 mA	
Coil resistance		5 Ω	20 Ω	56 Ω	80 Ω	180 Ω	320 Ω	1,280 Ω	
Coil inductance	Armature OFF	0.005	0.017	0.044	0.067	0.137	0.229	0.94	
(H) (ref. value)	Armature ON	0.009	0.034	0.091	0.136	0.297	0.496	2.1	
Must operate voltage		70% max. of rated voltage							
Must release voltage 10% min.			0% min. of rated voltage						
Max. voltage 120% of			20% of rated voltage at 23°C, 110% at °60C						
Power consumption Ap		Approx. 450 i	Approx. 450 mW						

High-sensitivity Relays

Rated voltage		1.5 VDC	3 VDC	5 VDC	6 VDC	9 VDC	12 VDC	24 VDC	
Rated current		125 mA	66.7 mA	41.7 mA	33.3 mA	22.5 mA	17.1 mA	8.6 mA	
Coil resistance		12 Ω	45 Ω	120 Ω	180 Ω	400 Ω	700 Ω	2,800 Ω	
Coil inductance	Armature OFF	0.005	0.022	0.055	0.083	0.165	0.228	1.465	
(H) (ref. value)	Armature ON	0.009	0.035	0.092	0.129	0.303	0.504	2.287	
Must operate voltage		80% max. of rated voltage							
Must release voltage		10% min. of rated voltage							
Max. voltage		140% of rated voltage at 23°C, 130% at 65°C							
Power consumption		Approx. 200 mW							

Note: 1. The rated current and coil resistance are measured at a coil temperature of 23°C with a tolerance of ±10%.

■ Contact Ratings

Item	Single crossbar	Bifurcated crossbar		
Load	Resistive load (cosφ = 1)	Resistive load (cos = 1)		
Rated load	0.5 A at 110 VAC; 1 A at 24 VDC	0.5 A at 110 VAC; 1 A at 24 VDC		
Contact material	AgPd (Au-clad)			
Rated carry current	2 A			
Max. switching voltage	125 VAC, 60 VDC			
Max. switching current	1 A			
Max. switching power	120 VA, 30 W	120 VA, 30 W		
Failure rate (reference value)	1 mA at 5 VDC	0.1 mA at 0.1 VDC		

Note P level: $\lambda_{60} = 0.1 \times 10^{-6}$ /operation

^{2.} Operating characteristics are measured at a coil temperature of 23°C.

■ Characteristics

Contact resistance	50 mΩ max.			
Operate time	General-purpose type: 5 ms max. (mean value: approx. 2.5 ms) High-sensitivity type: 7 ms max. (mean value: approx. 3.5 ms)			
Release time	3 ms max. (mean value: approx. 0.8 ms)			
Max. operating frequency	Mechanical: 18,000 operations/hr Electrical: 1,800 operations/hr (under rated load)			
Insulation resistance	100 $M\Omega$ min. (at 500 VDC)			
Dielectric withstand voltage	500 VAC, 50/60 Hz for 1 min between coil and contacts 500 VAC, 50/60 Hz for 1 min between contacts of same polarity			
Vibration resistance	Destruction: 10 to 55 to 10 Hz, 1.65-mm single amplitude (3.3-mm double amplitude) Malfunction: 10 to 55 to 10 Hz, 1.65-mm single amplitude (3.3-mm double amplitude)			
Shock resistance	Destruction: 1,000 m/s ² (approx. 100G) Malfunction: 200 m/s ² (approx. 20G)			
Endurance	Mechanical: 10,000,000 operations min. (at 18,000 operations/hr) Electrical: DC: 500,000 operations min. (1 A at 24 VDC resistive load) AC: 200,000 operations min. (0.5 A at 110 VAC resistive load) (at 1,800 operations/hr)			
Ambient temperature	Operating: -25°C to 60°C (with no icing) (high-sensitivity type: -25°C to 65°C)			
Ambient humidity	Operating: 5% to 85%			
Weight	Approx. 3.7 g			


■ Approved Standards

UL114, UL478, UL1950 (File No. E41515)/CSA C22.2 No.0, No.14 (File No. LR34815-97)


Model	Contact form	Coil ratings	Contact ratings
G2E-184P-M-US G2E-184P-H-M-US G2E-134P-M-US G2E-134P-H-M-US	SPDT	1.5 to 24 VDC	0.5 A, 125 VAC (general use) 1 A, 28 VDC (resistive)

Engineering Data

Maximum Switching Power G2E-184P-M-US




Endurance G2E-184P-M-US



Dimensions

Note: 1. All units are in millimeters unless otherwise indicated.


2. Orientation marks are indicated as follows:



Terminal Arrangement/ Internal Connections (Bottom View)



Mounting Holes (Bottom View)



ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

Cat. No. K006-E1-9D