MOS FET Relays

G3VM-351G

NEW 27

Note: The actual product is marked differently from the image

shown here.

Slim, 2.1-mm High Relay Incorporating a MOS FET Optically Coupled with an Infrared LED in a Miniature, Flat SOP Package

- Upgraded G3VM-S2 Series.
- Continuous load current of 110 mA.
- Dielectric strength of 1,500 Vrms between I/O.

■ Application Examples

- Broadband systems
- Measurement devices
- Data loggers
- Amusement machines

■ List of Models

Contact form	Terminals	Load voltage (peak value)	Model	Number per stick	Number per tape
SPST-NO	Surface-mounting	350 VAC	G3VM-351G	100	
	terminals		G3VM-351G(TR)		2,500


■ Dimensions

Note: All units are in millimeters unless otherwise indicated.

G3VM-351G




Note: The actual product is marked differently from the image shown here.



■ Terminal Arrangement/Internal Connections (Top View)

G3VM-351G



■ Actual Mounting Pad Dimensions (Recommended Value, Top View)

G3VM-351G

Note:


■ Absolute Maximum Ratings (Ta = 25°C)

Item		Symbol	Rating Unit		Measurement Conditions	
Input	Input LED forward current		50	mA		
	Repetitive peak LED forward current	I _{FP}	1	Α	100 μs pulses, 100 pps	
	LED forward current reduction rate	Δ I _F /°C	-0.5	mA/°C	Ta ≥ 25°C	
	LED reverse voltage	V_R	5	V		
	Connection temperature	Tj	125	°C		
Output	Output dielectric strength	V _{OFF}	350	V		
	Continuous load current	I _O	110	mA		
	ON current reduction rate	Δ I _{ON} /°C	-1.1	mA/°C	Ta ≥ 25°C	
	Connection temperature	Tj	125	°C		
Dielectr output (Dielectric strength between input and output (See note 1.)		1,500	Vrms	AC for 1 min	
Operating temperature		Ta	-40 to +85	°C	With no icing or condensation	
Storage temperature		T _{stg}	-55 to +125	°C	With no icing or condensation	
Soldering temperature (10 s)			260	°C	10 s	

1. The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on the light-receiving side.

■ Electrical Characteristics (Ta = 25°C)

	ltem	Symbol	Mini- mum	Typical	Maxi- mum	Unit	Measurement conditions	
Input	LED forward voltage	V_{F}	1.0	1.15	1.3	٧	I _F = 10 mA	
	Reverse current	I_R			10	μА	V _R = 5 V	
	Capacity between terminals	C _T		30		pF	V = 0, f = 1 MHz	
	Trigger LED forward current	I _{FT}		1	3	mA	I _O = 100 mA	
Output	Maximum resistance with output ON	R _{ON}		25	35	Ω	I _F = 5 mA, I _O = 110 mA, t < 1 s	
				35	50	Ω	I _F = 5 mA, I _O = 110 mA	
	Current leakage when the relay is open	I _{LEAK}			1.0	μА	V _{OFF} = 350 V	
Capacity	Capacity between I/O terminals			0.8		pF	f = 1 MHz, Vs = 0 V	
Insulation resistance		R _{I-O}	1,000			ΜΩ	V_{I-O} = 500 VDC, RoH \leq 60%	
Turn-ON time		tON		0.3	1.0	ms	$I_F = 5 \text{ mA}, R_L = 200 \Omega, V_{DD} = 20 \text{ V (See note 2.)}$	
Turn-OFF time		tOFF		0.1	1.0	ms		




■ Recommended Operating Conditions

Use the G3VM under the following conditions so that the Relay will operate properly.

Item	Symbol	Minimum	Typical	Maximum	Unit
Output dielectric strength	V_{DD}			280	V
Operating LED forward current	I _F	5	7.5	25	mA
Continuous load current	Io			100	mA
Operating temperature	Ta	- 20		65	°C

■Engineering Data

Load Current vs. Ambient Temperature G3VM-351G



■ Safety Precautions

Refer to page 6 for precautions common to all G3VM models.