


BBH Transformers

146194. → 146-199

portable isolation

240 / 110V

Safetran 2400 and 3500



Primary: 240V **Secondary:** 110V Centre tapped


Two new portable isolation transformers constructed to **BS3535** and complying with the requirements of Health and Safety at Work. Tool ratings of either 2400VA or 3500VA are available. Fitted with a 2 metre length of cable to the 240V primary, but with two separate industrial 16A output sockets manufactured to **BS4343/CEE17**.

Each transformer is fitted with an earth screen between primary and secondary windings. A resettable thermal cut-out is provided. Supplied complete with carrying strap.

Continuous Rating	Tool Rating	Weight	Dimensions		
			H	W	D
1200VA	2400VA	13.5kg	155	175	151
1750VA	3500VA	14.5kg	155	175	151

Continuous Rating	Order Code	
	FEC	BBH
1200VA	177-162	Z2763
1750VA	177-163	Z2779

240 / 110V



Primary: 240V **Secondary:** 110V Centre tapped

A range of robust safety transformers, which are kitemarked to **BS3535** (except Z2340 and Z2338), suitable for 110V portable electric tools.

A 2 metre length of cable is fitted to the 240V input connection and the output is a 16A, 2 pin + earth industrial socket, manufactured to **BS4343/CEE17**. The Z2340 is fitted with two 16A industrial sockets.

The transformer is fitted with an earth screen between primary and secondary windings. The outlet is fused and provides 110V which is only 55V above earth for the tool. Spare fuse supplied.

Continuous Rating	Tool Rating	Weight	Dimensions		
			H	W	D
450VA	900VA	12.7kg	260	192	192 inc handle
800VA	1600VA	17.2kg	260	192	192 exc sockets
1000VA	2000VA	16.0kg	220	167	167 exc sockets
1650VA	3300VA	21.0kg	260	192	192 exc sockets

Continuous Rating	Order Code	
	FEC	BBH
450VA	143-410	Z2121
800VA	143-411	Z2122
1000VA	146-812	Z2338
1650VA	146-194	Z2340