

FM Series

Miniature Toroidal - Single Primary



A high quality range of miniature open style toroidal transformers with flying leads. Featuring a single primary winding tapped at 115 and 230V 50/60Hz, and dual secondary windings. Secondary windings can be connected in series or parallel or used independently.

Features:

- High quality construction.
- Low radiated magnetic field, suitable for sensitive electronics.
- Double insulated primary leads.
- Resin filled centre with M4 clear mounting hole.
- Flexible lead outs can be trimmed to any length without the need of enamel removal.
- Suitable for use in low power equipment.
- Designed, tested and manufactured in accordance with EN60742, EN60065 and EN60950.
- 100% electrical and flash tested.

Specifications

VA	Regulation % typical	Iron Loss Watts	Copper Loss Watts	Temperature rise (°C)	Efficiency % typical	Diameter	Height	Weight (kg)
1.6	21	0.09	0.4	10	76%	42	23	0.13
3.2	20		0.8	16	79%	43	24	0.14
5.0	18	0.11	1.1	18	81%	50		0.17
7.0	19	0.13	1.6	25	80%	51		0.19

Figures given above are maximums for any given VA

Dimensions : Millimetres



FM Series

Miniature Toroidal - Single Primary



Maximum ambient temperature 40°C.

Overall temperature rating Class A (105°C).

Secondary voltage tolerance $\pm 1\%$ at nominal input and full resistive load.

No mounting screw supplied.

All leads 150mm long, stripped and tinned for last 6.0mm.

Note: Under no circumstances should both ends of any fixing bolt be allowed to come simultaneously in contact with metal chassis or framework so that an electrical path is formed through the bolt in the centre of the transformer via the external framework. This would constitute a shorted turn and would cause irreparable damage.

Specification Table

Specification	Load (VA)	Part Number
0-7V, 0-7V @ 0.114A	1.6	MCFM16/07
0-9V, 0-9V @ 0.089A		MCFM16/09
0-12V, 0-12V @ 0.067A		MCFM16/12
0-15V, 0-15V @ 0.053A		MCFM16/15
0-22V, 0-22V @ 0.036A		MCFM16/22
0-7V, 0-7V @ 0.229A	3.2	MCFM32/07
0-9V, 0-9V @ 0.178A		MCFM32/09
0-12V, 0-12V @ 0.133A		MCFM32/12
0-15V, 0-15V @ 0.2107A		MCFM32/15
0-18V, 0-18V @ 0.089A		MCFM32/18
0-7V, 0-7V @ 0.357A	5.0	MCFM50/07
0-9V, 0-9V @ 0.278A		MCFM50/09
0-12V, 0-12V @ 0.208A		MCFM50/12
0-15V, 0-15V @ 0.167A		MCFM50/15
0-18V, 0-18V @ 0.139A		MCFM50/18
0-22V, 0-22V @ 0.114A	MCFM50/22	
0-7V, 0-7V @ 0.5A	7.0	MCFM70/07
0-9V, 0-9V @ 0.389A		MCFM70/09
0-12V, 0-12V @ 0.292A		MCFM70/12
0-15V, 0-15V @ 0.233A		MCFM70/15
0-18V, 0-18V @ 0.194A		MCFM70/18
0-22V, 0-22V @ 0.159A	MCFM70/22	

Notes:

International Sales Offices:



AUSTRALIA - Farnell InOne
Tel No: ++ 61 2 9645 8888
Fax No: ++ 61 2 9644 7898



FINLAND - Farnell InOne
Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



NETHERLANDS - Farnell InOne
Tel No: ++ 31 30 241 7373
Fax No: ++ 31 30 241 7333



SWITZERLAND - Farnell InOne
Tel No: ++ 41 1 204 64 64
Fax No: ++ 41 1 204 64 54



AUSTRIA - Farnell InOne
Tel No: ++ 43 662 2180 680
Fax No: ++ 43 662 2180 670



FRANCE - Farnell InOne
Tel No: ++ 33 474 68 99 99
Fax No: ++ 33 474 68 99 90



NEW ZEALAND - Farnell InOne
Tel No: ++ 64 9 357 0646
Fax No: ++ 64 9 357 0656



UK - Farnell InOne
Tel No: ++ 44 8701 200 200
Fax No: ++ 44 8701 200 201



BELGIUM - Farnell InOne
Tel No: ++ 32 3 475 2810
Fax No: ++ 32 3 227 3648



GERMANY - Farnell InOne
Tel No: ++ 49 89 61 39 39 39
Fax No: ++ 49 89 613 59 01



NORWAY - Farnell InOne
Tel No: ++ 45 44 53 66 66
Fax No: ++ 45 44 53 66 02



UK - BuckHickman InOne
++ 44 8450 510 150
++ 44 8450 510 130



BRAZIL - Farnell-Newark InOne
Tel No: ++ 55 11 4066 9400
Fax No: ++ 55 11 4066 9410



HONG KONG - Farnell-Newark InOne
Tel No: ++ 852 2268 9888
Fax No: ++ 852 2268 9899



PORTUGAL - Farnell InOne
Tel No: ++ 34 93 475 8804
Fax No: ++ 34 93 474 5288



UK - CPC
++ 44 8701 202 530
++ 44 8701 202 531



CHINA - Farnell-Newark InOne
Tel No: ++86 10 6238 5152
Fax No: ++86 10 6238 5022



IRELAND - Farnell InOne
Tel No: ++ 353 1 830 9277
Fax No: ++ 353 1 830 9016



SINGAPORE - Farnell-Newark InOne
Tel No: ++ 65 6788 0200
Fax No: ++ 65 6788 0300



EXPORT - Farnell InOne
Tel No: ++ 44 8701 200 208
Fax No: ++ 44 8701 200 209

For enquiries from all other markets



DENMARK - Farnell InOne
Tel No: ++ 45 44 53 66 44
Fax No: ++ 45 44 53 66 06



ITALY - Farnell InOne
Tel No: ++ 39 02 93 995 200
Fax No: ++ 39 02 93 995 300



SPAIN - Farnell InOne
Tel No: ++ 34 93 475 8805
Fax No: ++ 34 93 474 5107



ESTONIA - Farnell InOne
Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



MALAYSIA - Farnell-Newark InOne
Tel No: ++ 60 3 7873 8000
Fax No: ++ 60 3 7873 7000



SWEDEN - Farnell InOne
Tel No: ++ 46 8 730 50 00
Fax No: ++ 46 8 83 52 62

<http://www.farnellinone.com>

<http://www.buckhickmaninone.com>

<http://www.cpc.co.uk>

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2004.