


NO	DESCRIPTION	DATE
①	MODIFICATION CENTER CONTACT ⑦ BACKGROUND FORMAT UPDATED	01.13.10'



#### 1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-900 MHz  
1.2 NOMINAL IMPEDANCE: 50 OHM

#### 2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604  
2.2 CENTER CONTACT: BRASS PER JIS-C3604  
2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

#### 3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

#### 4.0 ENVIRONMENTAL

- 4.1 OPERATING TEMPERATURE RANGE: -55° C TO +125° C

NO	DESCRIPTION	MATERIAL	Q'TY	FINISH
7	CENTER CONTACT	BRASS	1	GOLD
6	INSULATION	TEFLON	1	NONE
5	WASHER	BRASS	1	NONE
4	BODY	BRASS	1	NICKEL 100 μ" MIN.
3	GASKET	SILICONE	1	RED
2	INSULATION	TEFLON	1	NONE
1	SHELL	BRASS	1	NICKEL 100 μ" MIN.

APPROVED by \_\_\_\_\_ DATE: \_\_\_\_\_

DESCRIPTION		FME PLUG - TNC PLUG		DATE		REV.	
製圖	DRAWN	TOLERANCE	品名	23-12	T.G.N	日期	04.27.93'
	Yoko	.X ±0.2	TITLE	\ROHS COMPLIANT (50Ω)		版次	A-1
檢圖	CHECK	.XX ±0.1	單位	UNIT		DWG.NO. 23-0044	
	Jacky	.XXX ±0.05	mm(in)	SCALE		佳楠精密電子股份有限公司	
認定	APPROVAL	ANGLE ±5°	比例	4:1		CHIN NAN PRECISION ELECTRONICS CO.,LTD.	
	Lewis						