




Lunéta  
*lighting range*

GET  
PLC



GET PLC Unit 4, Brunswick Industrial Park, London N11 1JL England

Sales Hotline: 020 8211 9211 Fax Hotline: 020 8211 9222 email: [enquiry@getplc.co.uk](mailto:enquiry@getplc.co.uk) website: [www.getplc.co.uk](http://www.getplc.co.uk)

Publication No. G0025/10K/0502

# quality service value

To supply products of the highest quality, to support them with the best possible service, and to ensure that every product offers unbeatable value for money.



Those were the simple objectives of **GET's founders**, over 40 years ago.

Today, **GET GROUP PLC** is a public quoted company employing more than 200 people, but its objectives have never changed. Quality, service and value are still, and always will be, the foundation stones of GET's business philosophy.

**Quality** is the guiding principle for GET's highly experienced development team. Utilising the latest CAD systems, rapid prototyping can be achieved translating end user requirements into innovative designs for installer-friendly products.

All new products are subject to rigorous internal evaluation in GET's in-house laboratory before further testing by UKAS approved test houses. Only when their quality is proven and guaranteed are products released for sale. But that's not the end of the story. By listening carefully to customer feedback continual product enhancements improve not just quality but also performance and ease of use.

To ensure that its **customer service** remains second to none, GET invests continually. Already one of Europe's most modern warehouse facilities, GET's National Distribution Centre encompasses 300,000 square feet with provision for over 30,000 pallet locations.

Fast response to stock enquiries and rapid order processing is aided by a powerful IBM AS400 computer system enabling 99% of all orders to be despatched on the day of receipt. Strict quality control procedures ensure that customer's requirements are accurately and consistently satisfied, while daily nationwide deliveries provide all customers with rapid access to GET products.

GET products have a well deserved reputation for offering outstanding **value for money**. Advanced manufacturing techniques, latest materials and technology ensure products are made to the highest quality. GET's worldwide sourcing capability, together with its in-house design and development facilities further contribute to ensuring that all GET products set the standard for value.



## Lunéta Lighting for Tomorrow



Attractive style packaging.



Co-ordinated finishes for a complete 'one-stop-shop' facility.



Extensive and ever growing range of decorative and practical indoor fittings.



Variety of external fittings, ideal for creating lighting effects or for security purposes.

The Luneta range of lighting equipment is a growing part of GET's product portfolio – a sure sign of increased demand for varying lighting styles and effects for both the home and office.

The indoor range offers a broad and versatile selection of decorative fittings such as downlighters, spotlights and cabinet lights as well as more functional fittings such as shaver lights and striplights.

Recent additions to this part of the range include:

- A new range of low voltage and mains halogen die cast downlighters – available in seven stylish finishes which perfectly complement the GET Ultimate range of wiring accessories for that overall designer look.
- Three exciting new finishes have been added to our pressed MR16 low voltage and GU10 downlighters for further choice.
- New GU10 mains halogen spotlights.
- New compact fluorescent downlighters in either fixed or floating glass variants.
- New low voltage shower lights.

Moving outdoors, the Luneta range now offers a selection of fittings for external use, ideal for creating salubrious environments or with added security more in mind. Recent additions to this part of the range include:

- A new range of wall or post-top die cast lanterns, ideal for creating an inviting ambience along walkways or in doorways.
- New pagoda and spot light kits also provide a means of decorative lighting for around the garden and walkways.
- A new 70W sodium light with photocell also provides excellent security lighting.

To help with identification of new products, complete range introductions have been marked with a NEW flash whilst product additions are highlighted in red text.

Above all, the Luneta range boasts GET's principles of quality, value and service, ensuring the customer always receives quality products, available when required, at value for money prices.



# Lunéta die cast downlighters

## LOW VOLTAGE MR16 DOWNLIGHTERS



CODE	DESCRIPTION	CUT-OUT (mm)	PACK QTY
<b>FIXED</b>			
GDLLD50B	Brass effect	65mm	6
GDLLD50C	Chrome	65mm	6
GDLLD50W	White	65mm	6
GDLLD50BB	Brushed brass effect	65mm	6
GDLLD50CB	Brushed chrome	65mm	6
GDLLD50BN	Black nickel	65mm	6
GDLLD50PN	Pearl nickel	65mm	6


### WALL WASH

CODE	DESCRIPTION	CUT-OUT (mm)	PACK QTY
GDLLTD50B	Brass effect	80mm	6
GDLLTD50C	Chrome	80mm	6
GDLLTD50W	White	80mm	6
GDLLTD50BB	Brushed brass effect	80mm	6
GDLLTD50CB	Brushed chrome	80mm	6
GDLLTD50BN	Black nickel	80mm	6
GDLLTD50PN	Pearl nickel	80mm	6

### ADJUSTABLE

CODE	DESCRIPTION	CUT-OUT (mm)	PACK QTY
GDLLW50B	Brass effect	110mm	6
GDLLW50C	Chrome	110mm	6
GDLLW50W	White	110mm	6
GDLLW50BB	Brushed brass effect	110mm	6
GDLLW50CB	Brushed chrome	110mm	6

## MAINS HALOGEN GU10 DOWNLIGHTERS (CW LAMP)



CODE	DESCRIPTION	CUT-OUT (mm)	PACK QTY
<b>FIXED</b>			
GDLGD50B	Brass effect	65mm	6
GDLGD50C	Chrome	65mm	6
GDLGD50W	White	65mm	6
GDLGD50BB	Brushed brass effect	65mm	6
GDLGD50CB	Brushed chrome	65mm	6
GDLGD50BN	Black nickel	65mm	6
GDLGD50PN	Pearl nickel	65mm	6

### WALL WASH


CODE	DESCRIPTION	CUT-OUT (mm)	PACK QTY
GDLGTD50B	Brass effect	80mm	6
GDLGTD50C	Chrome	80mm	6
GDLGTD50W	White	80mm	6
GDLGTD50BB	Brushed brass effect	80mm	6
GDLGTD50CB	Brushed chrome	80mm	6
GDLGTD50BN	Black nickel	80mm	6
GDLGTD50PN	Pearl nickel	80mm	6

- All GET low voltage and mains halogen downlighters are supplied complete with stirrup and covered terminal block, quick fix steel spring clips and lamp retaining ring.
- All GET GU10 mains halogen downlighters are supplied complete with 50W GU10 lamps.

## DIMENSIONS


### Fixed

A	B	C
155	116	65




### Wallwash

A	B	C
158	125	80



### Adjustable

A	B
110	91.75



# Lunéta pressed downlighters

## LOW VOLTAGE MR16 DOWNLIGHTERS



CODE	DESCRIPTION	CUT-OUT (mm)	PACK QTY
<b>FIXED</b>			
GDLL50B	Brass effect	65mm	6
GDLL50C	Chrome	65mm	6
GDLL50W	White	65mm	6
GDLL50BB	Brushed brass effect	65mm	6
GDLL50CB	Brushed chrome	65mm	6
GDLL50BN	Black nickel	65mm	6

### EYEBALL

CODE	DESCRIPTION	CUT-OUT (mm)	PACK QTY
GDLLE50B	Brass effect	95mm	6
GDLLE50C	Chrome	95mm	6
GDLLE50W	White	95mm	6
GDLLE50BB	Brushed brass effect	95mm	6
GDLLE50CB	Brushed chrome	95mm	6
GDLLE50BN	Black nickel	95mm	6

### WALL WASH

CODE	DESCRIPTION	CUT-OUT (mm)	PACK QTY
GDLIT50B	Brass effect	80mm	6
GDLIT50C	Chrome	80mm	6
GDLIT50W	White	80mm	6
GDLIT50BB	Brushed brass effect	80mm	6
GDLIT50CB	Brushed chrome	80mm	6
GDLIT50BN	Black nickel	80mm	6

## MAINS HALOGEN GU10 DOWNLIGHTERS (CW LAMP)



CODE	DESCRIPTION	CUT-OUT (mm)	PACK QTY
<b>FIXED</b>			
GDLG50B	Brass effect	65mm	6
GDLG50C	Chrome	65mm	6
GDLG50W	White	65mm	6
GDLG50BB	Brushed brass effect	65mm	6
GDLG50CB	Brushed chrome	65mm	6
GDLG50BN	Black nickel	65mm	6

### EYEBALL

CODE	DESCRIPTION	CUT-OUT (mm)	PACK QTY
GDLGE50B	Brass effect	95mm	6
GDLGE50C	Chrome	95mm	6
GDLGE50W	White	95mm	6
GDLGE50BB	Brushed brass effect	95mm	6
GDLGE50CB	Brushed chrome	95mm	6
GDLGE50BN	Black nickel	95mm	6


### WALL WASH

CODE	DESCRIPTION	CUT-OUT (mm)	PACK QTY
GDLGT50B	Brass effect	80mm	6
GDLGT50C	Chrome	80mm	6
GDLGT50W	White	80mm	6
GDLGT50BB	Brushed brass effect	80mm	6
GDLGT50CB	Brushed chrome	80mm	6
GDLGT50BN	Black nickel	80mm	6

## DIMENSIONS


### Fixed

A	B	C
155	116	65




### Eyeball

A	B	C
220	140	95



### Wallwash

A	B	C
158	125	80



# Lunéta downlighters & accessories

## LOW VOLTAGE CABINET LIGHTS



CODE	DESCRIPTION	PACK QTY
GDLLC20B	20W Brass effect	1
GDLLC20C	20W Chrome	1
GDLLC20W	20W White	1

- Complete with removable mounting collar for surface or flush mounting
- Frosted glass diffuser for improved light dissipation
- Strong steel fixing clips for secure flush fixing
- Supplied c/w 20W G4 capsule lamp

## LOW VOLTAGE CABINET LIGHT KITS



CODE	DESCRIPTION	PACK QTY
GDLLC320B	20W Brass effect Kit	1
GDLLC320C	20W Chrome Kit	1
GDLLC320W	20W White Kit	1

Kit comprises:

- 3 x 20W low voltage cabinet lights
- 1 x 65VA light weight electronic transformer
- 1 x wiring loom
- 3 x 20W G4 capsule lamps
- Easy fit plug and socket system


## LOW VOLTAGE MR16 SHOWER LIGHTS



CODE	DESCRIPTION	CUT-OUT (mm)	PACK QTY
GDLLS50B	Brass effect	72.5mm	1
GDLLS50C	Chrome	72.5mm	1
GDLLS50W	White	72.5mm	1

- Suitable for use in bathrooms, shower cubicals or kitchens
- Clear glass diffuser
- Suitable for exterior use (IP54 rated)
- Die cast construction c/w stirrup and enclosed terminal block
- For use with max 50W MR16 dichroic Lamp

## DOWNLIGHTER ACCESSORIES




CODE	DESCRIPTION	PACK QTY
GJBN20ASBR	59mm 20A 4 terminal junction box (designed to fit through a standard cut-out)	10
GTR65L	65VA Dimmable electronic transformer	1
GTR105L	105VA Dimmable electronic transformer	1

- Supplied with 150mm input and output leads
- Compact design assists installation
- For use with GET low voltage luminaires
- Compatible with GET low voltage dimmer switches


# Lunéta mains downlighters

## MAINS FIXED DOWNLIGHTERS




BRASS EFFECT	WHITE	CHROME	DESCRIPTION	CUT-OUT (mm)	PACK QTY
GDL50B	GDL50W	GDL50C	R50 40W max	70	6
GDL64B	GDL64W	GDL64C	R64 60W max	85	6
GDL80B	GDL80W	GDL80C	R80 100W max	105	6

## PAR38 FIXED DOWNLIGHTERS




BRASS EFFECT	WHITE	CHROME	DESCRIPTION	CUT-OUT (mm)	PACK QTY
GDL38B	GDL38W	GDL38C	PAR38 120W max	145	6

## EYEBALL DOWNLIGHTERS



BRASS EFFECT	WHITE	CHROME	DESCRIPTION	CUT-OUT (mm)	PACK QTY
GDLE50B	GDLE50W	GDLE50C	R50 40W max	105	6
GDLE64B	GDLE64W	GDLE64C	R64 60W max	120	6
GDLE80B	GDLE80W	GDLE80C	R80 100W max	150	6

## PAR38 EYEBALL DOWNLIGHTERS





BRASS EFFECT	WHITE	CHROME	DESCRIPTION	CUT-OUT (mm)	PACK QTY
GDLE38B	GDLE38W	GDLE38C	PAR38 120W max	185	6

### Mains Downlighter Features:

- Fully enclosed
- 300mm pre-wired mains lead
- Ceramic lampholder for long-life
- All steel construction

### DIMENSIONS





# Lunéta GU10 spot lights (c/w lamps)



The new range of GU10 spotlights provide a stylish, modern effect in any room. The products are offered in 3 different finishes and are available in four configurations to ensure there is a fitting to satisfy any installation.

The fittings are supplied complete with 50W GU10 lamps and full installation instructions and fixing kit.



Choose from three finishes available:

Satin Nickel with frosted blue glass



Satin Nickel with frosted white glass



Polished Chrome

CODE	DESCRIPTION	BOX QTY
GCSG1P50C	Single Spot - Polished Chrome	1
GCSG1P50SGW	Single Spot - Satin Nickel with white glass	1
GCSG1P50SGB	Single Spot - Satin Nickel with blue glass	1
GCSG3P50C	Triple Plate - Polished Chrome	1
GCSG3P50SGW	Triple Plate - Satin Nickel with white glass	1
GCSG3P50SGB	Triple Plate - Satin Nickel with blue glass	1
GCSG3B50C	Triple Straight Bar - Polished Chrome	1
GCSG3W50SGW	Triple Wave Bar - Satin Nickel with white glass	1
GCSG3W50SGB	Triple Wave Bar - Satin Nickel with blue glass	1
GCSG4W50C	Quad Wave Bar - Polished Chrome	1
GCSG4W50SGW	Quad Wave Bar - Satin Nickel with white glass	1
GCSG4W50SGB	Quad Wave Bar - Satin Nickel with blue glass	1

### Features

- Fully adjustable heads
- Choice of single, triple or quad fittings
- Bar and plate designs
- Easy to change lamps
- Supplied complete with 50W GU10 lamps
- Manufactured to BS EN 60598-2-1
- 

# Lunéta decorative lighting

## MAINS SPOT LIGHTS



CODE	DESCRIPTION	BOX QTY
GCS1C80*S	60W Single Clip Spot	1
GCS1P80*S	100W Single Spot	1
GCS2B80*S	100W Twin bar	1
GCS3B80*	100W Triple Bar	1
GCS3P80*	100W Triple cluster plate	1

Replace \* with either B, C or W to denominate finish required.  
B = Brass effect, C = Chrome & W = White.

## 60W FLUSH LIGHTS



CODE	DESCRIPTION	BOX QTY
GFLC60B	60W Brass effect	1
GFLC60C	60W Chrome	1
GFLC60W	60W White	1

- Suitable for wall/ceiling mounting
- Slimline design
- 60W ES fitting suitable for use with GLS/Golfball/Candle lamps
- Decorative opal glass diffuser for even light dissipation

## COMPACT FLUORESCENT DOWNLIGHTERS



CODE	DESCRIPTION	BOX QTY
GD LCS29G	2 X 9W PL glass diffuser	1
GD LCS213G	2 X 13W PL glass diffuser	1
GD LCS218G	2 X 18W PL glass diffuser	1
GD LCS226G	2 X 26W PL glass diffuser	1
GD LCS29FG	2 X 9W PL floating glass diffuser	1
GD LCS213FG	2 X 13W PL floating glass diffuser	1
GD LCS218FG	2 X 18W PL floating glass diffuser	1
GD LCS226FG	2 X 26W PL floating glass diffuser	1


- Metallized polycarbonate reflector
- Pre-wired separate gear box with easy access termination
- Complies with BS EN 60598
- IP43 rated

## 221MM & 284MM STRIPLIGHTS



CODE	DESCRIPTION	BOX QTY
GSTLIT1	60W 221mm Unswitched	20
GSTLIT1PS	60W 221mm Push switch	20
GSTLIT1PU	60W 221mm Pull switch	20
GSTLIT4	60W 284mm Unswitched	20
GSTLIT4PS	60W 284mm Push switch	20
GSTLIT4PU	60W 284mm Pull switch	20

## Lunéta shaver lights



A stylish new range of four shaver light units are now available from GET. Designed to complement even the most modern of bathrooms, the soft lines ensure compatibility with any décor whilst limiting dust and dirt collection. Even light dissipation is achieved through the opal diffuser whilst also providing safe disconnection of lamp contacts\* when removed for easy replacement of lamps. (\*60W variants only).

Careful attention has been paid for fast and easy installation including a removable back plate and terminal access for wiring even after the unit has been fixed to the wall. The range is fully certified to all of the relevant safety standards.

### Features

- Stylish modern design blends with any décor.
- Opal diffuser for a softer light.
- Fitted with Earth looping terminal.
- Supplied with loose back plate for faster fixing.
- 60W fittings provide safe disconnection of lamp contact once the diffuser is removed.
- Easy connection method.
- Suitable for use in bathrooms.

### Specifications

- Dimensions: 500mm (L) x 60mm (W) x 70mm (H)
- Maximum lamp rating 60W
- Supplied pre-fitted with 284mm striplight or 11W PL11 fluorescent lamp
- Manufactured in flame retardant polycarbonate
- Compatible with UK, Europe, Australia and USA
- Complies with BS EN 60598-2-1



CODE	DESCRIPTION	BOX QTY
GSHVLIT	60W Tungsten Single Voltage 230V Output	1
GSHVLIT2	60W Tungsten Dual Voltage 115/230V Output	1
GSHVLITFL	11W Fluorescent Single Voltage 230V Output	1
GSHVLITFL2	11W Fluorescent Dual Voltage 115/230V Output	1

## Lunéta outdoor lighting

### DIE CAST LANTERNS



CODE	DESCRIPTION	PACK QTY
GLAN4SB	4 sided lantern 100W Max ES	1
GLAN4SPTB	4 sided post top lantern 100W Max ES	1
GLAN6SB	6 sided lantern 100W Max ES	1
GLAN6SPTB	6 sided post top lantern 100W Max ES	1
GLANHWB	Half wall lantern 60W Max ES	1



- Traditional style lantern
- Bevelled edge glass for decorative effect
- Ideal for lighting doorways and patios
- Vandal proof construction
- Die cast construction for durability
- For use with golfball or candle lamps
- Weatherproof IP43

### BULKHEADS



CODE	DESCRIPTION	PACK QTY
GBH100BC	100W with clear diffuser (IP65)	1
GBH100BR	100W with red diffuser (IP65)	1
GBH29C	2 X 9W with clear diffuser (IP65)	1
GBH29CP	2 X 9W with photocell and clear diffuser (IP65)	1
GBH60BC	60W Economy with clear diffuser	1

- Tough UV stabilised polycarbonate cover
- Choice of 20mm knockouts for cable and/or conduit entry
- Lamps not supplied

### 40W BRICKLIGHTS



GET CODE	DESCRIPTION	PACK QTY
GBL40LB	40W louvred black	1
GBL40PB	40W plain black	1

- Manufactured from die-cast aluminium with opal glass
- Powder coated paint finish for extra durability
- Corrosion resistant
- Suitable for lighting paths, driveways & car ports
- IP44 rated



# Lunéta garden lighting



The addition of garden lighting to the Luneta range offers the consumer a decorative method of lighting the garden for either security purposes or to create an salubrious environment.

Available in either mains or low voltage variants, the range provides a lighting unit to suit a variety of purposes.

All lights are supplied in a black casing to blend in with the garden environment and are weather resistant.

## MAINS GARDEN LIGHTS



CODE	DESCRIPTION	BOX QTY
GGLMP100	100W GLS Pagoda	1
GGLMSW38	120W PAR 38 Single wall spot	1
GGLMTW38	120W PAR 38 Twin wall spot	1
GGLMS38	120W PAR 38 Single spike spot	1
GGLMTS38	120W PAR 38 Twin spike spot	1

## FESTOON LIGHTING CHAINS



CODE	DESCRIPTION	BOX QTY
GFCH16	6m Chain with 10 B22 Lamps	1
GFCH29	9m Chain with 20 B22 Lamps	1
GFCH11	10m Chain with 10 B22 Lamps	1
GFCH22	20m Chain with 20 B22 Lamps	1

## LOW VOLTAGE KITS



CODE	DESCRIPTION	BOX QTY
GGLLK4P	3 Tier Low Voltage Pagoda kit	1
GGLLK4S	Low Voltage Spot kit	1

Kits comprise of:

- 4 pagoda or spotlights
- 15m low voltage cable
- 45W 36VA transformer and 13A plug
- 5 wedge bulbs

## LOW VOLTAGE TIMERS



CODE	DESCRIPTION	BOX QTY
GGLLT	Multi-function Low Voltage Timer	1
GGLLPT	Multi-function Low Voltage PIR Timer	1

- Weather resistant
- Dusk to dawn operation

# Lunéta floodlighting

## SITE LIGHTING - EN 60598



CODE	DESCRIPTION	FLEX LENGTH	BOX QTY
500T110	500W 110V single enclosed TH fitting c/w adjustable stand	3.6M	1
500T	500W 240V single enclosed TH fitting c/w adjustable stand	3.6M	1
1000T110	1000W 110V twin enclosed TH fitting c/w adjustable stand	3.6M	1
1000T	1000W 240V twin enclosed TH fitting c/w adjustable stand	3.6M	1
500P110	500W portable general purpose TH fitting, 110V	1.5M	1
500P	500W portable general purpose TH fitting, 240V	1.5M	1
150P110	150W portable general purpose TH fitting, 110V	1.5M	1
150P	150W portable general purpose TH fitting, 240V	1.5M	1
150G110	150W grippa handlamp c/w guard, 110V	1.5M	1
150G	150W grippa handlamp c/w guard, 240V	1.5M	1

A comprehensive range of lighting equipment designed and constructed to withstand the harshest of environments.

From PIR controlled floodlights, independent enclosed floods and independent PIR units to portable site equipment available in either 110V or 240V.

To ensure optimum working conditions on construction sites, equipment is available in power outputs of 150W, 500W and 1000W thus ensuring that there is a fitting in the GET range to suit virtually all applications.

- Complies with all relevant EMC and Low Voltage directives
- All floodlighting carries a 1 year guarantee

## FLOODLIGHTING - BS 4533 & BS EN 60730



CODE	DESCRIPTION	BOX QTY
GXPIRFD	500W professional 180° PIR floodlight c/w 500W lamp	1
GPIRFDV	500W PIR TH floodlight	1
P/MINI	150W horizontal mini PIR TH floodlight	1
P/MINIV	150W vertical mini PIR TH floodlight c/w 150W lamp	1
EXPIR	500W independent PIR unit	1
GFLD/BLV	500W enclosed TH floodlight	1
GFLD/300	300W enclosed TH floodlight	1
MINI/FLDV	150W compact enclosed TH floodlight	1
GPIRTWB	Twin 120W PAR38 floodlight with PIR	1

## SODIUM FLOODLIGHT



CODE	DESCRIPTION	BOX QTY
FLSON70	70W c/w toughened glass cover	1
FLSON70P	70W c/w polycarbonate cover	1
FLSON70PP	70W c/w photocell & polycarbonate cover	1

- Supplied with 70W HPS elliptical lamp

# Lunéta replacement lamps

## TUNGSTEN HALOGEN LAMPS



CODE	DESCRIPTION	LENGTH	BOX QTY
TH150	150W 240V	70mm	50
TH200	200W 240V	118mm	50
TH300	300W 240V	118mm	50
TH500	500W 240V	118mm	50
TH750	750W 240V	189mm	50
TH1000	1000W 240V	189mm	50
TH1500	1500W 240V	254mm	50
TH310	300W 110V	118mm	50
TH510	500W 110V	118mm	50
TH1010	1000W 110V	189mm	50

- Average life 2000 hours

## DICHROIC LAMPS



DESCRIPTION	SPOT BEAM (12°)	MEDIUM BEAM (24°)	FLOOD BEAM (28°)	BOX QTY
<b>50mm – MR16</b>				
20W open	M68	M94	M69	10
35W open	M71	M70	M81	10
50W open	M49	M50	M58	10
20W closed	M268	M294	M269	10
35W closed	M271	M270	M281	10
50W closed	M249	M250	M258	10
<b>35mm – MR11</b>				
20W open	M52	M51	M62	10
35W open	M65	M66	M199	10
20W closed	M252	M251	M262	10
35W closed	M265	M266	M299	10

- Average life 3000 hours

CODE	DESCRIPTION	BOX QTY
M2693	20W closed 38° flood beam triple pack	3
M2583	50W closed 38° flood beam triple pack	3

## 12V G4 CAPSULE LAMPS



CODE	DESCRIPTION	PACK QTY
GCL10	10W capsule lamps	10
GCL20	20W capsule lamps	10

## GU10 MAINS HALOGEN LAMP



CODE	DESCRIPTION	PACK QTY
GUH50F	50W 35° flood beam	10
GUH50F2	50W 35° flood beam twin pack	2

## technical information

### Mains Downlighters

Operating Voltage	230/240V AC 50Hz
Max Lamp Rating	R50 40W
	R64 60W
	R80 100W
	PAR38 120W
Standard Compliance	EN 60598-1:1997
Lamp Type	Reflector ES (R50 SES)

CE F\*

\* Excludes R80 Fitting

### Mains Halogen Downlighters

Operating Voltage	230/240V AC 50Hz
Max Lamp Rating	50W
Standard Compliance	EN 60598-1:1997
Lamp Type	GU10 Closed Halogen ES50

CE F

### Low Voltage Dichroic Downlighters

Operating Voltage	12V AC 50Hz
Max Lamp Rating	50W
Standard Compliance	EN 60598-1:1997
Lamp Type	MR16 Dichroic Closed Type

CE F

### Low Voltage Cabinet Lights

Operating Voltage	12V AC 50Hz
Max Lamp Rating	20W
Standard Compliance	EN 60598-1:1997
Lamp Type	G4 Capsule Lamp

CE

### Electronic Transformer

Input Voltage	230/240V AC 50/60Hz
Output Voltage	12V
Max Output Load	65VA (TREL65L)
	105VA (TREL105VA)
Ta	40°C
Tc	55°C
Output Lead Length	150mm
Input Lead Length	150mm

CE F

### Beam Diagrams

