

Torqueleader 'Torquesafe' Slipper Wrenches



- Streamlined production torque wrenches designed for modern needs.
- 3 models covering ranges of 3-125 N·m and 2-90 lbf·ft to suit the majority of volume production torque requirements.
- Accuracy ±5% repeatable. Guarantees equal tightness
- Lightweight less fatigue for the operator encourages use.
- Wrenches 'slip' when predetermined torque setting is reached - completely eliminates overtighting.
- Automatic resetting is signalled by an audible 'click' allowing fast continuation of work.
- Torque Safe' wrenches incorporate a fully supported ratchet with effectively 36 teeth on TSN 25 and 48 on TSN 55 and TSN 125 - giving smooth, positive torque control, even in confined spaces.
- Strong corrosion-resistant stainless steel head, plastic coated handle and non-slip knurled grip.


MODEL		-					A A	
		N-m	lbf-ft	(Inch)	mm	in	kg kg	₩ b
TSN 25	011000	3.70	2 – 18	1/4	216	8.5	0.34	0.75
TSN 55	: 011020 ·	15.68	10 – 40	3∕8	324	12.75	0.80	1.75
TSN 125	011040	40-125	30 - 90	1/2	460	18.13	1.36	3.0






Static Torque Meter

Torqueleader 'Breaking' Torque Handles




- Production, lever type wrenches for applying low torque
- Ideal for use in restricted spaces suitable for most light electro/mechanical/electronic applications.
- Compact, well balanced and strong for unskilled users.
- Breaking Torque Handles 'break' at predetermined torque value to give movement in either direction - 90° with TB 12 & TB 100 and 20° with TB 250 SR - then reset on returning to in-line position.
- Extensive range of interchangeable end fittings available.
- Special end fittings can be made to order, to comply with individual requirements.

MODEL							()	
		lbf-in	kgf-cm	N-m	 mm	in	gm	⊕ _{oz}
TB12C	011100	1.25-12	1.4-14	0.14-1.36	105	41/8	100	31/2
TB100C	011200	10-100	11.5–115	1-11	105	41/8	120	41/4
TB250SR	011300	80-250	90-300	930	185	71/4	350	121/4







Purpose-designed Double-ended Ratchet and Cap





Setting TB 100 on Spring Type Rig Torqueleader