



Revision Date: 03/09/2006

Issue date: 04/13/2006

1. CHEMICAL PRODUCT AND COMPANY IDENTIFICATION

Product name:	3106 UV Curing General Purpose Adhesive	Item No. :	23697
Product type:	Ultraviolet adhesive	Region:	United States
Company address:	Contact Information:		
Henkel Corporation	Telephone: 860.571.5100		
1001 Trout Brook Crossing	Emergency telephone: 860.571.5100		
Rocky Hill, Connecticut 06067	Internet: www.loctite.com		

2. COMPOSITION/INFORMATION ON INGREDIENTS

<u>Hazardous components</u>	<u>%</u>	<u>ACGIH TLV</u>	<u>OSHA PEL</u>	<u>OTHER</u>
Urethane Polymer Proprietary	30-60	None	None	None
Acrylate monomer Proprietary	30-60	None	None	None
Modified acrylamide 2680-03-7	10-30	None	None	0.1 mg/m ³ TWA (skin) 0.025 ppm TWA (skin)
Photoinitiator 24650-42-8	1-5	None	None	None
Substituted silane Proprietary	1-5	None	None	None
Silica, amorphous, fumed, crystalline-free 112945-52-5	1-5	6 mg/m ³ TWA	10 mg/m ³ TWA	3 mg/m ³ TWA respirable dust
Photoinitiator Proprietary	1-5	None	None	None
Hydroxyethyl acrylate 818-61-1	0.1-1	None	None	None

3. HAZARDS IDENTIFICATION

Item No. : 23697

Product name: 3106 UV Curing General Purpose Adhesive

EMERGENCY OVERVIEW

HMIS:

Physical state: Liquid
Color: Transparent to Slightly Hazy
Odor: Mild

HEALTH: 2*
FLAMMABILITY: 2
PHYSICAL HAZARD: 1
Personal Protection: See Section 8

WARNING: COMBUSTIBLE LIQUID
HARMFUL IF SWALLOWED, ABSORBED THROUGH SKIN OR INHALED.
DO NOT SPRAY. DO NOT HEAT.
MAY CAUSE ALLERGIC SKIN REACTION.
CAUSES EYE, SKIN AND RESPIRATORY TRACT IRRITATION

Relevant routes of exposure: Skin, Inhalation, Eyes

Potential Health Effects

Inhalation: Modified acrylamide is harmful if inhaled. Vapors and mists will irritate the respiratory tract and nasal passages. Headache. Nausea. DO NOT heat or spray as this increases the inhalation hazard.
Skin contact: Modified acrylamide may be absorbed through skin in harmful amounts. Toxic. May cause allergic skin reaction. Irritating to skin.
Eye contact: Contact with eyes will cause irritation.
Ingestion: Modified acrylamide is harmful if swallowed. Toxic.

Existing conditions aggravated by exposure: Eye, skin, and respiratory disorders.

See Section 11 for additional toxicological information.

4. FIRST AID MEASURES

Inhalation: Remove to fresh air. If symptoms develop and persist, get immediate medical attention.

Skin contact: Immediately flush skin with plenty of water (using soap, if available). Remove contaminated clothing and shoes. Wash clothing before reuse. Get immediate medical attention if symptoms occur.

Eye contact: Immediately flush eyes with plenty of water for at least 15 minutes. Get immediate medical attention.

Ingestion: Do not induce vomiting. Keep individual calm. Get medical attention immediately.

5. FIRE-FIGHTING MEASURES

Flash point: 77.8°C (172°F) Pensky Martens closed cup

Autoignition temperature: Not available

Flammable/Explosive limits-lower %: Not available

Flammable/Explosive limits-upper %: Not available

Extinguishing media: Foam, dry chemical or carbon dioxide.

Special fire fighting procedures: None

Unusual fire or explosion hazards: None

Hazardous combustion products: Oxides of carbon. Oxides of nitrogen. Oxides of sulfur. Irritating organic vapors. Toxic fumes.

6. ACCIDENTAL RELEASE MEASURES

Environmental precautions:	Remove sources of ignition. Prevent product from entering drains or open waters.
Clean-up methods:	Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up. Soak up with inert absorbent. Store in a partly filled, closed container until disposal.

7. HANDLING AND STORAGE

Handling:	Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. DO NOT heat or spray. Use only with adequate ventilation. Refer to Section 8. Use only in area provided with appropriate exhaust ventilation.
Storage:	For safe storage, store at or below 26°C (80°F). Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.
Incompatible products:	Refer to Section 10.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Engineering controls:	Local exhaust ventilation is recommended when general ventilation is not sufficient to control airborne contamination below occupational exposure limits.
Respiratory protection:	Use NIOSH approved respirator if there is potential to exceed exposure limit(s). If this material is handled at elevated temperatures or under mist forming conditions, without engineering controls, a NIOSH approved respirator must be used.
Skin protection:	Use impermeable gloves and protective clothing as necessary to prevent skin contact. Neoprene gloves.
Eye/face protection:	Safety goggles or safety glasses with side shields. In a splash hazard environment, chemical goggles should be used in combination with a full face shield.

See Section 2 for exposure limits.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Liquid
Color:	Transparent to Slightly Hazy
Odor:	Mild
Vapor pressure:	Less than 5 mm Hg at 20°C (68°F)
pH:	Not applicable
Boiling point/range:	Greater than 93°C (200°F)
Melting point/range:	Not available
Specific gravity:	1.078
Vapor density:	Greater than 1
Evaporation rate:	Not available
Solubility in water:	Slight
Partition coefficient (n-octanol/water):	Not available
VOC content:	ASTM D5403 Process volatiles 2.16 %, 23.28 grams/liter; Potential volatiles 1.05 %, 11.32 grams/liter; Total volatiles 3.21 %, 34.60 grams/liter.

10. STABILITY AND REACTIVITY

Stability:	Stable under normal conditions of storage and use.
Hazardous polymerization:	May occur.
Hazardous decomposition products:	Oxides of carbon. Oxides of nitrogen. Oxides of sulfur. Irritating organic vapors.
Incompatibility:	Strong oxidizers. Strong acids. Strong bases. Amines. Peroxides. Free radical initiators.

Conditions to avoid:

Heat, flames, sparks and other sources of ignition. Do not heat above 26°C (80°F).

11. TOXICOLOGICAL INFORMATION**Product toxicity data:**

Modified acrylamide: LD50 (oral, rat) 316 mg/kg
 LD50 (dermal, rabbit) 518 mg/kg
 LC50 (vapor, 1hour, rat) greater than 776 ppm

Carcinogen Status

Hazardous components	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen
Urethane Polymer Proprietary	No	No	No
Acrylate monomer Proprietary	No	No	No
Modified acrylamide 2680-03-7	No	No	No
Photoinitiator 24650-42-8	No	No	No
Substituted silane Proprietary	No	No	No
Silica, amorphous, fumed, crystalline-free 112945-52-5	No	No	No
Photoinitiator Proprietary	No	No	No
Hydroxyethyl acrylate 818-61-1	No	No	No

Literature Referenced Target Organ & Other Health Effects

Hazardous components	Health Effects/Target Organs
Urethane Polymer Proprietary	No Records
Acrylate monomer Proprietary	Allergen, Irritant
Modified acrylamide 2680-03-7	Less weight gain and food intake., Mutagen, Kidney, Irritant, Eyes
Photoinitiator 24650-42-8	No Target Organs
Substituted silane Proprietary	Allergen, Irritant
Silica, amorphous, fumed, crystalline-free 112945-52-5	Nuisance dust
Photoinitiator Proprietary	No data
Hydroxyethyl acrylate 818-61-1	Allergen, Central nervous system, Heart, Irritant, Kidney, Liver, Lung, Some evidence of carcinogenicity, Spleen

12. ECOLOGICAL INFORMATION**Ecological information:**

Not available

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Dispose of according to Federal, State and local governmental regulations.

EPA hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The shipping classifications in this section are for non-bulk packaging only (unless otherwise specified). Shipping classification may be different for bulk packaging.

U.S. Department of Transportation Ground (49 CFR):

Proper shipping name:	Unrestricted
Hazard class or division:	None
Identification number:	None
Packing group:	None

International Air Transportation (ICAO/IATA):

Proper shipping name:	Unrestricted
Hazard class or division:	None
Identification number:	None
Packing group:	None

WaterTransportation (IMO/IMDG):

Proper shipping name:	Unrestricted
Hazard class or division:	None
Identification number:	None
Packing group:	None
Marine pollutant:	None

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status:	All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12 (b) Export Notification:	4-Methoxyphenol (150-76-5).

CERCLA/SARA Section 302 EHS:	None above reporting de minimus.
CERCLA/SARA Section 311/312:	Immediate Health Hazard, Delayed Health Hazard, Fire
CERCLA/SARA 313:	None.

California Proposition 65: No California Proposition 65 listed chemicals are known to be present.

Canada Regulatory Information

CEPA DSL/NDL Status:	Contains one or more components listed on the Non-Domestic Substances list.
WHMIS hazard class:	B.3, D.1.B, D.2.B

16. OTHER INFORMATION

This material safety data sheet contains changes from the previous version in sections: 3,7,8

Prepared by:

Kyra Kozak Woods, Product Safety and Regulatory Affairs Specialist

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation does not assume responsibility for any results obtained by persons over whose methods Henkel Corporation has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any of Henkel Corporation's products. In light of the foregoing, Henkel Corporation specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation further disclaims any liability for consequential or incidental damages of any kind, including lost profits.