


Universal Machine Luminaire




WD 211

connected load	230 V; 50 Hz
fitted with	2 x compact fluorescent lamp TC-S 11 W
work equipment	conventional ballast
mains lead	approx. 1.5 m; shaped plug
luminaire body	
material	aluminium
surface	painted
tubular sections	
material	steel tube
surface	painted
weight (net)	approx. 3,1 kg
fastening	screw-down flange~table clamp (accessory)~wall bracket (accessory)
technology	switchable
usage	switch
lamp cover	screen; milky
balance of articulation joints	friction
system of protection	IP 54
class of protection	I
colour luminaire body	light grey
colour of tubular sections	light grey
article no.	101221000



E_{min}: 217 lx
 E_m: 673 lx
 E_{max}: 1424 lx



measuring conditions: 50

