





Standardausführung: V23529-Bx121-Bxxx-+
Standardversion



Schnitt AB des Lötanschlusses
Cross-section AB of solderpin
(20:1)



Ordercode Sachnr	Contacts Polzahl	Mass/Dimension					
		A	B	C	D	E	F
..-Bx09-+	09	31,19	16,46	25,0 $\begin{smallmatrix} +0,12 \\ -0,13 \end{smallmatrix}$	8,02	12,93	2,74
..-Bx15-+	15	39,52	24,79	33,3 $\begin{smallmatrix} +0,15 \\ -0,1 \end{smallmatrix}$			2,74
..-Bx25-+	25	53,42	38,5	47,04 $\begin{smallmatrix} +0,13 \\ -0,13 \end{smallmatrix}$			2,76
..-Bx37-+	37	69,7	54,96	63,5 $\begin{smallmatrix} +0,13 \\ -0,13 \end{smallmatrix}$			2,76

Anforderungsstufe/Performance level ¹⁾



1) nach DIN 41652T.2 und T.4
according to DIN 41652 T.2 AND T.4

OLD PN: V23529-B****-B***-*-7427



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GNANI JADAV A E CHK K.MALCZYK APVD K.MALCZYK PRODUCT SPEC — APPLICATION SPEC — WEIGHT — CUSTOMER DRAWING	07JAN10 —<
--	--	--	---

LOC	DIST	REVISIONS					
GW	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—



mit Gewindebolzen: M3 V23529-Bxx24-Bxxx-+
with threadlock 4-40 UNC V23529-Bxx25-Bxxx-+




mit Gewinde : M3 V23529-Bxx22-Bxxx-+
with thread 4-40 UNC V23529-Bxx23-Bxxx-+



mit clipbefestigung V23529-Bx22x-Bxxx-+
with snap-in



Leiterplattenbohrung
PCB hole pattern







Mass Dimension	Polzahl n			
	9	15	25	37
C	25	33,3	47,04	63,5
H	10,96	19,18	33,12	49,6
K	8,22	16,44	30,36	46,9
X	2,74	2,74	2,76	2,76
Y	2,54			

1) nach DIN 41652T.2 und T.4
according to DIN 41652 T.2 AND T.4

OLD PN: V23529-B****-B***-* -7427

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GNANI JADAV A E		07JAN10		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K.MALCZYK		NAME	
		1 PLC ± -		PRODUCT SPEC		Buchsenleiste ¹⁾ Einbauhöhe 3,6 mm (Variante 1) Socketconnector-90° solderversion (Type1) ¹⁾	
		2 PLC ± -		—			
		3 PLC ± -		APPLICATION SPEC			
4 PLC ± -		—		SIZE		CAGE CODE	DRAWING NO
ANGLES ± ± -		WEIGHT		A2		00779	 -1-1393480-7
MATERIAL		FINISH		CUSTOMER DRAWING		SCALE	SHEET
-		-				2:1	2 of 6
							REV
							A5

Standardausführung ohne Winkel: V23529-B50x1-Bxxx-+
Standardversion without bracket



Ordercode Sachnr	Contacts Polzahl	Mass/Dimension					
		A	B	C	D	E	F
..-Bx09-+	09	31,19	16,46	25,0 $\begin{smallmatrix} +0,12 \\ -0,13 \end{smallmatrix}$	8,02	12,93	2,74
..-Bx15-+	15	39,52	24,79	33,3 $\begin{smallmatrix} +0,15 \\ -0,1 \end{smallmatrix}$			2,74
..-Bx25-+	25	53,42	38,5	47,04 $\begin{smallmatrix} +0,13 \\ -0,13 \end{smallmatrix}$			2,76
..-Bx37-+	37	69,7	54,96	63,5 $\begin{smallmatrix} +0,13 \\ -0,13 \end{smallmatrix}$			2,76

Anforderungsstufe/Performance level ¹⁾

OLD PN: V23529-B****-B***-*7427

1) nach DIN 41652 T.2 und T.4
according to DIN 41652 T.2 AND T.4

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-
FINISH	-	-

MATERIAL

-

DWN
GNANI JADAV A E

CHK
K.MALCZYK

APVD
K.MALCZYK

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

07JAN10

-

NAME

Buchsenleiste
Einbauhöhe 3,6 mm (Variante 1)
Socketconnector-90° solderversion (Type1)¹⁾

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1-1393480-7

RESTRICTED TO
-

SCALE
2:1


SHEET
3 of 6

REV
A5




TE Connectivity

1-1393480-7


mit Gewindebolzen: M3 V23529-B50x4-Bxxx-+
with threadlock 4-40 UNC V23529-B50x5-Bxxx-+



mit Gewinde : M3 V23529-B50x2-Bxxx-+
with thread 4-40 UNC V23529-B50x3-Bxxx-+



Leiterplattenbohrung
PCB hole pattern



Mass Dimension	Polzahl n Number of contacts n			
	9	15	25	37
C	25	33,3	47,04	63,5
H	10,96	19,18	33,12	49,68
K	8,22	16,44	30,36	46,92
X	2,74	2,74	2,76	2,76
Y	2,54			

1) nach DIN 41652T.2 und T.4
according to DIN 41652 T.2 AND T.4

OLD PN: V23529-B****-B***-*-7427

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	$\pm$	-
1 PLC	$\pm$	-
2 PLC	$\pm$	-
3 PLC	$\pm$	-
4 PLC	$\pm$	-
ANGLES	$\pm$	-

MATERIAL

-

FINISH

-

DWN
GNANI JADAV A E

CHK
K.MALCZYK

APVD
K.MALCZYK

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

07JAN10

-

TE Connectivity


NAME

Buchsenleiste
Einbauhhe 3,6 mm (Variante 1)¹⁾
Socketconnector-90° solderversion (Type1)¹⁾

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C=1-1393480-7	-


SCALE	SHEET	REV
2:1	4 of 6	A5

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
GW	—					
		—		SEE SHEET 1	—	—



1) nach DIN 41652T.2 und T.4
according to DIN 41652 p.2 AND p.4

OLD PN: V23529-B*****-B***-*—7427

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 07JAN10 GNANI JADAV A E				TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME Buchsenleiste Einbauhöhe 3,6 mm (Variante 1) ¹⁾ Socketconnector-90° solderversion (Type1) ¹⁾			
		APVD K.MALCZYK		PRODUCT SPEC —		RESTRICTED TO	
MATERIAL —		FINISH —		APPLICATION SPEC —		SIZE A2	
		WEIGHT —		CAGE CODE 00779		DRAWING NO C=1-1393480-7	
CUSTOMER DRAWING				SCALE 2:1		SHEET 5 of 6	
						REV A5	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GW	—						
			—	SEE SHEET 1	—	—	—

Active part numbers. Contact TE CONNECTIVITY for other configuration availability

Old Part Number	TE CONNECTIVITY Part Number
V23529-B1121-B209	1-1393480-7
V23529-B1121-B215	1-1393480-8
V23529-B1121-B225	1-1393480-9
V23529-B1121-B237	2-1393480-0
V23529-B1122-B209	2-1393480-8
V23529-B1122-B215	2-1393480-9
V23529-B1122-B225	3-1393480-0
V23529-B1122-B237	3-1392010-8
V23529-B1123-B109	3-1393480-4
V23529-B1123-B209	3-1393480-6
V23529-B1123-B215	3-1393480-7
V23529-B1123-B225	3-1393480-8
V23529-B1123-B237	3-1393480-9
V23529-B1125-B209	4-1393480-7
V23529-B1125-B215	4-1393480-8
V23529-B1125-B225	4-1393480-9
V23529-B1125-B237	5-1393480-0
V23529-B1221-B209	5-1393480-5
V23529-B1221-B215	5-1393480-6
V23529-B1221-B225	5-1393480-7
V23529-B1222-B109	6-1393480-4

Old Part Number	TE CONNECTIVITY Part Number
V23529-B1222-B115	6-1393480-5
V23529-B1222-B125	6-1393480-6
V23529-B1222-B209	6-1393480-7
V23529-B1222-B215	6-1393480-8
V23529-B1222-B225	6-1393480-9
V23529-B1222-B237	7-1393480-0
V23529-B1223-B109	7-1393480-8
V23529-B1223-B115	7-1393480-9
V23529-B1223-B125	8-1393480-0
V23529-B1223-B209	8-1393480-1
V23529-B1223-B215	8-1393480-2
V23529-B1223-B225	8-1393480-3
V23529-B1223-B237	8-1393480-4
V23529-B1224-B209	9-1393480-0
V23529-B1224-B215	9-1393480-1
V23529-B1224-B225	9-1393480-2
V23529-B1225-B209	9-1393480-9
V23529-B1225-B215	1393481-1
V23529-B1225-B225	1393481-2
V23529-B1225-B237	3-1392010-7
V23529-B2221-B209	1-1393481-1

1) nach DIN 41652 T.2 und T.4
according to DIN 41652 p.2 AND p.4

OLD PN: V23529-B****-B***-*-7427

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
GNANI JADAV A E

CHK
K.MALCZYK

APVD
K.MALCZYK

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—


CUSTOMER DRAWING

07JAN10

—

TE Connectivity

DIMENSIONS:
mm



MATERIAL
—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

FINISH
—

NAME
Buchsleistenleiste
Einbauhöhe 3,6 mm (Variante 1)
Socketconnector-90° solderversion (Type1)¹⁾

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1-1393480-7

RESTRICTED TO
—

SCALE
2:1

SHEET
6 of 6

REV
A5