BCcomponents

DATA SHEET

MKP 338 1 Metallized polyester film capacitors


Product specification NEW File under BCcomponents, BC05



MKP 338 1

MKP RADIAL POTTED TYPE

PITCH 15/22.5/27.5 mm PITCH 7.5 mm (bent back leads)



FEATURES

- 7.5 to 27.5 mm lead pitch
- Supplied loose in box, taped on ammopack or reel
- Consists of a low-inductive wound cell of metallized polypropylene film, potted in a flame-retardant case.

APPLICATIONS

- For X1 electromagnetic interference suppression
- Specially designed to meet the NEW REQUIREMENTS of the new "IEC 60384-14 2nd edition and EN 132400", requiring a 4 kV peak pulse voltage test UL1414 and CSA-C22.2 No. 1 specifications.

QUICK REFERENCE DATA

DESCRIPTION	VALUE
Capacitance range (E12 series)	10 nF to 1 μF
Capacitance tolerance	±20%; ±10%; ±5%
Rated (AC) voltage, 50 to 60 Hz	440 V
Rated (DC) voltage	1000 V
Climatic category	55/105/56/B
Rated temperature	105 °C
Maximum application temperature	105 °C
Reference specifications	IEC 60384-14 2 nd edition and EN 132400
Safety approvals:	
250 V	UL1414; note 1
440 V	UL1283; note 2
440 V	FI; note 1
Materials	qualified in accordance with UL94V-O
Safety class	X1

Notes

- 1. Approved
- 2. Pending.

2

MKP 338 1

SAFETY APPROVALS

SAFETY	SAFETY APPROVALS (X1)		VALUE	FILE NUMBERS
TAL	UL1414	250 V (AC)	10 nF to 1 μF	E112471
c FU °us	UL1283	440 V (AC)	10 nF to 1 μF	pending
(1)	FI (EN132400)	440 V (AC)	10 nF to 1 μF	FI 15350


SAFETY TEST REPORT

SAFET	Y TEST REPORT	VOLTAGE	VALUE	FILE NUMBERS	
CB TEST CERTIFICATE		440 V (AC)	10 nF to 1.0 μF: 55/10	05/56/B FI 1653	
This approval together with the CB-Certificate replace all national approval marks of the following countries (they have already signed the CB-Agreement):					
Austria	Belgium	Denmark	Finland	Sweden	
France	Germany	Ireland	Italy	Switzerland	
Netherlands	Israel	Portugal	Spain	Great Britain	
Japan	Norway	China	Poland	Czech. Republic	
Singapore	Rep. of Korea	Hungary	Iceland	Slovenian	

3

MKP 338 1

COMPOSITION OF CATALOGUE NUMBER



Notes

- 1) For SPQ refer to this handbook, chapter "Packaging information"; taped on reel pitch = 27.5 mm is not available.
- 2) H = in-tape height; for detailed specifications refer to this handbook, chapter "Packaging information".


Product specification

Metallized polyester film capacitors

MKP 338 1

MKP 338 1 GENERAL DATA

PITCH 15/22.5/27.5 mm PITCH 7.5 mm (bent back leads)



Specific reference data for the 440 V AC (X1) capacitors

DECORPTION	VALUE		
DESCRIPTION	at 1 kHz	at 10 kHz	at 100 kHz
Tangent of loss angle:			
C ≤ 470 nF	≤10 × 10 ⁻⁴	≤20 × 10 ⁻⁴	≤100 × 10 ⁻⁴
C > 470 nF	≤20 × 10 ⁻⁴	≤70 × 10 ⁻⁴	-
Rated voltage pulse slope (dU/dt)R at 615 V:			
P = 15.0 mm		250 V/μs	
P = 22.5 mm		150 V/μs	
P = 27.5 mm		100 V/μs	
R between leads, for C ≤ 0.33 μF at 100 V; 1 minute	>15000 MΩ		
RC between leads, for C > 0.33 µF at 100 V; 1 minute	>5000 s		
R between leads and case; 100 V; 1 minute	>30 000 MΩ		
Withstanding (DC) voltage (cut off current 10 mA); rise time 100 V/s:	3400 V; 1 minute		
Withstanding (AC) voltage between leads and case	2380 V; 1 minute		

MKP 338 1

 $U_{Rac} = 440 \text{ V (X1)}; U_{Rdc} = 1000 \text{ V}$

			CATALOGUE NUMBER				
	DIMENSIONS		LOOSE IN BOX				
			short leads		long leads	TAPED LARGE REEL	
C (μF) b × h × l (mm)	MASS (g)	l _t = 3.5 ±0.3 mm	I _t = 5.0 ±1.0 mm	l _t = 25.0 ±2.0 mm	(500 mm) ⁽¹⁾⁽²⁾		
			C-1	tol = ±20%		C-tol = ±20%	
			catalogue number ⁽³⁾ last 5 digits ⁽³⁾		last 5 digits ⁽³⁾		
Pitch = 15.0 \pm 0.4 mm; d _t = 0.60 \pm 0.06 mm					reel; pitch = 7.5 mm; d _t = 0.60 mm		
0.01			2222 338 10 103	12 103	14103	16 103	
0.015	$5.0\times11.0\times17.5$	1.2	2222 338 10 153	12 153	14153	16 153	
0.022			2222 338 10 223	12 223	14223	16 223	
0.033	6.0 × 12.0 × 17.5	1.4	2222 338 10 333	12 333	14333	16 333	
Pitch = 15.0 \pm 0.4 mm; d _t = 0.80 \pm 0.08 mm					reel; pitch = 7.5 mm; d _t = 0.80 mm		
0.047	$7.0 \times 13.5 \times 17.5$	1.9	2222 338 10 473	12473	14473	16473	
0.068	8.5 × 15.0 × 17.5	2.6	2222 338 10 683	12683	14683	16 683	
0.1	10.0 × 16.5 × 17.5	3.1	2222 338 10 104	12 104	14 104	16 104	
Pitch =	22.5 ±0.4 mm; d _t = 0.80	±0.08 mm					
0.15	$8.5 \times 18.0 \times 26.0$	4.4	2222 338 10 154	12 154	14154		
0.22	10.0 × 19.5 × 26.0	5.5	2222 338 10 224	12 224	14 224	not available	
Pitch = 27.5 \pm 0.4 mm; d _t = 0.80 \pm 0.08 mm							
0.33	13.0 × 23.0 × 31.0	10.4	2222 338 10 334	12 334	14334		
0.47	15.0 × 25.0 × 31.0	12.8	2222 338 10474	12474	14474	not available	
0.68	18.0 × 28.0 × 31.0	17.2	2222 338 10 684	12684	14684		
1	21.0 × 31.0 × 31.0	20.4	2222 338 10 105	12 105	14 105		

Notes

- 1. H = in-tape height; P₀ = sprocket hole distance; for detailed specifications refer to this handbook, chapter "Packaging information".
- 2. For pitch = 7.5 mm (bent back): H = 16.0 mm and $P_0 = 15.0$ mm. The reel diameter = 500 mm; reel diameter = 356 mm is available on request.
- 3. The shading indicates preferred types.

BCcomponents Product specification


Metallized polyester film capacitors

MKP 338 1

CONSTRUCTION

Description

- Low-inductive wound cell of metallized polypropylene (PP) film, potted with epoxy resin in a flame-retardant polypropylene case
- · Radial leads, solder-coated:
 - Copper clad steel wire for original pitch = 15 mm (b ≤ 6 mm)
 - Copper wire for original pitch = 15 (b ≥ 7 mm), 22.5 and 27.5 mm
- Small stand-off pips allow removal of solder flux etc. during cleaning of the printed-circuit board.



Mounting

NORMAL USE

The capacitors are designed for mounting on printed-circuit boards. The capacitors packed in bandoliers are designed for mounting on printed-circuit boards by means of automatic insertion machines.

For detailed tape specifications refer to Type detail specification "HQN-384-01/102, Packaging information"

SPECIFIC METHOD OF MOUNTING TO WITHSTAND VIBRATION AND SHOCK


In order to withstand vibration and shock tests, it must be ensured that the stand-off pips are in good contact with the printed-circuit board:

- For pitches ≤15 mm capacitors shall be mechanically fixed by the leads.
- For larger pitches the capacitors shall be mounted in the same way and the body clamped.

SPACE REQUIREMENTS ON PRINTED-CIRCUIT BOARD

The maximum length and width of film capacitors is shown in Fig.5:

- Eccentricity as in Fig.5. The maximum eccentricity is smaller than or equal to the lead diameter of the product concerned.
- Product height with seating plane as given by "IEC 60717" as reference: h_{max} ≤ h + 0.3 mm.



Storage temperature

Storage temperature: T_{stg} = -25 to +40 °C with RH maximum 80% without condensation.

RATINGS AND CHARACTERISTICS REFERENCE CONDITIONS


Unless otherwise specified, all electrical values apply to an ambient temperature of 23 ± 1 °C, an atmospheric pressure of 86 to 106 kPa and a relative humidity of 50 $\pm 2\%$.

For reference testing, a conditioning period shall be applied over 96 ± 4 hours by heating the products in a circulating air oven at the rated temperature and a relative humidity not exceeding 20%.


MKP 338 1

CHARACTERISTICS

Capacitance




Tangent of loss angle




MKP 338 1

Impedance





Resonant frequency



MKP 338 1

Maximum RMS voltage and AC current (sinewave) as a function of frequency for $T_{amb} \le 100$ °C






10

BCcomponents Product specification

Metallized polyester film capacitors

MKP 338 1

Insulation resistance



APPLICATION NOTES

- For X1 electromagnetic interference suppression in across the line applications (50/60 Hz) with a maximum mains voltage of 440 V (AC).
- These capacitors are not intended for continuous pulse applications. For these situations, capacitors of the AC and pulse program must be used, such as: 2222 375; 2222 383 or 2222 479
- The maximum ambient temperature must not exceed 105 °C.
- Rated voltage pulse slope:
 - If the pulse voltage is lower than the rated voltage, the values of the specific reference data can be multiplied by 615 V (DC) and divided by the applied voltage.


MKP 338 1

MARKING

Product marking

The capacitors are marked by laser print; on the top for pitch \geq 22.5 mm (see Fig.14), or on the top and one side for pitch = 15 mm (see Fig.13) with the following information:

- 1. Rated capacitance code in accordance with "IEC 60062"
- 2. Tolerance on rated capacitance; M = $\pm 20\%$; K = $\pm 10\%$; J = $\pm 5\%$
- 3. Rated (AC) voltage (440 V)
- 4. Sub-class (e.g. X1)
- 5. Manufacturer's type designation (e.g. 338 1)
- 6. Code for dielectric material (MKP)
- 7. Manufacturer
- 8. Year and week of manufacture (e.g. 0020)
- Safety approvals: products will be marked with approvals depending on the available marking space per product. Although all approvals remain valid as indicated in the reference data.







Fig.14 Example of marking for a capacitor with pitch = 22.5 or 27.5 mm.

MKP 338 1

Package marking

The package containing the capacitors is marked as shown Fig.15.



LINE MARKING EXPLANATION 1 Manufacturer's name 2 Country of origin 3 Sub-family Type description and sub class 4 5 Capacitance value, tolerance, voltage and climatic category ("IEC 60068-1") 6 Safety approvals 7 Preference origin code: A Country of origin in code: 170 (Belgium) Responsible production centre: HQ Work order: WO 8 Product type description Quantity and production period, year and 9

Barcode label marking

week code

Product code (12NC)

Fig.15 Barcode label.

10

MKP 338 1

QUICK REFERENCE TEST REQUIREMENTS

TEST	PROCEDURE (quick reference)	REQUIREMENTS				
Robustness of leads						
Tensile strength: "IEC 60068-2-21"	load 10 N; 10 s					
Bending: "IEC 60068-2-21"	load 5 N; 4 × 90 °	no visible damage legible marking				
Resistance to soldering	solder bath: 260 °C; 10 s	∆C/C ≤ 5%				
heat: "IEC 60068-2-20"	solder bath: 350 °C; 3.5 s	Δ tan δ ≤ 80 × 10 ⁻⁴ at 10 kHz				
Component solvent resistance	isopropyl alcohol; 23 °C; 5 minutes					
Robustness of component						
Rapid change of temperature: "IEC 60068-2-14"	5 cycles 1 cycle = 30 minutes at -55 °C and 30 minutes at 100 °C	ΔC/C ≤ 5%				
Vibration: "IEC 60068-2-6"	10 to 55 Hz; amplitude 0.75 mm; 6 hours	Δ tan δ ≤ 80 × 10 ⁻⁴ at 10 kHz				
Shock: "IEC 60068-2-27"	half sinewave; 490 m/s ² ; 11 ms					
Climatic sequence						
Dry heat: "IEC 60068-2-2"	16 hours; 100 °C					
Damp heat, cyclic, test Db, first cycle: "IEC 60068-2-30"		 ∆C/C ≤ 5%				
Cold: "IEC 60068-2-1"	2 hours; –55 °C	Δ tan δ ≤ 80 × 10 ⁻⁴ at 10 kHz				
Damp heat, cyclic, test Db, remaining cycles: "IEC 60068-2-30"		R _{ins} ≥ 50% of specified value				
Voltage proof: "IEC 60384-14"	V _p = 1200 V (DC); 1 minute					
Other applicable tests	the state of the s					
Damp heat, steady state:	21 days; 40 °C; 90 to 95% RH no load V _p = 1200 V (DC); 1 minute	ΔC/C ≤ 5%				
"IEC 60068-2-3"		Δ tan δ ≤ 70 × 10 ⁻⁴				
		R _{ins} ≥ 50% of specified value				
Endurance (AC): "IEC 60384-14"	3×4.0 kV pulse voltage 1000 hours; $1.25 \times U_{Rac}$ at 100 °C; once per hour; 0.1 s;	ΔC/C ≤ 10%				
		Δ tan δ ≤ 80 × 10 ⁻⁴ at 10 kHz				
	1000 V (RMS) via resistor of 47 Ω; $V_p = 1200$ V (DC); 1 minute	R _{ins} ≥ 50% of specified value				

MKP 338 1

TEST	PROCEDURE (quick reference)	REQUIREMENTS
Charge and discharge: "IEC 60384-14"	10000 cycles; 5 ms; 1.5 × dV/dt	$ \Delta C/C \le 10\%$ $\Delta \tan \delta \le 80 \times 10^{-4}$ at 10 kHz $R_{ins} \ge 50\%$ of specified value
Passive flammability: "IEC 60384-14"	class B	no burning
Active flammability: "IEC 60384-14"	20 × 4 kV discharge	no burning
Heat storage: "IEC 60384-14"	1000 hours; 100 °C	$ \Delta C/C \le 5\%$ $\Delta \tan \delta \le 80 \times 10^{-4} \text{ at } 10 \text{ kHz}$
Resistance to soldering heat with preheating: "IEC 60384-14"	preheating: 100 °C; solder bath: 260 °C; 10 s	$ \Delta C/C \le 5\%$ $\Delta \tan \delta \le 80 \times 10^{-4}$ at 10 kHz
Active flammability test	Voltage proof up to 2 × peak impulse voltage of 4.13 or until breakdown (100 V/sec, current limited 2mA) Failed capacitors connected to a 250 V (AC) power supply during 5 minutes	no burning