





NOTES
1. MATERIAL : HEADER - PA66
2. FINISHES : PIN : BRASS(CDA 2700)
THICKNESS - TIN-LEAD(Sn-Pb) 3.0 MICROMETER MIN.
OVER Cu 1.5 MICROMETER MIN.

3. MATES WITH : 35977-****
4. PRODUCT SPECIFICATION : PS-35978-001

LEGEND
35978-****
COLOR : 0 - WHITE
1 - BLACK
2 - RED
3 - YELLOW
4 - BLUE
MATERIAL 7 : PA66 ⑧ : PC/PET
CONSECUTIVE No.



				0	0	0	0	X	0	20.86	19.80	23.76	3597804**	35978-04**	5	6	⑧
				0	0	0	0	X	0	36.70	35.64	39.6	3597803**	35978-03**	9	10	
								0	0	12.94	11.88	15.84	3597802**	35978-02**	3	4	
								0	X	12.94	11.88	15.84	3597801**	35978-01**	2	4	
10	9	8	7	6	5	4	3	2	1								
CKT NO.										C	B	A	MAT'L NO	ENG NO.	CKT	N	

REVISED

EC NO: KOR2010-0138

DRWN: JHPARK01 2010/03/08

CHKD: WY. YANG 2010/03/22

APPR: YUNS IKK IM 2010/03/22

DESCRIPTION

REV

QUALITY SYMBOLS

▽=0

▽C=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±---
2 PLACES	±---	±---
1 PLACE	±0.2	±---

ANGULAR ± 1 °

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE

MM ONLY

DRAWN BY	DATE
YR. WI	2000/09/30
CHECKED BY	DATE
JK. OJ	2000/09/30
APPROVED BY	DATE
CW. LEE	2000/09/30

MATERIAL NO.

SEE TABLE

SIZE A3

SCALE

3.5:1

DESIGN UNITS

METRIC

THIRD ANGLE PROJECTION

TITLE

3.96 PITCH W-T-B CONN. HEADER ASS'Y (VOID)

MOLEX INCORPORATED

DOCUMENT NO.

SD-35978-003

SHEET NO.

1 OF 01