

Fig. 1




Fig. 2




Fig. 3




Fig. 4





Fig. 5

- Series 350 & 450 single and double row headers use MM #0290 pins. See page 182 for details.
- Series 801 & 803 single and double row low profile sockets use MM #1303 pins. See page 150 for details.
- Series 801 and 803 receptacles use Hi-Rel, 6-finger BeCu #16 contacts rated at 4.5 amps. Receptacles accept .025" diameter and .025" square pins. See page 221 for details.

- Insulators are high temp. thermoplastic.



Ordering Information

Fig. 1	Single Row .025 Pin / .018 Solder Tail				
	350-XX-1 _ _ -00-001000 Specify # of pins └───> 01-64				
Fig. 2	Double Row .025 Pin / .018 Solder Tail				
	450-XX-2 _ _ -00-001000 Specify # of pins └───> 02-64				
For Electrical, Mechanical & Environmental Data, See pg. 4 XX=Plating Code See Below For RoHS compliance select ◇ plating code.					
SPECIFY PLATING CODE XX=		10◇	90	40◇	
Pin Plating 		10μ" Au	200μ" Sn/Pb	200μ" Sn	
Fig. 3	Single Row Low Profile Socket (short insulator)				
	801-43-0 _ _ -10-003000 Specify # of pins └───> 01-64				
Fig. 4	Single Row Low Profile Socket (long insulator)				
	801-43-0 _ _ -10-013000 Specify # of pins └───> 01-36				
Fig. 5	Double Row Low Profile Socket				
	803-43-0 _ _ -10-003000 Specify # of pins └───> 02-72				
For Electrical, Mechanical & Environmental Data, See pg. 4 For RoHS compliance select ◇ plating code.					
PLATING CODE =					43◇
Sleeve (Pin) 					200μ" Sn
Contact (Clip) 					30μ" Au