



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		B	ECR-09-006452	30/03/09	AM	JS



- NOTES:
- FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE.
 - ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED.
 - FOR PACKAGING DETAILS SEE SHEET 2.
 - MATERIAL: BODY - BRASS
SLEEVE - PVC (K65), 94V-0
 - APPLICATION SPEC 114-13196

2-1838215-0	1.5mmsq - 2.5mmsq 16-14(AWG)	6.4x0.8mm STANDARD ENTRY	BLUE FEMALE PUSH-ON TERMINAL (INSULATED)	2000	1000	6.70	22.00	4.90	11.00	0.40	0.80	1.5mmsq - 2.5mmsq 16-14(AWG)	6.40 X 0.8	BLUE FEMALE PUSH-ON TERMINAL (INSULATED)	2-1838215-0
1-1838215-0				3500	100										1-1838215-0
STOCK NUMBER	PACKING LABEL DESCRIPTION LINE 3	PACKING LABEL DESCRIPTION LINE 2	PACKING LABEL DESCRIPTION LINE 1	INNER CARTON QTY	QTY	B (±0.30)	L (±1.50)	D (±0.50)	E (±0.50)	t (±0.10)	t1 (±0.20)	WIRE SIZE (mmsq) & (AWG)	SIZE (mm)	DESCRIPTION	PART No
DIMENSIONS															

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± 0.5
1 PLC ± 0.2
2 PLC ± 0.1
3 PLC ± 0.015
4 PLC ± -
ANGLES ± -
FINISH
-

DWN
K.Raghunandan
CHK
S. Parlow
APVD
F. Wheeler-King
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
-

18AUG05
02/04/07
02/04/07

NAME
EURO-CRIMP INSULATED BLUE FEMALE PUSH-ON TERMINAL
1.5mmsq - 2.5mmsq / 16-14 AWG RANGE

SCALE
NTS

SHEET
1

OF
2

REV
B

Tyco Electronics
Bideford, UK, EX39 4HE

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1838215

RESTRICTED TO
-

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 18AUG ,2005. ALL RIGHTS RESERVED.

LOC E DIST B

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

BOX LABEL FIG 1

75
25
60
2
3
LINE 1
PART NUMBER
4
5
LINE 2
6
LINE 3
7
QTY:
8
UL
1
9
10

BOX FIG 2

80
55
35
1
2

LABEL NOTES:

1. PERFORATED LINE: DOTTED LINE TO BE ALIGNED WITH OPENING EDGE & FOLDED TO LEFT SIDE OF BOX.

2. LOGO: USE LATEST REVISION OF TYCO COMPANY LOGO.

3. LINE1: SEE SHEET 1, USE TEXT FROM COLUMN PACKAGING LABEL DESCRIPTION LINE 1.

4. PART NUMBER: FOR 1--0 & 2--0 USE TYCO PART NUMBER.
1--0 = 1-1838215-0
2--0 = 2-1838215-0

5. LINE 2: SEE SHEET 1, USE TEXT FROM COLUMN PACKAGING LABEL DESCRIPTION LINE 2.

6. LINE 3: SEE SHEET 1, USE TEXT FROM COLUMN PACKAGING LABEL DESCRIPTION LINE 3.

7. QTY: SEE SHEET 1, USE NUMBER FROM THE COLUMN QTY.

8. EAN BARCODE. USE LATEST TYCO BARCODE SUPPLIED.
1--0 = TYCO BARCODE
2--0 = TYCO BARCODE

9. UL: WHERE APPLICABLE USE UL LOGO, SEE SHEET 1.

10. PRODUCT PICTURE: A PRODUCT PICTURE IS REQUIRED.

BOX NOTES:

1. EURO SLOT: TO BE POSITIONED TO CENTRE ON FRONT COVER.

2. BOX HINGE: FRONT COVER TO BE HINGED ON RIGHT SIDE.

3. SPECIFICATION: COVER TO BE FREE FROM POSSIBLE WARPING & CAPABLE OF BEING RE-SEALED MIN 100 TIMES.

4. LABEL: CORRECT CUSTOMER BOX LABEL TO BE POSITIONED ON THE FRONT COVER WITH THE PERFORATED EDGE ON THE LEFT HAND SIDE.

PACK SPECIFICATION:

1. CLEAR PLASTIC BOX: PART NUMBER 1--0 TO BE PACKED 100 PARTS PER CLEAR PLASTIC BOX (FIG2) WITH THE CORRECT CUSTOMER LABEL (FIG1), 35 CLEAR PLASTIC BOXES OF THE SAME PART NUMBER ARE TO BE PACKED INTO A SUITABLE INNER CARTON BOX.

2. CLEAR PLASTIC BAG: PART NUMBER 2--0, USE A SUITABLE CLEAR PLASTIC BAG FOR A 2000 PARTS, POSITION AN APPROPRIATE LABEL AS IN FIG1 BUT WITHOUT THE PERFORATED SIDE, CENTRE OF BAG. 2 BAGS ARE THEN TO BE PACKED INTO A SUITABLE INNER CARTON BOX.

3. INNER CARTON LABEL: LABEL AS PER CLEAR PLASTIC BAG NOTE 2 BUT WITH INNER CARTON QTY 2000 TO BE POSITIONED ON THE SIDE OF THE BOX FOR VIEWING WHEN STORED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 18AUG05 K.Raghunandan	Tyco Electronics Corporation Bideford, UK, EX39 4HE	
DIMENSIONS: mm		CHK 02/04/07 S. Parlow	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 02/04/07 F. Wheeler-King	EURO-CRIMP INSULATED BLUE FEMALE PUSH-ON TERMINAL 1.5mmsq - 2.5mmsq / 16-14 AWG RANGE	
0 PLC ± 0.5 1 PLC ± 0.2 2 PLC ± 0.1 3 PLC ± 0.015 4 PLC ± - ANGLES ± -		PRODUCT SPEC — APPLICATION SPEC —	SIZE A2	CAGE CODE 00779
MATERIAL —		WEIGHT —	DRAWING NO C-1838215	RESTRICTED TO —
FINISH —		CUSTOMER DRAWING		
SCALE NTS		SHEET 2 OF 2 REV B		