



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		C	ECR-09-006452	30/03/09	AM	JS



- NOTES:
- FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE.
 - ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED.
 - FOR PACKAGING DETAILS SEE SHEET 2.
 - MATERIAL: BODY - BRASS
SLEEVE - PVC (K65), 94V-0
 - APPLICATION SPEC 114-13196

2-1838216-0	4.0mmsq - 6.0mmsq	6.4x0.8mm STANDARD ENTRY	YELLOW FEMALE PUSH-ON TERMINAL (INSULATED)	1500	500	6.70	25.00	6.50	14.00	0.40	0.80	4.0mmsq - 6.0mmsq 12-10(AWG)	6.40 X 0.8	YELLOW FEMALE PUSH-ON TERMINAL (INSULATED)	2-1838216-0
1-1838216-0	12-10(AWG)			1750	50										1-1838216-0
STOCK NUMBER	PACKING LABEL DESCRIPTION LINE 3	PACKING LABEL DESCRIPTION LINE 2	PACKING LABEL DESCRIPTION LINE 1	INNER CARTON QTY	QTY	B (±0.30)	L (±1.50)	D (±0.50)	E (±0.50)	t (±0.10)	t1 (±0.20)	WIRE SIZE (mmsq) & (AWG)	SIZE (mm)	DESCRIPTION	PART No
						DIMENSIONS									

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

MATERIAL -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± 0.5
1 PLC ± 0.2
2 PLC ± 0.1
3 PLC ± 0.015
4 PLC ± -
ANGLES ± -
FINISH -

FINISH -

DWN 18AUG05
CHK K.Raghunandan
S. Parlow
APVD 02/04/07
F. Wheeler-King
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -

18AUG05
02/04/07
EUR
-
-
-

CUSTOMER DRAWING

Tyco Electronics Corporation
Bideford, UK, EX39 4HE

NAME
O-CRIMP INSULATED YELLOW FEMALE PUSH-ON TERMINAL
4.0mmsq - 6.0mmsq / 12-10 AWG RANGE

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1838216


RESTRICTED TO
-

SCALE
NTS

SHEET
1

OF
2

REV
C



- LABEL NOTES:

1. PERFORATED LINE:

DOTTED LINE TO BE ALIGNED WITH OPENING EDGE & FOLDED TO LEFT SIDE OF BOX.

2. LOGO:

USE LATEST REVISION OF TYCO COMPANY LOGO.

3. LINE1:

SEE SHEET 1, USE TEXT FROM COLUMN PACKAGING LABEL DESCRIPTION LINE 1.

4. PART NUMBER:

FOR 1--0 & 2--0 USE TYCO PART NUMBER.
1--0 = 1-1838216-0
2--0 = 2-1838216-0

5. LINE 2:

SEE SHEET 1, USE TEXT FROM COLUMN PACKAGING LABEL DESCRIPTION LINE 2.

6. LINE 3:

SEE SHEET 1, USE TEXT FROM COLUMN PACKAGING LABEL DESCRIPTION LINE 3.

7. QTY:

SEE SHEET 1, USE NUMBER FROM THE COLUMN QTY.

8. EAN BARCODE.

USE LATEST TYCO BARCODE SUPPLIED.
1--0 = TYCO BARCODE
2--0 = TYCO BARCODE

9. UL:

WHERE APPLICABLE USE UL LOGO, SEE SHEET 1.

10. PRODUCT PICTURE:

A PRODUCT PICTURE IS REQUIRED.
- BOX NOTES:

1. EURO SLOT:

TO BE POSITIONED TO CENTRE ON FRONT COVER.

2. BOX HINGE:

FRONT COVER TO BE HINGED ON RIGHT SIDE.

3. SPECIFICATION:

COVER TO BE FREE FROM POSSIBLE WARPING & CAPABLE OF BEING RE-SEALED MIN 100 TIMES.

4. LABEL:

CORRECT CUSTOMER BOX LABEL TO BE POSITIONED ON THE FRONT COVER WITH THE PERFORATED EDGE ON THE LEFT HAND SIDE.
- PACK SPECIFICATION:

1. CLEAR PLASTIC BOX:

PART NUMBER 1--0 TO BE PACKED 50 PARTS PER CLEAR PLASTIC BOX (FIG2) WITH THE CORRECT CUSTOMER LABEL (FIG1), 35 CLEAR PLASTIC BOXES OF THE SAME PART NUMBER ARE TO BE PACKED INTO A SUITABLE INNER CARTON BOX.

2. CLEAR PLASTIC BAG:

PART NUMBER 2--0, USE A SUITABLE CLEAR PLASTIC BAG FOR 500 PARTS, POSITION AN APPROPRIATE LABEL AS IN FIG1 BUT WITHOUT THE PERFORATED SIDE, CENTRE OF BAG. 3 BAGS ARE THEN TO BE PACKED INTO A SUITABLE INNER CARTON BOX.

3. INNER CARTON LABEL:

LABEL AS PER CLEAR PLASTIC BAG NOTE 2 BUT WITH INNER CARTON QTY 1500 TO BE POSITIONED ON THE SIDE OF THE BOX FOR VIEWING WHEN STORED.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

18AUG05

K.Raghunandan

CHK

02/04/07

S. Parlow

APVD

02/04/07

F. Wheeler-King

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING

DIMENSIONS:

mm

MATERIAL

—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC

± 0.5

1 PLC

± 0.2

2 PLC

± 0.1

3 PLC

± 0.015

4 PLC

± —

ANGLES

± —

FINISH

—

NAME

—

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=1838216

—

SCALE

NTS

SHEET

2

OF

2

REV

C

Tyco Electronics Corporation
Bideford, UK, EX39 4HE

0-CRIMP INSULATED YELLOW FEMALE PUSH-ON TERMINAL
4.0mmsq - 6.0mmsq / 12-10 AWG RANGE