




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		B	ECR-09-006452	30/03/09	AM	JS



- NOTES:
- FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE.
 - ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED.
 - FOR PACKAGING DETAILS SEE SHEET 2.
 - MATERIAL: BODY - BRASS
SLEEVE - PVC (K65), 94V-0
 - APPLICATION SPEC 114-13196

2-1838219-0	0.5mmsq - 1.5mmsq	4.8x0.8 mm STANDARD ENTRY	RED FEMALE PUSH-ON TERMINAL	2000	1000	5.00	7.40	20.50	4.10	10.50	0.40	0.80	0.5mmsq - 1.5mmsq	4.80 X 0.8	RED FEMALE PUSH-ON TERMINAL	2-1838219-0
1-1838219-0	22-16(AWG)		(FULLY INSULATED)	3500	100								22-16(AWG)		(FULLY INSULATED)	1-1838219-0
STOCK NUMBER	PACKING LABEL DESCRIPTION LINE 3	PACKING LABEL DESCRIPTION LINE 2	PACKING LABEL DESCRIPTION LINE 1	INNER CARTON QTY	QTY	DIMENSIONS							WIRE SIZE (mmsq) & (AWG)	SIZE (mm)	DESCRIPTION	PART No
						B (±0.30)	b (±0.50)	L (±1.50)	D (±0.50)	E (±1.50)	t (±0.10)	t1 (±0.20)				

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

MATERIAL -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± 0.5
1 PLC ± 0.2
2 PLC ± 0.1
3 PLC ± 0.015
4 PLC ± -
ANGLES ± -
FINISH -

DWN 12AUG05 K.Raghunandan
CHK 02/04/07 S. Parlow
APVD 02/04/07 F. Wheeler-King
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -


CUSTOMER DRAWING

Tyco Electronics Corporation
Bideford, UK, EX39 4HE

NAME
EURO-CRIMP FULLY INSULATED
RED FEMALE PUSH-ON TERMINAL
0.5mmsq - 1.5mmsq / 22-16 AWG RANGE

SIZE A2
CAGE CODE 00779
DRAWING NO C=1838219
RESTRICTED TO -

SCALE NTS
SHEET 1 OF 2
REV B



BOX NOTES:

- | | |
|---|--|
| 1.  EURO SLOT: | TO BE POSITIONED TO CENTRE ON FRONT COVER. |
| 2.  BOX HINGE: | FRONT COVER TO BE HINGED ON RIGHT SIDE. |
| 3. SPECIFICATION: | COVER TO BE FREE FROM POSSIBLE WARPING & CAPABLE OF BEING RE-SEALED MIN 100 TIMES. |
| 4. LABEL: | CORRECT CUSTOMER BOX LABEL TO BE POSITIONED ON THE FRONT COVER WITH THE PERFORATED EDGE ON THE LEFT HAND SIDE. |

PACK SPECIFICATION:

- | | |
|------------------------|--|
| 1. CLEAR PLASTIC BOX: | PART NUMBER 1--0 TO BE PACKED 100 PARTS PER CLEAR PLASTIC BOX (FIG2) WITH THE CORRECT CUSTOMER LABEL (FIG1), 35 CLEAR PLASTIC BOXES OF THE SAME PART NUMBER ARE TO BE PACKED INTO A SUITABLE INNER CARTON BOX. |
| 2. CLEAR PLASTIC BAG: | PART NUMBER 2--0, USE A SUITABLE CLEAR PLASTIC BAG FOR A 1000 PARTS, POSITION AN APPROPRIATE LABEL AS IN FIG1 BUT WITHOUT THE PERFORATED SIDE, CENTRE OF BAG. 2 BAGS ARE THEN TO BE PACKED INTO A SUITABLE INNER CARTON BOX. |
| 3. INNER CARTON LABEL: | LABEL AS PER CLEAR PLASTIC BAG NOTE 2 BUT WITH INNER CARTON QTY 2000 TO BE POSITIONED ON THE SIDE OF THE BOX FOR VIEWING WHEN STORED. |

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.RaghuNandan		12AUG05		Tyco Electronics Corporation		Tyco Electronics Corporation	
		CHK S. Parlow		02/04/07		Tyco Electronics		Bideford, UK, EX39 4HE	
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD S. Wheeler-King		02/04/07		NAME	
		0 PLC ± 0.5		PRODUCT SPEC		CRIMP FULLY INSULATED RED FEMALE PUSH-ON TERMINAL			
		1 PLC ± 0.2		—		0.5mmsq – 1.5mmsq / 22-16 AWG RANGE			
		2 PLC ± 0.1		APPLICATION SPEC		SIZE		CAGE CODE	DRAWING NO
		3 PLC ± 0.015		—		A2		00779	C=1838219
		4 PLC ± —		—		RESTRICTED TO		—	
MATERIAL		FINISH		WEIGHT		—		—	
—		—		—		—		—	
CUSTOMER DRAWING						SCALE		NTS	SHEET 2 OF 2
								REV	B