


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		B	ECR-09-006452	30/03/09	AM	JS



- NOTES:
- FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE.
 - ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED.
 - FOR PACKAGING DETAILS SEE SHEET 2.
 - MATERIAL: BODY - BRASS
SLEEVE - PVC (K65), 94V-0
 - APPLICATION SPEC 114-13196

2-1838228-0	0.5mmsq-1.5mmsq	6.4x0.8mm STANDARD ENTRY	RED PIGGY BACK TERMINAL (INSULATED)	1500	500	6.80	6.35	22.50	4.10	10.50	0.40	0.80	0.5mmsq-1.5mmsq	6.4 X 0.8	RED PIGGY BACK TERMINAL (INSULATED)	2-1838228-0
1-1838228-0	22-16 (AWG)			1750	50								22-16(AWG)			1-1838228-0
STOCK NUMBER	PACKING LABEL DESCRIPTION LINE 3	PACKING LABEL DESCRIPTION LINE 2	PACKING LABEL DESCRIPTION LINE 1	INNER CARTON QTY	QTY	B (±0.30)	b (±0.20)	L (±1.50)	D (±0.50)	E (±0.50)	t (±0.10)	t1 (±0.20)	WIRE SIZE (mmsq) & (AWG)	SIZE (mm)	DESCRIPTION	PART No
DIMENSIONS																

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

MATERIAL -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± 0.5
1 PLC ± 0.2
2 PLC ± 0.1
3 PLC ± 0.015
4 PLC ± -
ANGLES ± -
FINISH -

FINISH -

DWN 25AUG05 K.Raghunandan
CHK 03/04/07 S. Parlow
APVD 03/04/07 F. Wheeler-King
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

CUSTOMER DRAWING

Tyco Electronics Tyco Electronics Corporation Bideford, UK, EX39 4HE

NAME EURO-CRIMP INSULATED RED PIGGY BACK TERMINAL 0.5mmsq-1.5mmsq / 22-16 AWG RANGE

SIZE A2 CAGE CODE 00779 DRAWING NO C=1838228 RESTRICTED TO -

SCALE NTS SHEET 1 OF 2 REV B

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

25AUG ,2005.

© COPYRIGHT

2005

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

E

B

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—

BOX LABEL FIG 1

75

25

80

2

3

4

5

6

7

8

LINE 1

PART NUMBER

LINE 2

LINE 3

QTY:

UL

1

9

10

BOX FIG 2

1

2

80

55

35

LABEL NOTES:

1.

PERFORATED LINE:

2.

LOGO:

3.

LINE1:

4.

PART NUMBER:

5.

LINE 2:

6.

LINE 3:

7.

QTY:

8.

EAN BARCODE.

9.

UL:

10.

PRODUCT PICTURE:

DOTTED LINE TO BE ALIGNED WITH OPENING EDGE & FOLDED TO LEFT SIDE OF BOX.

USE LATEST REVISION OF TYCO COMPANY LOGO.

SEE SHEET 1, USE TEXT FROM COLUMN PACKAGING LABEL DESCRIPTION LINE 1.

FOR 1--0 & 2--0 USE TYCO PART NUMBER.
1--0 = 1-1838228-0
2--0 = 2-1838228-0

SEE SHEET 1, USE TEXT FROM COLUMN PACKAGING LABEL DESCRIPTION LINE 2.

SEE SHEET 1, USE TEXT FROM COLUMN PACKAGING LABEL DESCRIPTION LINE 3.

SEE SHEET 1, USE NUMBER FROM THE COLUMN QTY.

USE LATEST TYCO BARCODE SUPPLIED.
1--0 = TYCO BARCODE
2--0 = TYCO BARCODE

WHERE APPLICABLE USE UL LOGO, SEE SHEET 1.

A PRODUCT PICTURE IS REQUIRED.

BOX NOTES:

1.

EURO SLOT:

2.

BOX HINGE:

3.

SPECIFICATION:

4.

LABEL:

TO BE POSITIONED TO CENTRE ON FRONT COVER.

FRONT COVER TO BE HINGED ON RIGHT SIDE.

COVER TO BE FREE FROM POSSIBLE WARPING & CAPABLE OF BEING RE-SEALED MIN 100 TIMES.

CORRECT CUSTOMER BOX LABEL TO BE POSITIONED ON THE FRONT COVER WITH THE PERFORATED EDGE ON THE LEFT HAND SIDE.

PACK SPECIFICATION:

1.

CLEAR PLASTIC BOX:

2.

CLEAR PLASTIC BAG:

3.

INNER CARTON LABEL:

PART NUMBER 1--0 TO BE PACKED 50 PARTS PER CLEAR PLASTIC BOX (FIG2) WITH THE CORRECT CUSTOMER LABEL (FIG1), 35 CLEAR PLASTIC BOXES OF THE SAME PART NUMBER ARE TO BE PACKED INTO A SUITABLE INNER CARTON BOX.

PART NUMBER 2--0, USE A SUITABLE CLEAR PLASTIC BAG FOR 500 PARTS, POSITION AN APPROPRIATE LABEL AS IN FIG1 BUT WITHOUT THE PERFORATED SIDE, CENTRE OF BAG. 3 BAGS ARE THEN TO BE PACKED INTO A SUITABLE INNER CARTON BOX.

LABEL AS PER CLEAR PLASTIC BAG NOTE 2 BUT WITH INNER CARTON QTY 1500 TO BE POSITIONED ON THE SIDE OF THE BOX FOR VIEWING WHEN STORED.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

0 PLC ± 0.5

1 PLC ± 0.2

2 PLC ± 0.1

3 PLC ± 0.015

4 PLC ± -

ANGLES ± -

FINISH

-

DWN

25AUG05

K.Raghu

CHK

03/04/07

S. Parlow

APVD

03/04/07

F. Wheeler-King

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING

Tyco Electronics

Tyco Electronics Corporation

Bideford, UK, EX39 4HE

NAME

EURO-CRIMP INSULATED RED PIGGY BACK TERMINAL

0.5mmsq-1.5mmsq / 22-16 AWG RANGE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=1838228

—

SCALE

NTS

SHEET

2

OF

2

REV

B

AMP 1471-9 REV 31MAR2000

1838228