

PRODUCT NUMBER  
76341-YYYZ





OPTIONAL LETTER  
H: HIGH TEMPERATURE PRODUCT.

NUMBER OF POSITIONS: 02 TO 50.

PLATING CODE  
3= 0.76µm GOLD ON CONTACT AREA.  
3.81µm TIN-LEAD ON TAIL.  
4= 5µm TIN-LEAD ON CONTACT AREA.  
3.81µm TIN-LEAD ON TAIL.

NOTES:

- 1 - HOUSING MAT'L: THERMOPLASTIC GLASS FILLED  
FLAME RETARDANT PER UL 94 V-0  
LOW TEMPERATURE: COLOR BLUE  
HIGH TEMPERATURE: COLOR GREY.
- 2 - TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 - 2 UP TO 4 POSITIONS PRODUCT PACKED IN PLASTIC BOX.  
5 UP TO 50 POSITIONS PRODUCT PACKED IN TUBE.
- 4 - TO DETERMINE DIMENSIONS:  
N = NUMBER OF POSITIONS  
EXAMPLE: 8 POS:  $(N \times 2.54) - 0.08 = 20.24$  mm



mat'l code				tolerances unless otherwise specified		CUSTOMER COPY		FPC ELECTRONICS	
SEE NOTES						CDPY		www.fpcconnect.com	
lir	ecn no	dr	date	linear		projection		title	
G	F10030	PVA	91.02.28					BtB RECEPT.	
H	F80711	PNZ	98.10.11					VERT SR TMT	
J	F80115	PNZ	98.01.22	angles					
K	F10110	GCO	01.01.16	chr	P.NIZZI	98.10.11	mm	product family	DUBOX
L	F03-0284	DLE	03.10.07	engr	JM.PHAMVAN	98.10.11		size	dwg no
				chr	P.NIZZI	98.10.11		scale	5:1
				appd	JM.P	98.10.11			
sheet index	revision sheet	L	1					A3	76341
									code 213
									sheet 1 of 1