



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		B	ECR-07-013161	30/04/07	AM	FWK



- NOTES:
- FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE.
 - ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED.
 - FOR PACKAGING DETAILS SEE SHEET 2.
 - MATERIAL: BODY - BRASS
SLEEVE - PVC (K65), 94V-0
 - APPLICATION SPEC 114-13196

2-1838230-0	4.0mmsq-6.0mmsq	6.4x0.8mm STANDARD ENTRY	YELLOW PIGGY BACK TERMINAL (INSULATED)	1000	500	6.80	6.35	25.00	6.50	14.00	0.40	0.80	4.0mmsq-6.0mmsq	6.4 X 0.8	YELLOW PIGGY BACK TERMINAL (INSULATED)	2-1838230-0
1-1838230-0	12-10 (AWG)			1750	50								12-10(AWG)			1-1838230-0
STOCK NUMBER	PACKING LABEL DESCRIPTION LINE 3	PACKING LABEL DESCRIPTION LINE 2	PACKING LABEL DESCRIPTION LINE 1	INNER CARTON QTY	QTY	B (±0.30)	b (±0.20)	L (±1.50)	D (±0.50)	E (±0.50)	t (±0.10)	t1 (±0.20)	WIRE SIZE (mmsq) & (AWG)	SIZE (mm)	DESCRIPTION	PART No
DIMENSIONS																

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

MATERIAL -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± 0.5
1 PLC ± 0.2
2 PLC ± 0.1
3 PLC ± 0.015
4 PLC ± -
ANGLES ± -
FINISH -

DWN 25AUG05 K.Raghunandan

CHK 03/04/07 S. Parlow

APVD 03/04/07 F. Wheeler-King

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -


CUSTOMER DRAWING

tyco Tyco Electronics Corporation
Electronics Bideford, UK, EX39 4HE

NAME EURO-CRIMP
INSULATED YELLOW PIGGY BACK TERMINAL
4.0mmsq-6.0mmsq / 12-10 AWG RANGE

SIZE A2 CAGE CODE 00779 DRAWING NO C=1838230 RESTRICTED TO -

SCALE NTS SHEET 1 OF 2 REV B



LABEL NOTES:

1.

PERFORATED LINE:

DOTTED LINE TO BE ALIGNED WITH OPENING EDGE & FOLDED TO LEFT SIDE OF BOX.
2.

LOGO:

USE LATEST REVISION OF TYCO COMPANY LOGO.
3.

LINE1:

SEE SHEET 1, USE TEXT FROM COLUMN PACKAGING LABEL DESCRIPTION LINE 1.
4.

PART NUMBER:

FOR 1--0 & 2--0 USE TYCO PART NUMBER.
1--0 = 1-1838230-0
2--0 = 2-1838230-0
5.

LINE 2:

SEE SHEET 1, USE TEXT FROM COLUMN PACKAGING LABEL DESCRIPTION LINE 2.
6.

LINE 3:

SEE SHEET 1, USE TEXT FROM COLUMN PACKAGING LABEL DESCRIPTION LINE 3.
7.

QTY:

SEE SHEET 1, USE NUMBER FROM THE COLUMN QTY.
8.

EAN BARCODE.

USE LATEST TYCO BARCODE SUPPLIED.
1--0 = TYCO BARCODE
2--0 = TYCO BARCODE
9.

UL:

WHERE APPLICABLE USE UL LOGO, SEE SHEET 1.
10.

PRODUCT PICTURE:

A PRODUCT PICTURE IS REQUIRED.

BOX NOTES:

1.

EURO SLOT:

TO BE POSITIONED TO CENTRE ON FRONT COVER.
2.

BOX HINGE:

FRONT COVER TO BE HINGED ON RIGHT SIDE.
3.

SPECIFICATION:

COVER TO BE FREE FROM POSSIBLE WARPING & CAPABLE OF BEING RE-SEALED MIN 100 TIMES.
4.

LABEL:

CORRECT CUSTOMER BOX LABEL TO BE POSITIONED ON THE FRONT COVER WITH THE PERFORATED EDGE ON THE LEFT HAND SIDE.

PACK SPECIFICATION:

1.

CLEAR PLASTIC BOX:

PART NUMBER 1--0 TO BE PACKED 50 PARTS PER CLEAR PLASTIC BOX (FIG2) WITH THE CORRECT CUSTOMER LABEL (FIG1), 35 CLEAR PLASTIC BOXES OF THE SAME PART NUMBER ARE TO BE PACKED INTO A SUITABLE INNER CARTON BOX.
2.

CLEAR PLASTIC BAG:

PART NUMBER 2--0, USE A SUITABLE CLEAR PLASTIC BAG FOR 500 PARTS, POSITION AN APPROPRIATE LABEL AS IN FIG1 BUT WITHOUT THE PERFORATED SIDE, CENTRE OF BAG. 2 BAGS ARE THEN TO BE PACKED INTO A SUITABLE INNER CARTON BOX.
3.

INNER CARTON LABEL:

LABEL AS PER CLEAR PLASTIC BAG NOTE 2 BUT WITH INNER CARTON QTY 1000 TO BE POSITIONED ON THE SIDE OF THE BOX FOR VIEWING WHEN STORED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.Raghunandan	25AUG05	tyco Electronics		Tyco Electronics Corporation	
		CHK S. Parlow	03/04/07			Bideford, UK, EX39 4HE	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		EURO-CRIMP	
		0 PLC ± 0.5		APVD F. Wheeler-King		INSULATED YELLOW PIGGY BACK TERMINAL	
		1 PLC ± 0.2		PRODUCT SPEC		4.0mmsq-6.0mmsq / 12-10 AWG RANGE	
		2 PLC ± 0.1		APPLICATION SPEC		SIZE	RESTRICTED TO
		3 PLC ± 0.015				CAGE CODE	
		4 PLC ± -				DRAWING NO	
		ANGLES ± -					
MATERIAL		FINISH		WEIGHT		A2 00779 C=1838230	
				CUSTOMER DRAWING		SCALE	REV
						NTS	B
						SHEET	
						2	
						2	