pro-signal	PART NO.	REVISIONS								
		ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
		-	А	RELEASED	NOO	08/6/12	SHA	08/6/12		22/6/12
824 18		Feat • Colo • Hous • Seal • Wav	our sing ma led bas	: Black aterial : Noryl						
Tolerance: ±0.5										

Dimensions : Millimetres

All data at 25°C unless otherwise specified

Specifications	ABI-007-RC Piezo Indicator			
Rated Voltage	12 V dc			
Operating Voltage	3 to 16 V dc			
Rated Current at Rated Voltage	8 mA			
Sound Output at 30 cm, at Rated Voltage	≥90 dB			
Resonant Frequency at Rated Voltage	3,700 ± 500 Hz			
Operating Temperature	-20 to +60°C			
Storage Temperature	-30 to +80°C			
Weight	5 g			

Part Number Table

Description	Part Number			
Piezo Buzzer, 12 V dc, PCB	ABI-007-RC			

www.element14.com www.farnell.com www.newark.com www.cpc.co.uk

Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any	TOLERANCES:	DRAWN BY:	DATE:	DRAWING TITLE:				
	UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	NOO	08/06/12	Piezo Buzzer				
		CHECKED BY:	DATE:	SIZE DWG NO.	XXX	ELECTRONIC FILE	REV A	
		SHA	08/06/12	Α		356845 DWG		
		APPROVED BY:	DATE:					
			22/06/12	SCALE: NTS	U.O.M.: mm	SHEET: 1 OI	F 1	