

4

DRAWING MADE IN THIRD ANGLE PROJECTION

3

2

1

LOC CM DIST 53

© COPYRIGHT

REVISIONS

P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
✓	✓		R	REVISED PER ECR-12-013323	10AUG12	TM

.005 MAX
A
SWAGE
DETAIL D
.790
SEE DETAIL D
.023 MIN
2 PLC
.015 MAX
CUT-OFF TAB
.165
REF.

.130
.105

SECTION A-A

POINT OF MEASUREMENT

.0840
.0815 DIA

.180
.090
.125
.055
A
B
A
B

.170
.145

SECTION B-B

① PLATED WITH .000030 GOLD, OVER .000050 NICKEL UNDERPLATE

② PLATED INTERNALLY WITH .000030 GOLD.

③ INSULATION RANGE: .060-.130 DIA

GOLD	①	.012 BRASS	350547-7
		.012 PH. BRZ	350547-6
PRE-TIN		.012 PH. BRZ.	350547-3
GOLD	①/②	.012 BRASS	350547-2
PRE-TIN			350547-1
FINISH		MATERIAL	PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .015 ANGLES ±	CONTRACT NO	
	DR	M. FEHER 5-6-81
	CHK	D.S. Heisle 6/9/81
	APPD	R. Polaski 6-10-81
WIRE RANGE	20-14 AWG	
INSULATION RANGE	③	
	DSGN APPD	
	OTHER APPD	

TE Connectivity

NAME PIN, (LOOSE PIECE)
UNIVERSAL MATE-N-LOK

SIZE	CODE IDENT NO	DRAWING NO
B	00779	350547

SCALE 4-1	SHEET #
-----------	---------

CUSTOMER DRAWING