


# ÖLFLEX® CLASSIC 110

The new control cable with numbered cores:  
Smaller, lighter, VDE-approval.  
Replaces ÖLFLEX® 110/03 and 110/05



| Part Number    | No. of cores and mm <sup>2</sup> per conductor | Approx. outside diameter in mm | Copper weight kg/km | Approx. weight kg/km |
|----------------|------------------------------------------------|--------------------------------|---------------------|----------------------|
| 1119 250 T     | 50 G 1,0                                       | 20,6                           | 480,0               | 797                  |
| 1119 256 T     | 56 G 1,0                                       | 21,4                           | 538,0               | 888                  |
| 1119 261 T     | 61 G 1,0                                       | 22,1                           | 586,0               | 958                  |
| 1119 265 T     | 65 G 1,0                                       | 23,6                           | 624,0               | 1033                 |
| 1119 280* T    | 80 G 1,0                                       | 25,3                           | 768,0               | 1251                 |
| 1119 300* T    | 100 G 1,0                                      | 28,3                           | 960,0               | 1560                 |
| 1119 902 R + T | 2 X 1,5                                        | 6,3                            | 29,0                | 68                   |
| 1119 303 R + T | 3 G 1,5                                        | 6,7                            | 43,0                | 84                   |
| 1119 903 R + T | 3 X 1,5                                        | 6,7                            | 43,0                | 84                   |
| 1119 304 R + T | 4 G 1,5                                        | 7,2                            | 58,0                | 104                  |
| 1119 904 R + T | 4 X 1,5                                        | 7,2                            | 58,0                | 104                  |
| 1119 305 R + T | 5 G 1,5                                        | 8,1                            | 72,0                | 128                  |
| 1119 905 R + T | 5 X 1,5                                        | 8,1                            | 72,0                | 128                  |
| 1119 307 R + T | 7 G 1,5                                        | 8,9                            | 101,0               | 166                  |
| 1119 907 R + T | 7 X 1,5                                        | 8,9                            | 101,0               | 166                  |
| 1119 308 R + T | 8 G 1,5                                        | 10,6                           | 115,0               | 197                  |
| 1119 309 R + T | 9 G 1,5                                        | 11,4                           | 130,0               | 221                  |
| 1119 310 R + T | 10 G 1,5                                       | 11,6                           | 143,0               | 243                  |
| 1119 311 R + T | 11 G 1,5                                       | 11,6                           | 158,0               | 258                  |
| 1119 312 R + T | 12 G 1,5                                       | 12                             | 173,0               | 279                  |
| 1119 912 R + T | 12 X 1,5                                       | 12                             | 173,0               | 279                  |
| 1119 314 R + T | 14 G 1,5                                       | 12,7                           | 202,0               | 323                  |
| 1119 316 R + T | 16 G 1,5                                       | 13,4                           | 230,4               | 361                  |
| 1119 318 R + T | 18 G 1,5                                       | 14,4                           | 259,0               | 407                  |
| 1119 321 R + T | 21 G 1,5                                       | 15,7                           | 302,0               | 469                  |
| 1119 325 R + T | 25 G 1,5                                       | 16,9                           | 360,0               | 560                  |
| 1119 326 T     | 26 G 1,5                                       | 17,3                           | 374,4               | 582                  |
| 1119 332 T     | 32 G 1,5                                       | 17,5                           | 461,0               | 704                  |
| 1119 334 T     | 34 G 1,5                                       | 19,4                           | 490,0               | 746                  |
| 1119 341 T     | 41 G 1,5                                       | 21,3                           | 591,0               | 895                  |
| 1119 350 T     | 50 G 1,5                                       | 23,5                           | 720,0               | 1089                 |
| 1119 361 T     | 61 G 1,5                                       | 25,2                           | 878,0               | 1309                 |
| 1119 365 T     | 65 G 1,5                                       | 26,7                           | 936,0               | 1398                 |
| 1119 380* T    | 80 G 1,5                                       | 28,8                           | 1152,0              | 1708                 |
| 1119 952 R + T | 2 X 2,5                                        | 7,5                            | 48,0                | 101                  |
| 1119 403 R + T | 3 G 2,5                                        | 8,1                            | 72,0                | 132                  |
| 1119 404 R + T | 4 G 2,5                                        | 8,9                            | 96,0                | 163                  |
| 1119 405 R + T | 5 G 2,5                                        | 10                             | 120,0               | 200                  |
| 1119 407 R + T | 7 G 2,5                                        | 11,1                           | 168,0               | 267                  |
| 1119 412 R + T | 12 G 2,5                                       | 14,8                           | 288,0               | 445                  |
| 1119 414 R + T | 14 G 2,5                                       | 15,8                           | 336,0               | 515                  |
| 1119 418 R + T | 18 G 2,5                                       | 17,8                           | 432,0               | 648                  |
| 1119 425 R + T | 25 G 2,5                                       | 20,8                           | 600,0               | 890                  |
| 1119 434 T     | 34 G 2,5                                       | 24,4                           | 816,0               | 1208                 |
| 1119 450 T     | 50 G 2,5                                       | 29,4                           | 1200,0              | 1754                 |
| 1119 503 R + T | 3 G 4,0                                        | 9,9                            | 115,0               | 201                  |
| 1119 504 R + T | 4 G 4,0                                        | 10,8                           | 154,0               | 249                  |
| 1119 505 R + T | 5 G 4,0                                        | 12,1                           | 192,0               | 305                  |
| 1119 507 R + T | 7 G 4,0                                        | 13,4                           | 269,0               | 407                  |
| 1119 511 T     | 11 G 4,0                                       | 17,6                           | 422,0               | 634                  |
| 1119 603 R + T | 3 G 6,0                                        | 11,7                           | 172,8               | 289                  |
| 1119 604 R + T | 4 G 6,0                                        | 13                             | 230,0               | 365                  |
| 1119 605 R + T | 5 G 6,0                                        | 14,5                           | 288,0               | 447                  |
| 1119 607 R + T | 7 G 6,0                                        | 16                             | 403,0               | 600                  |
| 1119 613 T     | 3 G 10,0                                       | 14,6                           | 288,0               | 466                  |
| 1119 614 T     | 4 G 10,0                                       | 16,2                           | 384,0               | 590                  |
| 1119 615 T     | 5 G 10,0                                       | 18,1                           | 480,0               | 722                  |
| 1119 617 T     | 7 G 10,0                                       | 20                             | 672,0               | 968                  |
| 1119 624 T     | 4 G 16,0                                       | 18,8                           | 614,0               | 1087                 |
| 1119 625 T     | 5 G 16,0                                       | 21,2                           | 768,0               | 1370                 |
| 1119 627 T     | 7 G 16,0                                       | 23,4                           | 1075,0              | 1779                 |
| 1119 634 T     | 4 G 25,0                                       | 23,5                           | 960,0               | 1582                 |
| 1119 635 T     | 5 G 25,0                                       | 26,4                           | 1200,0              | 1998                 |
| 1119 644 T     | 4 G 35,0                                       | 26,8                           | 1344,0              | 2106                 |
| 1119 645 T     | 5 G 35,0                                       | 30,1                           | 1680,0              | 2635                 |

R= Coils up to 30 kg, T = Drums  
No surplus sectioning for the lengths: 50 m, 100 m, 500 m, 1000 m  
G = with protective conductor GNYE  
Y = without protective conductor