


LOC	DIST	REVISIONS					
IR	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			AV	ECR-10-002350	01/02/10	MJG	JA
			AV1	ECR-10-022530	06JUN2011	KK	HMR
			AV2	TABLE UPDATED (ECR-11-018833)	13SEP2011	PKS	RRP
			AV3	8-154719-4 OBSOLETE	12APR2013	PKS	RRP



5 USING EQUIVALENT ALTERNATE MATERIAL

		8-154719-6	As Drg	UL 94 V0	PA 66	Orange
		8-154719-5	As Drg	UL 94 V2	PA 6/6 or Equivalent	Natural
OBSOLETE		8-154719-4	As Drg	UL 94 V0	PA 66	Natural
		8-154719-3	As Drg.	UL 94 V0	PA 66/6	Terracotta
OBSOLETE		8-154719-1	As Drg.	UL 94 V2	PA 6/6 or Equivalent	Black
		8-154719-0	As drg.	UL 94 V0	PA 6/6 or Equivalent	Clear
		7-154719-0	AE	UL 94 V0	PA 66	Orange (Ral 2000)
		6-154719-6	AB	UL 94 V2	PBT	Black
		5-154719-0	AB	UL 94 V0	PPE+PS	Orange
		4-154719-0	AA	UL 94 V0	PA 66	(Bk-59 Black)
		2-154719-0	AA	UL 94 V0	PPE+PS	Red
		1-154719-1	As Drg.	UL 94 V0	PA 6/6 or Equivalent	Natural
		1-154719-0	AE	UL 94 V0	PA 6/6 or Equivalent	Natural
		154719-9	As Drg.	UL 94 V2	PA 6/6 or Equivalent	Brown
		154719-6	As Drg.	UL 94 V2	PA 6/6 or Equivalent	Blue
		154719-5	As Drg.	UL 94 V2	PA 6/6 or Equivalent	Green
		154719-4	As Drg.	UL 94 V2	PA 6/6 or Equivalent	Yellow
		154719-2	As Drg.	UL 94 V2	PA 6/6 or Equivalent	Red
		154719-1	As Drg.	UL 94 V2	PA 6/6 or Equivalent	Natural
		154719	As. Drg.	UL 94 V2	PA 6/6 or Equivalent	Black
	Notes	Part Number	Part Revision	Flammability Rating	Material	Colour

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 09MAY2002 A. J. BEKEN CHK 09MAY2002 S. CLAPPISON APVD 09MAY2002 S. CLAPPISON		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: LINEAR ±0.5 0-PLC ±0.1 1-PLC ±0.1 2-PLC ±0.05 3-PLC ±0.1 4-PLC ±0.1 ANGLES ±2 FINISH		NAME POSITIVE LOCK RECEPTACLE INSULATOR -	
MATERIAL See Table		PRODUCT SPEC 108-3252 APPLICATION SPEC 114-2153 WEIGHT 0.5g		SIZE A2	CAGE CODE 00779
		DRAWING NO C-154719		RESTRICTED TO -	
		Customer Drawing		SCALE 5.	SHEET OF
				REV AV3	