


OMS, MSQ Series


DWG. NO. **A** OMS & MSQ SERIES

REVISIONS				
SYM.	DESCRIPTION	DATE	APPROVAL	
A	RELEASED TO PRODUCTION STATUS	4-23-09	21721	



Flush Mt. Panel Cutout  
 $\frac{+.25}{-.00}$   
 $\frac{+.010}{-.000}$

Surface Mt. Panel Cutout



Alternate terminals used only on ammeters unless otherwise ordered.

**DIMENSIONAL DATA OMS, MSQ SERIES**

	A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	U	V	W
<b>OMS</b>	mm. 36.83	28.96	8.38	24.13	30.48	22.48	16.26	38.3	8.9	22.86	8.9	11.3	40.4	1.52	21.49	.76	12.7	9.6	36.68	21.74	5.89
	in. 1.450	1.140	.330	.950	1.200	.885	.640	1.51	.35	.900	.35	.445	1.59	.060	.846	.030	.500	.38	1.444	.856	.232
<b>MSQ</b>	mm. 58.93	31.75	8.89	28.70	50.80	35.81	18.03	63.0	4.3	27.9	12.9	15.39	59.9	2.0	35.79	1.27	12.95	10.7	59.44	36.04	6.68
	in. 2.320	1.250	.350	1.130	2.000	1.410	.710	2.48	.17	1.10	.51	.606	2.360	.080	1.409	.050	.51	.42	2.340	1.419	.263

TOLERANCE UNLESS SPECIFIED		
RAW MATERIAL - COMMERCIAL STANDARD		
DIMENSIONS ARE IN INCHES.	DRAWN BY	V.K. 4-23-09
MATERIAL	CHECKED BY	
FINISH	ENGINEER	
	USED ON	NEXT ASSY
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF JEWELL INSTRUMENTS, LLC. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT PERMISSION.		

"M" SERIES  
 OMS & MSQ  
 OUTLINE

SCALE NONE EPA NO. 11229A

**Jewell**  
 INSTRUMENTS, LLC.  
 MANCHESTER NEW HAMPSHIRE  
 DWG. NO. OMS & MSQ SERIES  
 CAT. NO.  
 CODE 33005