
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -
© COPYRIGHT 19 - ALL RIGHTS RESERVED.

LOC	DIST
H	-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	W1	REVISED PER ECO-11-005294	21MAR2011	RK	HMR




NOTES:

1. SHOWN IS A 10 POS. CONNECTOR
2. FOR FLAT RIBBON CABLE REQUIREMENTS, SEE APPLICATION SPEC 114-19016.
3. CONNECTOR-HEIGHT AFTER CABLE TERMINATION 5,1mm AVERAGE, DEPENDING ON PROCESSING, SEE APPLICATION SPEC 114-19016.
4. REF. CONTACT SHOULDER BOTTOM, THAT CAN TOUCH THE PC-BOARD SURFACE.

PARTNUMBER BOX PACKAGING	PARTNUMBER REEL PACKAGING	NO OF POS "n"	DIMENSION "A" MAX
7-215570-4	215570-4	4	8,6
7-215570-6	215570-6	6	11,1
7-215570-8	215570-8	8	13,6
8-215570-0	1-215570-0	10	16,2
8-215570-2	1-215570-2	12	18,7
8-215570-4	1-215570-4	14	21,3
8-215570-6	1-215570-6	16	23,8
8-215570-8	1-215570-8	18	26,3
9-215570-0	2-215570-0	20	28,9
9-215570-4	2-215570-4	24	34,0


250 CONNECTORS PER BOX.

BOX PACKAGING



DETAIL A


DEREELING DIRECTION AND POSITION OF CONNECTORS.



2500 CONNECTORS PER REEL.

REEL PACKAGING

PC-BOARD HOLE LAYOUT
(COMPONENT SIDE OF BOARD SHOWN)



Item no.	Description	Material	Finish
3	PADDLEBOARD HOUSING	G.F.POLYESTER (RED)	-
2	CONTACT	PHOSFOR BRONZE	TIN OVER NICKEL
1	COVER	G.F.POLYESTER (RED)	-

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-

MATERIAL SEE TABLE

FINISH SEE TABLE

DWN	M.GOSSELINK -
CHK	M.GOSSELINK -
APVD	F.LEIJTENS -
PRODUCT SPEC	108-19052
APPLICATION SPEC	114-19016
WEIGHT	-

TE Connectivity

NAME
Micro-MaTch
PADDLE BOARD CONNECTOR
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-215570	-

CUSTOMER DRAWING

SCALE 5:1 SHEET 1 OF 1 REV W1

1470-19 (3/11)

Pro/ENGINEER DRAWING