



Technical request

1. All the part should be installed correctly. No omission, No loosen, No dislocation come out etc.
2. Clean appearance is requested, No smudge and No scratch defect etc.
3. Electrical safety performance Shall comply with GB4706.15-2003 《 Household and similar electrical appliances - Safety for skin and hair care appliances - Particular requirements 》
4. Rated voltage 220V, Rate frequency 50hz,Rate power 3000W
5. Wire and wiring method by NFJ300C-JX 《Electrical wiring diagram 》
6. Product life not less than 3 years (30 min / day)
7. Product inspection requirements by 《Household and similar skin and hair care appliances factory inspection standards 》 and 《Household and similar skin and hair care equipment type test 》 .

32		washer	external diameter $\phi 16$ internal diameter $\phi 12$	2	
31		Cross recessed hexagon bolt with washer	M6X12	4	
30		Cross recessed pan head tapping screws with washer	ST3. 5X10-C-H	2	
29	GB818-2000	Cross recessed pan head screws	M4X6	4	
28	NFJ300-0-12	stand adjustment block	45# $\delta=2$	2	
27	NFJ300-0-11	Wind wheel bearing cap	A3 $\delta=1$	2	
26	NFJ300-0-9	Wind wheel bearings		2	
25	NFJ300-0-8	Rubber bearing base	rubber	2	
24	NFJ300-5-0	Air duct assembly		2	
23	NFJ300-4-0	Heating element assembly		2	
22	NFJ300-3-0	Wind wheel assembly		2	
21	NFJ300-0-7	Earth termina	304 $\delta=0.8$	2	
20	NFJ300-2-0	Outlet network assembly		1	
19		Heating element leads		4	refer to NFJ300-JX
18	NFJ300-0-6	Air duct connector	A3 $\delta=1.2$	2	
17	GB6170-2000	Hexagon nuts	M4	2	
16	GB818-2000	Cross recessed pan head screws	M4X10	1	
15		Motor leads		4	refer to NFJ300-JX
14		Closed terminal		2	refer to NFJ300-JX
13	GB845-76	Cross recessed pan head tapping screws	ST3. 5X16-C-H	2	
12		Motor assembly		1	refer to NFJ300-JX

49	NFJ300-0-3	specification sticker	foil paper sticker	1	
48	NFJ300-0-21	Outlet network fixing part A	A3 $\delta=0.8$	1	
47		Cross recessed pan head tapping screws with washer	ST3. 5X10-C-H	4	
46	NFJ300-0-19	Fan mounting plate	galvanized sheet 1	1	
45	GB12618-1990	Open type oval head rivets	4X11	8	
44	GB818-2000	Cross recessed pan head screws	M4X20	2	
43		power wire		1	refer to NFJ300-JX
42	NFJ300-0-18	Bushing	rubber	1	
41	NFJ300-0-17	Pressure line block	PP	1	
40	NFJ300-0-16	Connector fixed block	galvanized $\delta=0.8$	1	
39	GB845-85	Cross recessed pan head tapping screws	ST4X20-C-H	2	
38	NFJ300-0-15	main body	A3 $\delta=0.8$	1	
37		Cross recessed pan head tapping screws with washer	ST3. 5X10-C-H	2	
36		Cross recessed pan head tapping screws with washer	ST3. 5X10-C-H	4	
35	NFJ300-0-14	Seal plate fixed block	A3 $\delta=0.8$	2	
34	NFJ300-0-13	Left Seal plate	A3 $\delta=0.8$	1	
33		Cross recessed pan head tapping screws with washer	ST3. 5X10-C-H	4	

11	NFJ300-0-5	power wire fixing clip	A3 $\delta=0.8$	1	
10		Wiring Terminals		1	refer to NFJ300-JX
9	GB818-2000	Cross recessed pan head screws	M4X6	2	
8	NFJ300-1-0	Switch plate assembly		1	
7	NFJ300-0-4	Plate	A3 $\delta=0.8$	1	
6		Cross recessed pan head tapping screws with washer	ST3. 5X10-C-H	2	
5	NFJ300-0-3	Mounting stand	A3 $\delta=2$	1	refer to NFJ300-JX
4		Switch		3	refer to NFJ300-JX
3	NFJ300-0-2	Switch covering	A3 $\delta=0.8$	1	
2		Cross recessed pan head tapping screws with washer	ST3. 5X10-C-H	8	
1	NFJ300-0-1	Right Seal plate	A3 $\delta=0.8$	1	
Order	Drawing code	Name	Materials Specification	Quantity	Remarks

TAISHAN JIEDA ELECTRICAL INDUSTRIAL CO., LTD.
 NFJ300 warm air blower
 Assemble Drawing
 NFJ300-0