

IZ series

Rear mounted sealed pushbutton switches - bushing Ø 16

Distinctive features and specifications



- Illuminated and non-illuminated
- Tactile feedback ?
- Flat actuator for optional marking ?
- Sealed to IP67

ENVIRONMENTAL AND GENERAL SPECIFICATIONS

- Degree of protection : IP67
- Temperature range : -40°C to +85°C
- Total travel : 1,7 mm (.067)
- Operating force : 5N ±1 Ne pas indiquer ?
- Mechanical life : 1.000.000 cycles

MATERIALS

- Case : Pa-6T UL94-V0
- Plunger : polyamide 6/6
- Bushing/bezel : polyamide 6/6
- Contacts :
 - 4 : silver, gold plated
 - 2 : silver (screw terminals)
- Multi-wire lead AWG20, section 0,6 mm², UL approved ??
- LED wire : AWG26
- Lens : polycarbonate
- Terminal seal : epoxy

ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load :
 - Gold plated silver contacts (code 4) : 400mA 32VAC - 100mA 50VDC - 125mA 125VAC
 - Silver contacts (code 2) - screw terminals : 2A 250VAC - 4A 48VDC ???
- Electrical life at full load : 500.000 cycles
- Initial contact resistance : 50 mΩ max.
- Insulation resistance : 1 GΩ min. at 500VDC
- Dielectric strength : 1.000 Vrms 50 Hz
- Contact bounce : 10 ms ???

LED COMPONENT SPECIFICATIONS

LED colour	Forward current	Typ. forward voltage	Max. forward voltage
Super red (LOS)	20mA	2,1V	2,3V
Yellow (LOY)	20mA	2,1V	2,3V
Green (LOG)	20mA	2,1V	2,3V
Blue (LOB)	20mA	3,2V	3,8V
White (LOW)	20mA	3,35V	4,25V

A resistor must be series-connected by the user.
 Resistor value = $\frac{\text{supply voltage} - \text{LED forward voltage}}{\text{LED forward current}}$
 On wire lead versions, the LED resistor can be integrated by APEM on request. ????

Specs LED reprises sur l'IR. A valider.

Dimensions : First dimensions are in mm while inches are shown as bracketed numbers.


Tolerance : The general tolerance for dimensions in this brochure is ± 0,3 (.012).
 Overall dimension tolerance is ± 0,5 (.020).

Dimensions, specifications and data shown in this brochure are subject to change without notice.

IZ series

Rear mounted sealed pushbutton switches - bushing Ø 16

Overview



ABOUT THIS SERIES

On the following pages, you will find successively :
 model structure of switches and options in the same order as in above chart

Dimensions : first dimensions are in mm while inches are shown as bracketted numbers.



NOTICE : please note that not all combinations of above numbers are available. Refer to the following pages for further information.



Mounting accessories : Standard hardware supplied : **A INDIQUER**



Packaging unit : **A INDIQUER**

IZ series


Rear mounted sealed pushbutton switches - bushing Ø 16

Illuminated - momentary or latching


Nouveau dessin

Function 3 (NO) Function 1 (ON-OFF)

- Five LED colours
- Tin plated LED terminals
- Gold plated contacts



MODEL STRUCTURE




Plunger marking available on IZP models (symbol 12 mm max.). On request. ??

Solder lug terminals - momentary

→ Flat

Photo




Nouveau dessin

Solder lug terminals - latching

→ Flat

Photo




Nouveau dessin

Flying lead terminals - momentary

→ Flat

Photo



Nouveau dessin


Wire colours : black : NO contact, red : LED anode(+), blue : LED cathode(-) **A confirmer.**

IZ series

Rear mounted sealed pushbutton switches - bushing Ø 16


Illuminated - momentary or latching

PLUNGER COLOUR




1 : blue - **B** : dark blue - **2** : black - **3** : green - **5** : yellow - **6** : red - **7** : white - **8** : bright chrome - **9** : orange
A : satin chrome

BUSHING AND BEZEL COLOUR



1 : blue - **B** : dark blue - **2** : black - **3** : green - **5** : yellow - **6** : red - **7** : white - **8** : bright chrome - **9** : orange
A : satin chrome

LED COLOUR





LOS : super red - **LOY** : yellow - **LOG** : green - **LOB** : blue - **LOW** : white (momentary only)


IZ series

Rear mounted sealed pushbutton switches - bushing Ø 16

Non-illuminated - momentary



MODEL STRUCTURE



Plunger marking available on IZP models (symbol 12 mm max.). On request. ??

Solder lug terminals - gold plated contacts

→ Flat

Photo

Curved actuator
IZR3S4



Normally Open

Flat actuator
IZP3S4



Normally Open

Nouveau dessin

Also available with straight PC terminals : **IZ•3P4** and quick-connect terminals : **IZ•3Z4**.

Sealed flying lead terminals - gold plated contacts

→ Flat

Photo

Curved actuator
IZR3S4



Normally Open

Flat actuator
IZP3S4



Normally Open

Nouveau dessin

Screw terminals - silver contacts

→ Flat

Photo

Curved actuator
IZR3V2



Normally open

Flat actuator
IZP3V2



Normally open



Nouveau dessin

Plunger colour and bushing/bezel colour : select the desired codes on next page.


IZ series

Rear mounted sealed pushbutton switches - bushing Ø 16

Non-illuminated - latching



MODEL STRUCTURE



Plunger marking available on IZP models (symbol 12 mm max.). On request. ??

Solder lug terminals - gold plated contacts

→ Flat

Photo

Curved actuator
IZR1S4

ON - OFF


Flat actuator
IZP1S4

ON - OFF

Nouveau dessin

Also available with straight PC terminals : **IZ•1P4** and quick-connect terminals : **IZ•1Z4**.

PLUNGER COLOUR



1 : blue - **B** : dark blue - **2** : black - **3** : green - **5** : yellow - **6** : red - **7** : white - **8** : bright chrome - **9** : orange
A : satin chrome

BUSHING AND BEZEL COLOUR



1 : blue - **B** : dark blue - **2** : black - **3** : green - **5** : yellow - **6** : red - **7** : white - **8** : bright chrome - **9** : orange
A : satin chrome