LedEngin, Inc.

High Luminous Efficacy White Power LedFlex[™] Emitter

LZ4-00CW15

Power ed DV Le dending of the

Key Features

- High Luminous Efficacy 15W White LED
- Unique package design with ceramic substrate, integrated glass lens and Flex PCB
- New industry standard for Lumen Maintenance (> 90% at 100,000 Hours)
- Extremely low Thermal Resistance (2.6°C/W)
- Isolated thermal path electrical connections on Flex PCB
- Mount directly to heatsink MCPCB not required
- Exceptional spatial color uniformity across radiation pattern
- Industry's highest Luminous Flux density
- High ESD protection (> 8 kV HBM)
- JEDEC Level 2 Moisture Sensitivity Level
- Lead (Pb) free and RoHS compliant

Typical Applications

- Architectural lighting
- Street lighting
- Stage and Studio lighting
- Task and Accent lighting
- Medical lighting

Description

LedEngin's LZ4-00CW15 White Power LedFlex™ emitter is capable of 15W power dissipation and provides exceptional luminous flux density. The LZ4-00CW15 offers ultimate design flexibility with separate electrical and thermal paths. The thermal contact can be mounted directly to a heatsink, eliminating the requirement for a MCPCB. The Anode and Cathode contacts are remotely located on the Flex PCB, allowing for connection versatility and unobstructed access to the optics. LedEngin's patent-pending thermally insulated phosphor layer provides for exceptional spatial color uniformity across the radiation pattern and a consistent CCT over time and temperature. The patent-pending design has unparalleled thermal and optical performance. The high quality materials used in the package are chosen to optimize light output and minimize stresses which results in monumental reliability and lumen maintenance.

Table of Contents

Product Nomenclature	3
IPC/JEDEC Moisture Sensitivity	3
Average Lumen Maintenance Projections	3
Luminous Flux Binning	4
Forward Voltage Binning	4
Cool White Chromaticity Binning	5
Absolute Maximum Ratings	6
Optical Characteristics	6
Electrical Characteristics	6
Mechanical Dimensions	7
Typical Radiation Pattern	8
Typical Relative Spectral Power Distribution	8
Typical Relative Light Output	9
Typical Relative Light Output over Temperature	9
Typical Forward Current Characteristics	10
Current Derating Curves	10
Company Information	1 1

Product Nomenclature

The LZ Series part number designation is defined as follows:

Where:

A – designates the number of LED die in the package ("4" for 15W)

B – designates the package level ("0" for Emitter)

C – designates the radiation pattern ("0" for Lambertian)

D and E – designate the color ("CW" for Cool White: 5000 K < CCT < 10000 K)

F and G – designate the Power ("15" for 15W typical rating)

H – designates the Flux bin (See Table 2)

J and K – designate the CCT bin groups (see Figure 1 and Table 4)

L – designates the V_F bin (See Table 3)

Ordering information:

For ordering LedEngin products, please reference the base part number. The base part number represents any of the luminous flux, chromaticity groups, or forward voltage bins specified in the binning tables below. For ordering products with special bin selections, please contact a LedEngin sales representative or authorized distributor.

IPC/JEDEC Moisture Sensitivity Level

Table 1 - IPC/JEDEC J-STD-20 MSL Classification:

			Soak Requirements					
	Floor Life		Standard		Accelerated			
Level	Time	Conditions	Time (hrs)	Conditions	Time (hrs)	Conditions		
2	1 Year	≤ 30°C/ 60% RH	168 +5/-0	30°C/ 60% RH	n/a	n/a		

Notes for Table 1:

Average Lumen Maintenance Projections

Lumen maintenance generally describes the ability of a lamp to retain its output over time. The useful lifetime for solid state lighting devices (Power LEDs) is also defined as Lumen Maintenance, with the percentage of the original light output remaining at a defined time period.

Based on long-term WHTOL testing, LedEngin projects that the LZ Series will deliver, on average, 90% Lumen Maintenance at 100,000 hours of operation at a forward current of 1000 mA. This projection is based on constant current operation with junction temperature maintained at or below 125°C.

The standard soak time is the sum of the default value of 24 hours for the semiconductor manufacturer's exposure
time (MET) between bake and bag and the floor life of maximum time allowed out of the bag at the end user of
distributor's facility.

Luminous Flux Bins

Table 2:

Bin Code	Minimum Luminous Flux (Φ_V) @ $I_F = 1000$ mA $^{[1,2]}$ (Im)	Maximum Luminous Flux (Φ_V) @ $I_F = 1000$ mA $^{[1,2]}$ (Im)	Typical Luminous Flux (Φ _V) @ I _F = 1500mA ^[2] (Im)	
S	356	445	538	
Т	445	556	637	
U	556	695	796	
V	695	868	995	

Notes for Table 2:

- Luminous flux performance guaranteed within published operating conditions. LedEngin maintains a tolerance of ± 10% on flux measurements.
- Future products will have even higher levels of luminous flux performance. Contact LedEngin Sales for updated information.

Forward Voltage Bins

Table 3:

Bin Code	Forward Voltage (V _F) @ I _F = 1000mA ^[1] (V)	Forward Voltage (V _F) @ I _F = 1000mA ^[1] (V)
F	12.80	13.76
G	13.76	14.72
Н	14.72	15.68
J	15.68	16.64

Notes for Table 3:

1. LedEngin maintains a tolerance of \pm 0.04V for forward voltage measurements.

Cool White Chromaticity Groups




Figure 1: Standard Chromaticity Groups plotted on excerpt from the CIE 1931 (2°) x-y Chromaticity Diagram. Coordinates are listed below in Table 4.

Cool White Chromaticity Coordinates

Table 4:

Bin Code	x	у	Typical CCT (K)		3in ode	x	у	Typical CCT (K)
	0.348	0.386				0.316	0.357	
1.11	0.346	0.360	5250	V	ΝL	0.318	0.334	6600
UL	0.332	0.348	5250	v	/VL	0.305	0.321	6600
	0.333	0.372				0.302	0.341	
UM	0.346	0.360				0.318	0.334	
	0.344	0.333	5250	V	VM	0.320	0.311	6600
	0.332	0.323		V	VIVI	0.309	0.301	6600
	0.332	0.348				0.305	0.321	
	0.333	0.372				0.302	0.341	
VL	0.332	0.348	5850	,	XL	0.305	0.321	8500
٧L	0.318	0.334		,	^L	0.278	0.290	8300
	0.316	0.357				0.271	0.305	
VM	0.332	0.348	5850			0.305	0.321	
	0.332	0.323		,	ΚM	0.309	0.301	8500
	0.320	0.311		/	ZIVI	0.286	0.275	0300
	0.318	0.334				0.278	0.290	

Absolute Maximum Ratings

Table 5:

Parameter	Symbol	Value	Unit
DC Forward Current ^[1]	I _F	1500	mA
Peak Pulsed Forward Current ^[2]	I _{FP}	2000	mA
Reverse Voltage	V_R	See Note 3	V
Storage Temperature	T _{stg}	-40 ~ +150	°C
Junction Temperature	TJ	150	°C
Soldering Temperature	T _{sol}	260	°C
ESD Sensitivity ^[4]		> 8,000 V HBM Class 3B JESD22-A114-D)

Notes for Table 5:

- 1. Maximum DC forward current is determined by the overall thermal resistance and ambient temperature. Follow the curves in Figure 8 for current derating.
- 2: Pulse forward current conditions: Pulse Width ≤ 10msec and Duty cycle ≤ 10%.
- 3. LEDs are not designed to be reverse biased.
- LedEngin recommends taking reasonable precautions towards possible ESD damages and handling the LZ4-00CW15 in an electrostatic protected area (EPA). An EPA may be adequately protected by ESD controls as outlined in ANSI/ESD S6.1.

Optical Characteristics @ $T_C = 25$ °C

Table 6:

Parameter	Symbol	Typical	Unit
Luminous Flux (@ I _F = 1000mA)	Фу	552	lm
Luminous Flux (@ I _F = 1500mA)	Фу	703	lm
Correlated Color Temperature ^[1]	CCT	6200	K
Chromaticity Coordinates	x,y	0.318, 0.330	
Viewing Angle ^[2]	2Θ _{1/2}	105	Degrees
Total Included Angle[3]	Θ _{0.9V}	135	Degrees

Notes for Table 6:

- 1. Typical Color Rendering Index (CRI) is 75.
- 2. Viewing Angle is the off axis angle from emitter centerline where the luminous intensity is ½ of the peak value.
- 3. Total Included Angle is the total angle that includes 90% of the total luminous flux.

Electrical Characteristics @ T_C = 25°C

Table 7:

Parameter	Symbol	Typical	Unit	
Forward Voltage (@ I _F = 1000mA)	V _F	14.5	V	
Forward Voltage (@ I _F = 1500mA)	V_{F}	15.1	V	
Temperature Coefficient of Forward Voltage	$\Delta V_F/\Delta T_J$	-8.2	mV/°C	
Thermal Resistance (Junction to Case)	$R\Theta_{J-C}$	2.6	°C/W	

Mechanical Dimensions (mm)




Figure 2: Package outline drawing.

Notes for Figure 2:

- Unless otherwise noted, the tolerance = \pm 0.20 mm.
- Solder contact pads on Flex PCB are labeled "+" for Anode and "-" for Cathode.

 LedEngin recommends using thermally conductive tapes or adhesives when attaching Thermal Contact to a heat sink.

Typical Radiation Pattern




Figure 3: Typical representative spatial radiation pattern.

Typical Relative Spectral Power Distribution




Figure 4: Relative spectral power vs. wavelength.

Typical Relative Light Output




Figure 5: Typical relative light output vs. forward current @ $T_C = 25$ °C.

Typical Relative Light Output over Temperature




Figure 6: Typical relative light output vs. case temperature.

Typical Forward Current Characteristics




Figure 7: Typical forward current vs. forward voltage @ $T_C = 25$ °C.




Figure 8: Maximum forward current vs. ambient temperature based on $T_{J(MAX)}$ = 150°C.

Notes for Figure 8:

- 1. RO_{J-C} [Junction to Case Thermal Resistance] for the LZ4-00CW15 is typically 2.6°C/W.
- 2. RO_{J-A} [Junction to Ambient Thermal Resistance] = RO_{J-C} + RO_{C-A} [Case to Ambient Thermal Resistance].

Company Information

The LZ4-00CW15 Power LedFlex™ emitter is developed, manufactured, and marketed by LedEngin, Inc., located in Santa Clara, CA. LedEngin is a global market leader in advanced high-power LED emitters and light-source modules. LedEngin provides total solutions from 3W to 15W in single packages with ultra-small footprints in all colors from White, Dental Blue, Blue, Green, Red, RGB, and UV. LedEngin supports customers to generate solid-state lighting designs that conserve natural resources. LedEngin is focused on differentiated Ultra High-Brightness LED solutions for diverse global markets using its patent-pending package designs and manufacturing processes. LedEngin offers catalog as well as full custom solutions to enable flexible system designs for its customers. LedEngin is dedicated to long-term win-win partnering with its customers and suppliers.

LedEngin reserves the right to make changes to improve performance without notice.

Please contact <u>Sales@ledengin.com</u> for more information.