

5

4

3

2

1

D



Description: See table I  
 Part No: 27-9300-XX  
 Application: Attenuation  
 Crimp Tool: N/A  
 Impedance: 50 ohm  
 Frequency Range: 0~2 GHz  
 Material: Body Brass Nickel plated  
 Insulator Delrin  
 Contact Brass Gold plated  
 Nut Zinc Nickel plated  
 Label Self adhesive paper  
 RoHS Compliance: Yes  
 Technical Detail: Refer to Emerson Document P/N 27-0000

DRAWING NO.  
27-9300-XX


## REVISIONS

01	OFFICIAL RELEASE				2009.09.0
	08-18-09	L	L	T	H

C

B

A

**DIM OUTLINE**

## 受控 CONTROLLED DOCUMENT

编号 P/N	27-9300-CUST	版本 Rev	01	日期 Rel'd Date	SEP 14,09
-----------	--------------	-----------	----	------------------	-----------

Table I

P/N	Description	VSWR	Attenuation Tolerance
27-9300-3	3DB BNC ATTENUATOR PAD	1.1 TO 1GHz	±0.4 dB TO 1GHz
27-9300-6	6DB BNC ATTENUATOR PAD	1.2 TO 2GHz	±0.45 dB TO 2GHz
27-9300-10	10DB BNC ATTENUATOR PAD	1.35 TO 4GHz	±0.65 dB TO 4GHz
27-9300-20	20DB BNC ATTENUATOR PAD	1.65 TO 8GHz	±1.0 dB TO 8GHz

CUSTOMER COPY

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY LINDA.WU	DATE 08-18-09
DECIMALS	mm	CHECKED BY LINDA.WU	DATE 08-18-09
X	± 0.5	APPROVED BY THOMAS	DATE 08-18-09
X.X	± 0.3		
X.XX	± 0.1		
ANGLES	± 0.5°	U/M	mm

TITLE  
6DB/3DB/20DB/10DB BNC  
ATTENUATOR PADSHEET 1 OF 1  
DRAWING NO. 27-9300-XX  
SIZE A

5

4

3

2

1