



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	9/30/08	D.GRIFFIN
B	ECN#3659, MATCH ASSEMBLY TO AS BUILT, REMOVE NOTE 1	2008.10.22	E. STAUBLE
C	ECN5805: LENGTH DIM WAS CBL LENGTH BETWEEN CONNS. UPDATE FORMAT. COLOR WAS GRAY. MODIFIED NOTE 2.	11/02/11	D.FP
D	ECN 7538: REVISED PACKAGING NOTE 2, FORMAT, ADDED ROHS	7/31/14	D.FRISIELLO



PART #	LENGTH	
	INCHES	METERS
CAESA-05M	19.68	0.5
CAESA-1M	39.37	1.0
CAESA-2M	78.74	2.0

NOTES:

- CABLE ASSEMBLY SHALL BE SUBJECTED TO A CONTINUITY TEST.
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN A CLEAR POLY BAG AND LABELED PER L-COM SPECIFICATION LSP-010.
- REGULATORY COMPLIANCE:**
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY E. STAUBLE	2008.09.25		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY D. PARHAM	2008.09.29	PRODUCT DESCRIPTION	
PROJECTION	APPROVED BY S. SMITH	2008.09.29	CBL,ESATA/ESATA	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. CAESA-XM	REV. D
			SCALE: NONE	CAD FILE: CAESA-XM.SLDDRW
				SHEET 1 OF 1