




2 CKT




4-12 CKT




4 CKT




8 CKT




10 CKT



12 CKT



PCB LAYOUT: COMPONENT SIDE
RECOMMENDED PCB THICKNESS: 1.58 MM/.062 IN TO
2.36 MM/.093 IN



PCB LAYOUT: COMPONENT SIDE
RECOMMENDED PCB THICKNESS: 1.58 MM/.062 IN TO
2.36 MM/.093 IN

SEE SHT 1 REV D4	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	MEGA-FIT VERTICAL HEADER ASSY 2-12 CKT TOP LATCH molex SD-76829-0100	SHEET NO. 2 OF 2	
			mm	INCH	DRAWN BY MKARADIMAS	DATE 2010/10/06	TITLE					
			3 PLACES ±	±	CHECKED BY APATEL	DATE 2010/10/06						
			2 PLACES ±0.25	±	APPROVED BY	DATE						
			1 PLACE ±	±	APATEL	2012/06/13						
			0 PLACE ±	±	MATERIAL NO.				DOCUMENT NO.			
			ANGULAR ±1/2°		SEE CHART				SD-76829-0100			
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE D				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			