





STRIP MATERIAL NUMBER	FINISH
84525-0017	SELECTIVE TIN 100μ INCH MINIMUM OVER NICKEL 80μ INCH MINIMUM OVERALL
84525-0039	SELECTIVE HARD GOLD 30μ INCH MINIMUM WITH SELECTIVE TIN 100μ INCH MINIMUM OVER NICKEL 50μ INCH MINIMUM OVERALL



WIRE INSULATION O.D. RANGE  $\frac{.075-.130}{1.90-3.30}$



Section Y-Y  
Scale 5:1  
INSULATION CRIMP



Section Z-Z  
Scale 5:1  
CONDUCTOR CRIMP

- NOTES:
1. TERMINAL MATERIAL: COPPER ALLOY, .0118/0.300 THICK. FINISH: SEE CHART.
  2. HOOD MATERIAL: STAINLESS STEEL, .006/0.15 THICK.
  3. STRIP PARTS ARE REELED 3000 PARTS PER REEL AS SHOWN ABOVE.
  4. TERMINAL FOR USE WITH SERIES XRC CONNECTOR ASSEMBLIES.
  5. ALL MATERIALS AND FINISHES ARE ROHS COMPLIANT.

UPDATE LENGTH EC NO: IPG2012-0063 DRAWING/REV 2011/12/06 CHKD: CHIKD APPR: DTITUS 2012/01/09	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
	$\nabla=0$ $\nabla=0$	mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± .005 2 PLACES ± 0.13 ± --- 1 PLACE ± --- ± --- ANGULAR ± ---°	IN/MM	2:1	INCH	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DRAWN BY: MODELL CHECKED BY: RDEROSS APPROVED BY: DTITUS DATE: 2009/04/03 DATE: 2009/04/03 DATE: 2010/12/06	MATERIAL NO. SEE CHART	TITLE XRC SOCKET W/SNAP WINDOW 14-18AWG .075"-.130" WIRE DIA	DOCUMENT NO. SD-84525-005	SHEET NO. 1 OF 1
	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					