




- NOTES:
- △ MATERIAL CONTACTS; PHOSPHORBRONZE
 - △ MATERIAL SHIELD ; PHOSPHORBRONZE
 - △ MATERIAL HOUSING; GLASSFILLED POLYESTER (GRAY)
 - △ GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1,27μm NICKEL MIN. AND ACTION PIN: 0,5μm TIN MIN. FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
 - △ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 2.
 - △ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 1.
 - △ CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.
 - △ CONNECTOR LUBRICATED WITH TELCORDIA GR-1217-CORE APPROVED LUBRICANT.
 - △ ASSEMBLY PRINTED WITH P/N AND DATECODE
 - △ THE MARKING CAN APPEAR ON THE FRONT SIDE OR BACK SIDE.
 - △ HOLE PATTERN FOR FEMALE CONNECTOR TYPE C
 - △ 55 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
 - △ ROW "f" 6 PLATED THROUGH HOLES FOR UPBERSHIELD
 - △ SHIELD MOUNTED ON CONNECTOR WITH DOUBLE SIDED ADHESIVE TAPE OR ADHESIVE
 - 12 FITS WITH LOWERSHIELD, BASIC PARTNUMBER : 5352112.
 - △ 0.76μm MIN Au PLATING AT MATING SURFACES.

COMPONENT SIDE AS SHOWN

RECOMMENDED PCB-HOLE LAY-OUT

SCALE 2,5:1

5x 4,0 = 20,0

4x 2,0 = 8,0

10x 2,0 = 20,0

1,5

EDGE OF P.C.BOARD

ALL HOLES

2,0

0,05

1 1

P.C.B. HOLE DIM. ACTION PIN

FOR DETAILS SEE

APPLICATION SPECIFICATION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

±0.2

MATERIAL

-

FINISH

-

DWN

K.N.KIRAN

19AUG2004

CHK

B.MOOIJ

24SEP2004

APVD

B.MOOIJ

24SEP2004

PRODUCT SPEC

108-19082

APPLICATION SPEC

114-19029

WEIGHT

-

CUSTOMER DRAWING

FINISH

△△△

MATERIAL

△

PARTNUMBER

3-5352115-0

△

5352115-9

△

5352115-4

△

5352115-1

TE Connectivity

Z-PACK 2mm HM

TYPE C - 11 COLUMNS

PRE-SHIELDED RECEPTACLE

SIZE

A2

CAGE CODE

00779

DRAWING NO

C=5352115

RESTRICTED TO

-

SCALE

5:1

SHEET

1 of 1

REV

G