


ENERGIZER 522





Industry Standard Dimensions



Specifications

Classification: Alkaline

Chemical System: Zinc-Manganese Dioxide (Zn/MnO₂)

No added mercury or cadmium

Designation: ANSI-1604A, IEC-6LR61

Nominal Voltage: 9.0 volts

-18°C to 55°C (0°F to 130°F) Operating Temp:

Typical Weight: 45.6 grams (1.6 oz.)


Typical Volume: 21.1 cubic centimeters (1.3 cubic inch)

Jacket: **Shelf Life:** 5 years at 21°C (80% of initial capacity)

Terminal: Miniature Snap


Milliamp-Hours Capacity

Continuous discharge to 4.8 volts at 21°C



Device Selection Guide:

Battery Selection Indicator



Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication. © Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

Form No. EBC - 1108I Page 1 of 2




ENERGIZER 522




www.energizer.com


Constant Resistance Performance





Constant Current Performance



Industry Standard Tests (21°C)







Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.

©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

Form No. EBC - 1108I Page 2 of 2