

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2011

REVISIONS

© COPYRIGHT 2011 BY - ALL RIGHTS RESERVED.

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	ECR-14-009314	24MAR2015	M.P.	M.G.
	D1	REVISED (ECR-15-014031)	25SEP2015	M.G.	M.G.

27.4 REF.

9.3±0.2

7.4±0.2

∅5.5±0.2

3.0±0.2

6.0±0.2

24.0±0.2

32.2

26.6±0.2

7.2

30.8±0.3

14.0±0.2

31.4±0.2

33.3±0.2

35.2±0.2

1

2

3

4

5

PA66-GF20

3.1

STE

5

4

3

2

1

STE

3.1

PA66-GF20

5

4

3

2

1

STE

3.1

PA66-GF20

1) FOR COUNTERPART DETAILS, SEE SHEET 2 OF 2

FINISH/COLOR	MATERIAL	PART NUMBER
GRAY	HOUSING+SEC.LOCK: PA66-GF SEALING: LSR	282089-2
BLACK	HOUSING+SEC.LOCK: PA66-GF SEALING: LSR	282089-1

TE CONNECTIVITY TRADE MARK,
(IN ALTERNATIVE: "AMP" LOGO,
OR "Tyco Electronics" LOGO)SEALING
(COLOUR YELLOW)PRE-ASSEMBLED SECONDARY LOCK
(COLOUR RED)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0.3
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±2°

FINISH

SEE TABLE

DWN 05-1992

C. BERTINI

CHK 05-1992

A. BRUNI

APVD -

NAME -

PRODUCT SPEC

108-20090

APPLICATION SPEC

412-20000

WEIGHT

5.45gr

Customer Drawing

TE Connectivity

AMP SUPERSEAL 1.5 SRS.
5 POSITIONS PLUG ASS'Y




SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-282089	-

SCALE 3:1 SHEET 1 OF 2 REV D1


1470-19 (3/13)

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

COUNTERPART DETAILS



TAB DETAILS



MATERIALS: PA66-GF FOR HOUSING
TIN PLATED BRASS FOR TABS

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN C. BERTINI 05-1992


CHK A. BRUNI 05-1992

APVD -

NAME -

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:



- 0 PLC ±0.3
- 1 PLC ±0.1
- 2 PLC ±0.05
- 3 PLC ±
- 4 PLC ±
- ANGLES ±2°
- FINISH

MATERIAL

PRODUCT SPEC

108-20090

APPLICATION SPEC

412-20000

WEIGHT 5.45gr

AMP SUPERSEAL 1.5 SRS. 5 POSITIONS PLUG ASS'Y

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A300779 C-282089

Customer Drawing

SCALE 1:1 SHEET 2 OF 2 REV DI