







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	U1	REVISED PER ECR-15-016346	07MAY2016	NK	LP



- 1 CONTINUOUS STRIP ON REELS.
- 2 FEED IS 8.89±0.13 [.350±.005]
- 3 TIN PLATE 0.002032 [.000080] MIN.
- 4 GOLD PLATE 0.000381 [.000015] MIN OVER 0.000762 [.000030] MIN THK NICKEL.
- 5 GOLD PLATE REQUIRED IN THIS AREA ONLY.
- 6 REVERSE REELING.
- 7 MAX TEST TAB MUST ENTER & WITHDRAW FROM RECPT. WITH A MAX FORCE OF 11 LBS. (USE GAGE 100716-40). MIN TEST TAB MUST WITHDRAW FROM RECPT WITH MIN PULL OF 1 LB AFTER MAX TAB HAS BEEN INSERTED & WITHDRAWN 3 TIMES.

6	OBSOLETE	GOLD	4	1.02-2.03 DIA [.040-.080] DIA	[#24-#20] AWG	±0.025 0.79 X 1.58 ±.001 [.031 X .062]	60900-5-
	6	3	TIN				60900-4
			-				60900-3
	OBSOLETE	GOLD	4				60900-2-
	OBSOLETE	3	TIN				60900-1-
		FINISH		INSULATION RANGE	WIRE SIZE	MATING TAB THK	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 1/24/95		 TE Connectivity						
		CHK MS FEHER 1/24/95								
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R REINER 1/24/95		NAME				
		0 PLC ± —		RECEPTACLE, TAB, WRAP TYPE						
		1 PLC ± —								
		2 PLC ± 0.25 [.010]								
		3 PLC ± —		PRODUCT SPEC						
		4 PLC ± —		APPLICATION SPEC						
		ANGLES ± —		—						
MATERIAL		FINISH		WEIGHT		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
BRASS		SEE TABLE				A3		00779	C-60900	—
CUSTOMER DRAWING						SCALE		SHEET		REV
						5:1		1 OF 1		U1