


J O B B E R D R I L L S

Straight Shank

Standard Helix

BS 328 DIN 338 ISO 235/1

2658091

**Range****Finish****01 000 HSS**

1/64"-3/64"

Bright

0.30mm-1.30mm

Bright

1/16"-3/4"

P1 Blue

1.35mm-25.00mm

P1 Blue

Point Angle 118° General Purpose

Dia	Flute	Overall	Availability
in	Length	Length	
d	mm	mm	
	l ₂	l ₁	

Dia	Flute	Overall	Availability
in	Length	Length	
d	mm	mm	
	l ₂	l ₁	

Dia	Flute	Overall	Availability
in	Length	Length	
d	mm	mm	
	l ₂	l ₁	

1/64	0.30	4	19	•
	0.32	4	19	•
	0.35	4	19	•
	0.38	4	19	•
	0.40	5	20	•
	0.42	5	20	•
	0.45	5	20	•
	0.48	5	20	•
	0.50	6	22	•
	0.52	6	22	•
	0.55	7	24	•
	0.58	7	24	•
	0.60	7	24	•
	0.62	8	26	•
	0.65	8	26	•
	0.68	9	28	•
	0.70	9	28	•
	0.72	9	28	•
	0.75	9	28	•
1/32	0.78	10	30	•
	0.80	10	30	•
	0.82	10	30	•
	0.85	10	30	•
	0.88	11	32	•
	0.90	11	32	•
	0.92	11	32	•
	0.95	11	32	•
	0.98	12	34	•
	1.00	12	34	•
	1.05	12	34	•
	1.10	14	36	•
3/64	1.15	14	36	•
	1.20	16	38	•
	1.25	16	38	•
	1.30	16	38	•
	1.35	18	40	•
	1.40	18	40	•
	1.45	18	40	•
	1.50	18	40	•
1/16	1.55	20	43	•
	1.60	20	43	•
	1.65	20	43	•
	1.70	20	43	•
	1.75	22	46	•

5/64	1.80	22	46	•
	1.85	22	46	•
	1.90	22	46	•
	1.95	24	49	•
	2.00	24	49	•
	2.05	24	49	•
	2.10	24	49	•
	2.15	27	53	•
	2.20	27	53	•
	2.25	27	53	•
	2.30	27	53	•
	2.35	27	53	•
3/32	2.40	30	57	•
	2.45	30	57	•
	2.50	30	57	•
	2.55	30	57	•
	2.60	30	57	•
	2.65	30	57	•
	2.70	33	61	•
	2.75	33	61	•
7/64	2.80	33	61	•
	2.85	33	61	•
	2.90	33	61	•
	2.95	33	61	•
	3.00	33	61	•
	3.05	36	65	•
	3.10	36	65	•
	3.15	36	65	•
1/8	3.20	36	65	•
	3.25	36	65	•
	3.30	36	65	•
	3.40	39	70	•
	3.45	39	70	•
	3.50	39	70	•
	3.55	39	70	•
9/64	3.60	39	70	•
	3.65	39	70	•
	3.70	39	70	•
	3.75	39	70	•
	3.80	43	75	•
	3.85	43	75	•
	3.90	43	75	•
	3.95	43	75	•

5/32	4.00	43	75	•
	4.05	43	75	•
	4.10	43	75	•
	4.15	43	75	•
	4.20	43	75	•
	4.25	43	75	•
	4.30	47	80	•
11/64	4.40	47	80	•
	4.50	47	80	•
	4.55	47	80	•
	4.60	47	80	•
	4.65	47	80	•
	4.70	47	80	•
	4.75	47	80	•
3/16	4.80	52	86	•
	4.85	52	86	•
	4.90	52	86	•
	5.00	52	86	•
	5.10	52	86	•
13/64	5.20	52	86	•
	5.25	52	86	•
	5.30	52	86	•
	5.40	57	93	•
	5.50	57	93	•
7/32	5.60	57	93	•
	5.70	57	93	•
	5.75	57	93	•
	5.80	57	93	•
	5.90	57	93	•
15/64	6.00	57	93	•
	6.10	63	101	•
	6.20	63	101	•
	6.25	63	101	•
	6.30	63	101	•
1/4	6.35	63	101	•
	6.40	63	101	•
	6.50	63	101	•
	6.60	63	101	•
	6.70	63	101	•
17/64	6.80	69	109	•