


SAFETY ORGANIZATION(S):

THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET.

UL RECOGNIZED
CSA CERTIFIED
VDE APPROVED

IN PROCESS
IN PROCESS
IN PROCESS




OPERATING SPECIFICATIONS:

LINE VOLTAGE/CURRENT,
6 AMP., 120/250 VAC
6 AMP/40°C, 250 VAC
50-60Hz
MAX. LEAKAGE CURRENT, EACH
.25mA at 120V 60 Hz
LINE TO GROUND
.42mA at 250V 50 Hz
OPERATING AMBIENT TEMP. RANGE,
-10°C TO +40°C @ RATED CURRENT, I_o
IN AN AMBIENT, T_a , HIGHER THAN 40°C, THE MAXIMUM OPERATING
CURRENT, I_o , IS AS FOLLOWS,
 $I_o = I_r \sqrt{\frac{85-T_a}{45}}$
RELIABILITY SPECIFICATIONS:
STORAGE TEMPERATURE,
-25°C TO +85°C
HUMIDITY,
21 DAYS @ 40°C 95% RH
CURRENT OVERLOAD TEST,
6 TIMES RATED CURRENT FOR 8 SECONDS
TEST SPECIFICATIONS:
INDUCTANCE,
0.93 mH NOMINAL
CAPACITANCE, (MEASURED @ 1 KHz, 0.25 VAC MAX., 25°C ± 1°C)
LINE TO GROUND,
.003µF ± 20%
LINE TO LINE,
.02µF ± 20%
DISCHARGE RESISTOR,
1.5MΩ
LINE/GROUND AND LINE/LINE
6000 MΩ (MIN) AT 100 VDC
INSULATION RESISTANCE
20°C AND 50% RH
(W/O DISCHARGE RESISTOR)

RECOMMENDED RECEIVING INSPECTION HIPOUT:

LINE TO GROUND,
1500 Vdc FOR 1 MINUTE
LINE TO LINE,
1450 Vdc FOR 1 MINUTE
FILTER APPROVAL,
THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING
TO TEST THE UNIT IN YOUR EQUIPMENT.



50Ω - 50Ω (MINIMUM) INSERTION LOSS												
FREQUENCY MHz	1	2	3	4	5	8	10	20	30			
COMMON	15	24	25	29	31	36	40	45	45	40	20	15
DIFF. dB	1	4	6	9	17	40	40	40	41	42	35	


This document is proprietary to CORCOM INC. and is not
to be reproduced nor used for manufacturing purposes
except on CORCOM's order or prior written consent.

TOLERANCE EXCEPT AS NOTED

DECIMAL, .XXX .XX .X ANGLES
ENGLISH, ±.025
METRIC, ±

MATERIAL: AS SUPPLIED

FINISH:



POWER LINE FILTER

SCALE	DATE	DRG. NO.	REV.
NTS	10/21/92		6EOP.00
BY	ORIGINATOR		
TAM	TAM		